

SCHOTTKY BARRIER RECTIFIERS

REVERSE VOLTAGE - **70 to 100** Volts
 FORWARD CURRENT - **1.0** Ampere


FEATURES

- Metal-Semiconductor junction with guard ring
- Epitaxial construction
- Low forward voltage drop
- High current capability
- The plastic material carries UL recognition 94V-0
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

MECHANICAL DATA

- Case : JEDEC DO-41 molded plastic
- Polarity : Color band denotes cathode
- Weight : 0.012 ounces, 0.34 grams
- Mounting position : Any

DO-41



DO-41		
Dim.	Min.	Max.
A	25.4	-
B	4.10	5.20
C	0.71 $\varnothing$	0.86 $\varnothing$
D	2.00 $\varnothing$	2.70 $\varnothing$
All Dimensions in millimeter		






MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

CHARACTERISTICS	SYMBOL	SB170	SB180	SB190	SB1100	UNIT
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	70	80	90	100	V
Maximum RMS Voltage	V_{RMS}	49	56	63	70	V
Maximum DC Blocking Voltage	V_{DC}	70	80	90	100	V
Maximum Average Forward Rectified Current .375" (9.5mm) Lead Lengths @ $T_L = 100^\circ\text{C}$	$I_{(AV)}$	1.0				A
Peak Forward Surge Current 8.3ms single half sine-wave super imposed on rated load (JEDEC Method)	I_{FSM}	40				A
Maximum Forward Voltage at $I_F = 1.0\text{A}, T_J = 25^\circ\text{C}$ $I_F = 1.0\text{A}, T_J = 100^\circ\text{C}$	V_F	0.79 0.69				V
Maximum DC Reverse Current at Rated DC Blocking Voltage @ $T_J = 25^\circ\text{C}$ @ $T_J = 100^\circ\text{C}$	I_R	0.2 2.0				mA
Typical Junction Capacitance (Note 1)	C_J	30				pF
Typical Thermal Resistance (Note 2)	$R_{\theta JL}$	50				$^\circ\text{C/W}$
Operating Temperature Range	T_J	-55 to +150				$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 to +150				$^\circ\text{C}$

NOTES : 1. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
 2. Thermal Resistance Junction to Lead.

REV. 5, Oct-2010, KDHC03



Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.