







10 9 8 7 6 5 4 3 2 1


引き出し方向
PULL OUT DIRECTION

DETAIL "F"

引き出し方向
PULL OUT DIRECTION16幅テープ
(TAPE WIDTH:16)

NOTES

1. 梱包数量: 1000個/リール
NUMBER OF CONNECTOR: 1000PCS/REEL
2. リードテープ長さ
LEAD TAPE LENGTH




3. トップテープの剥離強度: 0.6±0.35N(60±35gf) (剥離方向は下図参照)
PEELING OFF FORCE OF TOP TAPE: 0.6±0.35N(60±35gf)
(PEELING DIRECTION IS SHOWN IN FOLLOWING FIG.)

<剥離速度: 300mm/min (参考)>
PEELING SPEED: 300mm/min.
(REFERENCE)

4. 製品詳細寸法は製品単体図面を参照して下さい。
For detail of connector dimensions, please see the drawing of connector itself (not packaged).
5. 材料 (MATERIAL)
キャリアテープ (CARRIER TAPE): ポリプロピレン (POLYPROPYLENE)
トップテープ (TOP TAPE): PET, PE, PEF
リール (REEL): ポリスチレン (P.S.) <リサイクル材含む>
POLYSTYRENE (P.S.) <RECYCLE MATERIAL CONTAINED>
6. 本製品は乾燥剤入り、ハイバリア梱包仕様である。
THIS PRODUCT IS HIGH BARRIER PACKAGE WITH DESICCANT.

16	17.4	3.7 2.45	9.5 8.25	5.8 4.55	53398-035*	53398-037*	3
					53398-025*	53398-027*	2
キャリアテープ幅 CARRIER TAPE WIDTH		(C)	(B)	(A)	MATERIAL NO. MODEL NO. 53398-xx* COLOR 3: 黄 YELLOW 4: 青(紫) BLUE(PURPLE) 6: 緑 GREEN	MATERIAL NO. MODEL NO. 53398-xx* COLOR 6: 黒 BLACK 7: 赤 RED	極数 CKT.

REVISED	EC NO. J2009-2060 DRWN:TKON CHKD:HMATSUMOTO APPR:NUKITA	2009/05/20 2009/05/21 2009/05/21	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				10 UNDER	± 0.2	DRAWN BY M.UMEDA	DATE 2005/02/18	TITLE 1.25 W/B CONN. WAFER ASSY EMBSTP PKG. -LEAD FREE-				
				10 OVER 30 UNDER	± 0.25	CHECKED BY K. TOYODA	DATE 2005/02/18					
				30 OVER	± 0.3	APPROVED BY N. UKITA	DATE 2005/02/18	MOLEX MOLEX INCORPORATED				
				ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-53398-039		1 OF 3		
B	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										



32	33.4	16.2	22	18.3	53398-135*	53398-137*	13	
		14.95	20.75	17.05	▲ -125*	▲ -127*	12	
		13.7	19.5	15.8	-115*	-117*	11	
24	25.4	12.45	18.25	14.55	-105*	-107*	10	
		11.2	17	13.3	-095*	-097*	9	
		9.95	15.75	12.05	-085*	-087*	8	
		8.7	14.5	10.8	-075*	-077*	7	
		7.45	13.25	9.55	-065*	-067*	6	
		6.2	12	8.3	▼ -055*	▼ -057*	5	
		4.95	10.75	7.05	53398-045*	53398-047*	4	
キャリアテープ幅 CARRIER TAPE WIDTH	D	(C)	(B)	(A)	MATERIAL NO.		極致 CKT.	
					MODEL NO. 53398-**5*			MODEL NO. 53398-**7*
					COLOR 3: 黄 YELLOW 4: 青(紫) BLUE(PURPLE) 6: 緑 GREEN			COLOR 6: 黒 BLACK 7: 赤 RED

REVISED EC NO: J2009-2060 DRWN:TKN 2009/05/20 CHKD:HMATSUMOTO 2009/05/21 APPR:NUKITA 2009/05/21 B	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	M.UMEDA	2005/02/18	TITLE 1.25 W/B CONN. WAFER ASSY EMBSTP PKG. -LEAD FREE-				
		10 OVER 30 UNDER	± 0.25	CHECKED BY	DATE					
		30 OVER	± 0.3	K.TOYODA	2005/02/18	MOLEX MOLEX INCORPORATED				
		ANGULAR ±3 °	APPROVED BY	DATE						
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		N.UKITA	2005/02/18	SD-53398-039					
			MATERIAL NO.							DOCUMENT NO.
REV			SEE TABLE		2 OF 3					
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F



E

D

C

B

A



44	45.4	18.7	24.5	20.8	53398-155*	53398-157*	15
		17.45	23.25	19.55	53398-145*	53398-147*	14
キャリアテープ幅 CARRIER TAPE WIDTH		D	(C)	(B)	(A)	MATERIAL NO. MODEL NO. 53398-xx5*	MATERIAL NO. MODEL NO. 53398-xx7*
						COLOR 3: 黄 YELLOW 4: 青(紫) BLUE/PURPLE 6: 緑 GREEN	COLOR 6: 黒 BLACK 7: 赤 RED
							種数 CKT.

REVISED EC NO: J2009-2060 DRWN:TKON CHKD:HMATSUMOTO APPR:NUKITA REV B	DESCRIPTION 2009/05/20 2009/05/21 2009/05/21	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	±0.2	DRAWN BY M.UMEDA	DATE 2005/02/18	TITLE 1.25 W/B CONN. WAFER ASSY EMBSTP PKG. -LEAD FREE-				
		10 OVER 30 UNDER	±0.25	CHECKED BY K.TOYODA	DATE 2005/02/18					
		30 OVER	±0.3	APPROVED BY N.UKITA	DATE 2005/02/18	MOLEX MOLEX INCORPORATED				
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-53398-039		3 OF 3			
	REV				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				