




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PART NO	CLEARANCE HOLE FOR SCREW	HOLE DIA
MTM1H-C	#8 (4mm)	.176 (4.47mm)
MTM1H10-C	#10 (5mm)	.214 (5.43mm)
MTM1H25-C	#14 (6mm)	.281 (7.14mm)



NOTES:

- DIMENSIONAL TOLERANCES:
 $.XX \pm .02 (.50)$
 $.XXX \pm .010 (.254)$
- USE WITH STD, LIGHT HEAVY, HEAVY MLT'S & 3/8" STRAPPING.
- DIM'S IN () ARE mm.
- PACKAGE C = 100



							TITLE							
07A	02/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW PANDUIT GLOBAL TITLE BLOCK WITH PANDUIT LOGO	SSECN01031	METAL TIE MOUNT (1) HOLE							
06A	09/04	JAMB	EJD	----	Ⓒ ADDED "LIGHT-HEAVY" MLT'S TO NOTE 2. Ⓓ CHANGED "AISI NO. 5 EDGE" TO "BROCKEN EDGES"	12052	CUSTOMER DRAWING							
05	06/04	JAMB	DPN	----	Ⓑ CHANGED PART NO. MTM1H8-C TO MTM1H-C	11723	ITEM REVISION NAME		N41042BS/07					
04	05/04	JAMB	DPN	----	Ⓐ PART NO.CHANGED FROM MTM1H14C TO MTM1H25C	11714	DATASET FILE NAME		N41042BS_DC/07A					
03	05/02	JAMB	DPN	----	MATERIAL WAS 302 S.S.	10042	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					MATERIAL:		
02	01/01	KMD	JAC	----	ADDED NOTE 4. CAD FILE SPEC WAS NPC-S41042_01	09010						304 STAINLESS STEEL		
01	5/92	DL	LM	----	ADDED MTM1H10 & MTM1H14	01012						DRAWING NUMBER:		
												N41042BS_DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY		DATE	CHK	SCALE	SHT 1 OF 1		SIZE
							SAM		3/25/91	JAC	2:1			A