

A

B



C

D

E

D MAX

B

NO. PASSI $\times$ 2.54
(NO. OF PITCHES $\times$ 2.54)

NOTE (NOTES)

- 1 FINITURA (FINISH): STAGNATO $3.5\mu\text{M}$ (TIN PLATED $3.5\mu\text{M}$).
- 2 FINITURA (FINISH): DORATO $0.4\mu\text{M}$ NELL'AREA DI CONTATTO E STAGNATO $2.5\mu\text{M}$ NELLA ZONA A SALDARE, SU $1.3\mu\text{M}$ DI NI. (DUPLEX PLATED $0.4\mu\text{M}$ GOLD IN CONTACT AREA AND $2.5\mu\text{M}$ TIN IN SOLDER AREA, OVER $1.3\mu\text{M}$ NICKEL).
- 3 FINITURA (FINISH): DORATO $0.8\mu\text{M}$ NELL'AREA DI CONTATTO E STAGNATO $2.5\mu\text{M}$ NELLA ZONA A SALDARE, SU $1.3\mu\text{M}$ DI NI. (DUPLEX PLATED $0.8\mu\text{M}$ GOLD IN CONTACT AREA AND $2.5\mu\text{M}$ TIN IN SOLDER AREA, OVER $1.3\mu\text{M}$ NICKEL).
- 4 MATERIALI (MATERIALS):
 - BLOCCHETTI: POLIESTERE AUTOESTINGUENTE UL94V-0, COLORE NERO. (HOUSINGS: FLAME RETARDANT THERMOPLASTIC, COLOR BLACK).
 - CONTATTI STAGNATI: BRONZO FOSFOROSO. (TIN PLATED CONTACTS: PHOSPHOR BRONZE).
 - CONTATTI DORATI: OTTONE. (GOLD PLATED CONTACTS: BRASS).
- 5 OBSOLETO (OBSOLETE)


6) SPECIFICA DI PRODOTTO : 108-20025
(PRODUCT SPECIFICATION : 108-20025)

7) $\varnothing$ FORI RACCOMANDATO SU PCB: $1.1^{+0.2}_{-0.2}$; 0.75 MIN. AMMESSO SOLO PER 2 POS.
(RECOMMENDED PCB HOLES DIA: $1.1^{+0.2}_{-0.2}$; 0.75 MIN. ADMITTED FOR 2 POS. ONLY)

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN
(DIMENSIONS IN) mm

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



58.5	53.34	5 280383-3	280383-2	280383-1	22
40.7	35.56	5 280382-3	280382-2	280382-1	15
33.1	27.94	280523-3	280523-2	280523-1	12
28.0	22.86	280381-3	280381-2	280381-1	10
25.4	20.32	5 280511-3	5 280511-2	280511-1	9
22.9	17.78	280380-3	280380-2	280380-1	8
17.8	12.70	280379-3	280379-2	280379-1	6
12.7	7.62	280378-3	280378-2	280378-1	4
7.7	2.54	280377-3	280377-2	280377-1	2
D	B	NUMERO (PART NUMBER) 3	NUMERO (PART NUMBER) 2	NUMERO (PART NUMBER) 1	NO. POS.

CUSTOMER DRAWING
FOR REFERENCE ONLYDISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDINGTOLLERANZE: SE NON
DIVERSAMENTE SPECIFICATO
(TOLERANCES, UNLESS
OTHERWISE SPECIFIED)

MATERIALI (MATERIALS)

SCALA
(SCALE)

VEDERE NOTA (SEE NOTE) 4

5:1

AMP AMP ITALIA S.p.A.
Corso F.lli Cervi, 15
COLLENO (TORINO)DESCRIZIONE
(DESCRIPTION) AMPMODU II HEADER
ASS. IES, R. ANGLE, SINGLE ROWLOC. SIZE NUMERO
(DWG NO.) REV. FOGLIO
(SHEET) 1 DI
(OF) 1

R2	ADDED NOTE 7) PER EC ET00-0213-01	07 SEP 2001	ANGOLI (ANGLES) $\pm 2^\circ$
R1	ADDED DIMENSION & PROD. SPEC. NO. PER EC ET00-0292-00	F.R. 29 NOV 2000	DIS. G. CAMPIA (DR.) 12 FEB 90
R	OBSOLETE P/N'S ET00-0256-97	F.B. 18 JUL 1997	CONT. - (CHK)
L	OBSOLETE IL PN. 280382-3 OBSOLETE PN 280382-3	C.C. 8/91	
K	AGGIORNATO E RIDISEGNATO (REVISED & REDRAWN)	G.C. 2/90	
REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DR) (DATE)	APP. DATA (APP.) (DATE)