


Rev.	Revision	Date
01	Update	11/4/2010



① CABLE:COAXIAL CABLE RG58/U
OD:5.0MM BLACK PVC

② CONN:BNC Soldering Lin type

③ PVC:PVC 45P BLACK

P1		P2
1	CORE	1
2	WEAVES	2

Wiring table

Test Condition

(1)high-pressured test:DC 300V

(2)Insulation impedance:10M Ω

(3)Leads passes impedance:5.0 Ω MAX

DRAWN	Phoebe	11/4/2010	UNIT: foot		
CHECKED	Sara	11/4/2010			
ENG APPR.					
MFG APPR.			Sinotech		
Q.A.					
GSE 231015			SIZE A4	P/N 169818	REV 01
			SCALE: 8:1	Weight(kg):	SHEET 1 OF 1