

H-Series





The H-Series toggle switches are heavy-duty, high voltage, high amperage, three-pole switches. These switches have a slow-make, slow-break contact mechanism, are AC rated to 600V, and are available in a wide range of ratings, circuits, terminations and bushing/toggle configurations.

Specifications

- Certifications*: UL, CSA,
- Dielectric Strength: 1,000 V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Phenolic
- Actuator Material: Brass/Nickel Plate or Polycarbonate
- Bushing Material: Brass/Nickel Plate

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



H **K** **25** **1** **-** **73**

SERIES **CIRCUIT¹** **TERMINATION/FUNCTION**

H THREE POLE TOGGLE

K ON-NONE-OFF
L ON-NONE-ON
M ON-OFF-ON

RATING

A27 6A 600VAC	26 3A 250VAC
12A 250VAC	6A 125VAC
17A 125VAC	1/4HP 125-250VAC
1HP 125VAC	1, 2 OR 3 PHASE
1, 2 OR 3 PHASE	27 12A 250VAC
1 1/2HP 250VAC	17A 125VAC
1, 2 OR 3 PHASE	1 1/2HP 250VAC
2HP 480-600VAC;	1, 2 OR 3 PHASE
3 PHASE	28 5A 250VAC
25 10A 250VAC	8A 125VAC
15A 125VAC	1/2HP 125-250VAC
3/4HP 125-250VAC	1, 2 OR 3 PHASE
1, 2 OR 3 PHASE	

NOTES:

Shading indicates standard configurations.

For bushing accessories, see pages 69 and 70.

¹ Consult factory for additional circuits.

² Nylon toggles are available with 4-pole base only.

NBL toggle uses black oxide plated metal bushing for standard construction. NWH toggle uses nickel plated metal bushing for standard construction.

FUNCTION	SOLDER LUG	.250 TAB (QC)	.187 TAB (QC)	SCREW TERM.	WIRE LEAD	PC TERM.
ON-NONE-OFF	0	1	3	4	5	6
(ON)-NONE-OFF	A	B	D	E	F	G
ON-NONE-(OFF)	L	M	R	S	T	U
ON-NONE-ON	0	1	3	4	5	6
ON-NONE-(ON)	A	B	D	E	F	G
ON-OFF-ON	0	1	3	4	5	6
ON-OFF-(ON)	A	B	D	E	F	G
(ON)-OFF-(ON)	L	M	R	S	T	U

TOGGLE STYLE²

BAT	TOGGLE LENGTH	BUSHING LENGTH	SUFFIX NO.	NEOPRENE SEAL
	.687	.465	73	78
	1.25	.343	B2	---



NYLON .687 .465
.687 .465

NBL3 **NBL8**
NWH3 **NWH8**

