

SAC-12P-MS/10,0-PVC SCO

Order No.: 1554801



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1554801>

Sensor/Actuator cable, 12-position, PVC, Black RAL 9005, Plug, straight M12-SPEEDCON, A-coded, on Free conductor end, Cable length: 10 m



Product notes

WEEE/RoHS-compliant since:
04/13/2007



Commercial data

GTIN (EAN)	 4 046356 176224
sales group	D118
Pack	1 pcs.
Customs tariff	85444290
Catalog page information	Page 96 (PC-2009)

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Rated current at 40°C	1.5 A
Rated voltage	30 V
Number of positions	12
Volume resistance	≤ 5 mΩ

Insulation resistance	$\geq 10 \text{ M}\Omega$
Length of cable	10 m
Stripping length of the free conductor end	35 mm
Ambient temperature (operation)	-25 °C ... 90 °C (Male connector / female connector)

General characteristics


Standards/regulations	M12 connector IEC 61076-2-101
Coding	A - standard
Surge voltage category	II
Pollution degree	3
Degree of protection	IP65/IP68/IP69K
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material of grip body	TPU, hardly inflammable, self-extinguishing
Material, knurls	Zinc die-cast, (nickel-plated)
Status display	No

Conductor data

Cable type	PVC black
Conductor cross section	0.14 mm ²
AWG signal line	26
Conductor structure signal line	18x 0.10 mm
External cable diameter	5.90 mm
Wire colors	Color-coded DIN 47100
External sheath, color	Black RAL 9005
Conductor resistance	142 Ω /m
Overall twist	Wires twisted in layers
Outer sheath, material	PVC
Material conductor insulation	PVC
Conductor material	Bare Cu litz wires
Smallest bending radius, movable installation	88.5 mm
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (cable, flexible installation)


Diagrams/Drawings

Dimensioned drawing




M12 SPEEDCON connector, straight

Circuit diagram



Contact assignment of the M12 plug

Schematic diagram



Pin assignment M12 male connector, 12-pos., male side view

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;