


6 mm Square Thin Type SMD Light Touch Switches

Type: **EVQP0**
EVQQ2




■ Features

- External dimensions : 6.5 mm×6.0 mm, Height 1.8 mm (Excluding the push plate)
- With or without ground terminal, height, operating force
- Overstroke travel

■ Recommended Applications

- Operating switches for other electronic equipment
- Operation switches for PC mouse
- Car audio systems

■ Explanation of Part Numbers










■ Specifications

Type			Snap action/Push-on type SPST	
Electrical	Rating		10 μA 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance		100 mΩ max.	
	Insulation Resistance		100 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage		250 Vac for 1 minute	
	Bouncing		10 ms max. (ON, OFF)	
Mechanical	Operating Force	EVQP0	0.6 N, 1.0 N	
		EVQQ2	0.5 N, 1.0 N, 1.3 N, 1.6 N, 2.6 N, 3.5 N	
	Travel		Short push travel 0.25 mm, Overstroke travle 0.35 mm	
Endurance	Operating Life	EVQP0	0.6 N : 2000000 cycles min. 1.0 N : 1000000 cycles min.	
		EVQQ2	0.5 N : 2000000 cycles min. 1.0 N, 1.3 N, 1.6 N : 1000000 cycles min. 2.6 N : 200000 cycles min. 3.5 N : 100000 cycles min.	
Operating Temperature			-20 °C to +70 °C	
Storage Temperature			-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit			H=2.0 mm	4000 pcs. Embossed Taping (Reel Pack)
			H=2.5 mm, 3.1 mm	2000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton			H=2.0 mm	20000 pcs.
			H=2.5 mm, 3.1 mm	10000 pcs.






Note: Non washable

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.


■ Dimensions in mm (not to scale)

No. 1					
EVQP0					
Overstroke travel : 0.35 mm With J-bent terminals					
					
	 Circuit Diagram  PWB land pattern for reference				
Part Numbers	Operating Force	Height	Push Plate Color	Ground Terminal	Operating Life
EVQP0N02B	0.6 N	2.5 mm	Blue	Without	2000000 cycles
EVQP0P02B	0.6 N	2.5 mm	Blue	With	2000000 cycles
EVQP0Q02Q	1.0 N	2.5 mm	Gray	Without	1000000 cycles
EVQP0S02Q	1.0 N	2.5 mm	Gray	With	1000000 cycles


■ Dimensions in mm (not to scale)

No. 2															
EVQQ2															
Short push travel : 0.25 mm With J-bent terminals															
															
		 Circuit Diagram  PWB land pattern for reference <table><tr><th colspan="2">Height</th></tr><tr><th>H</th><th></th></tr><tr><td>2.0±0.2</td><td></td></tr><tr><td>2.5±0.2</td><td></td></tr><tr><td>3.1^{+0.3}_{-0.1}</td><td></td></tr></table>				Height		H		2.0±0.2		2.5±0.2		3.1 ^{+0.3} _{-0.1}	
Height															
H															
2.0±0.2															
2.5±0.2															
3.1 ^{+0.3} _{-0.1}															
Part Numbers	Operating Force	H=Height	Push Plate Color	Ground Terminal	Operating Life										
EVQQ2B01W	0.5 N	2.0 mm	White	Without	2000000 cycles										
EVQQ2B02W	0.5 N	2.5 mm	White	Without	2000000 cycles										
EVQQ2B03W	0.5 N	3.1 mm	White	Without	2000000 cycles										
EVQQ2D01W	0.5 N	2.0 mm	White	With	2000000 cycles										
EVQQ2D02W	0.5 N	2.5 mm	White	With	2000000 cycles										
EVQQ2D03W	0.5 N	3.1 mm	White	With	2000000 cycles										
EVQQ2F01W	1.0 N	2.0 mm	White	Without	1000000 cycles										
EVQQ2F02W	1.0 N	2.5 mm	White	Without	1000000 cycles										
EVQQ2F03W	1.0 N	3.1 mm	White	Without	1000000 cycles										
EVQQ2H01W	1.0 N	2.0 mm	White	With	1000000 cycles										
EVQQ2H02W	1.0 N	2.5 mm	White	With	1000000 cycles										
EVQQ2H03W	1.0 N	3.1 mm	White	With	1000000 cycles										
EVQQ2K01W	1.3 N	2.0 mm	White	Without	1000000 cycles										
EVQQ2K02W	1.3 N	2.5 mm	White	Without	1000000 cycles										
EVQQ2K03W	1.3 N	3.1 mm	White	Without	1000000 cycles										
EVQQ2M01W	1.3 N	2.0 mm	White	With	1000000 cycles										
EVQQ2M02W	1.3 N	2.5 mm	White	With	1000000 cycles										
EVQQ2M03W	1.3 N	3.1 mm	White	With	1000000 cycles										
EVQQ2P01W	1.6 N	2.0 mm	White	Without	1000000 cycles										
EVQQ2P02W	1.6 N	2.5 mm	White	Without	1000000 cycles										
EVQQ2P03W	1.6 N	3.1 mm	White	Without	1000000 cycles										
EVQQ2S01W	1.6 N	2.0 mm	White	With	1000000 cycles										
EVQQ2S02W	1.6 N	2.5 mm	White	With	1000000 cycles										
EVQQ2S03W	1.6 N	3.1 mm	White	With	1000000 cycles										
EVQQ2U01W	2.6 N	2.0 mm	White	Without	200000 cycles										
EVQQ2U02W	2.6 N	2.5 mm	White	Without	200000 cycles										
EVQQ2U03W	2.6 N	3.1 mm	White	Without	200000 cycles										
EVQQ2W01W	2.6 N	2.0 mm	White	With	200000 cycles										
EVQQ2W02W	2.6 N	2.5 mm	White	With	200000 cycles										
EVQQ2W03W	2.6 N	3.1 mm	White	With	200000 cycles										
EVQQ2Y01W	3.5 N	2.0 mm	White	Without	100000 cycles										
EVQQ2Y02W	3.5 N	2.5 mm	White	Without	100000 cycles										
EVQQ2Y03W	3.5 N	3.1 mm	White	Without	100000 cycles										
EVQQ2201W	3.5 N	2.0 mm	White	With	100000 cycles										
EVQQ2202W	3.5 N	2.5 mm	White	With	100000 cycles										
EVQQ2203W	3.5 N	3.1 mm	White	With	100000 cycles										

■ Recommended Reflow Soldering Conditions




● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P1	P2	P0	D0 Dia	t1	t2
EVQP0, EVQQ2	2.0	6.7±0.2	7.5±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 ^{+0.1} ₋₀	0.30±0.05	2.2±0.2
	2.5/3.1											3.2±0.2


● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.2	φ21.0±0.8	2.0±0.5

Item	W	T	t	r
Rate (mm)	13.5±1.0	17.5±1.0	—	—

■ Recommended Shape of Test Pole



■ Recommended Operating Conditions

