






AUX. VIEW
SCALE 1:1



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: NONE
6. "XX" REFERS TO QUANTITY OF CIRCUITS
7. INCH DIMENSIONS ARE SHOWN IN BRACKETS [XXX].
8. ALL COMPONENTS ARE ROHS COMPLIANT.
9. -59 OPTION: SCREWS SUPPLIED UNASSEMBLED.

5	XX	SCREW, #6-32X.250 PAN HD PH-SL W/SQ WSHR (-50 OPTION)	STEEL	ZN, CLEAR CHROMATE
4	XX	SCREW, #6-32 X .250 PAN HD PH-SL (-49 OPTION)	BRASS	NICKEL
3	XX	SCREW, #6-32 X .250 BHD PH-SL (STANDARD)	STEEL	ZN, CLEAR CHROMATE
2	XX	TERMINAL, STYLE 9, FAST TAB	BRASS	TIN
1	1	BARRIER TERMINAL STRIP	THERMOPLASTIC	BLACK
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

ADDED -59 OPTION
EC NO: ETC2006-0503
2006/07/17
DR:WNEHLE
CHKD:JMACNEIL
APPR:RDORESS
2006/07/20

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .01	± .001
2 PLACES	± .03	± .003
1 PLACE	± .06	± .006
ANGULAR	± 2 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY
C. YORK

DATE
2003/12/29

CHECKED BY

DATE

APPROVED BY

DATE

MATERIAL NO.
SEE CHART

SCALE
2:1

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

11.11MM [.437] SR BTS
FT ASSY

MOLEX INCORPORATED

DOCUMENT NO.
SD-38731-001

SHEET NO.
1 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

10

9

8

7

6

5

4

3

2

38731

F

E

D

C

B

A

F

E

D

C

B

A

MATERIAL NO. (STD)	MATERIAL NO. (-49)	MATERIAL NO. (-50)	MATERIAL NO. (-51)	MATERIAL NO. (-49-59)	# OF CIRC. "XX"	"A"	"B"	"C"	"D"
387316602	387316902	387317202	387390012	-	2	43.5 [1.71]	11.1 [0.44]	33.3 [1.31]	24.5 [0.97]
387316603	387316903	387317203	-	387390094	3	54.6 [2.15]	22.2 [0.88]	44.5 [1.75]	35.7 [1.40]
387316604	387316904	387317204	387390110	-	4	65.7 [2.59]	33.3 [1.31]	55.6 [2.19]	46.8 [1.84]
387316605	387316905	387317205	-	-	5	76.8 [3.03]	44.5 [1.75]	66.7 [2.63]	57.9 [2.28]
387316606	387316906	387317206	-	-	6	87.9 [3.46]	55.6 [2.19]	77.8 [3.06]	69.0 [2.72]
387316607	387316907	387317207	-	-	7	99.1 [3.90]	66.7 [2.63]	88.9 [3.50]	80.1 [3.15]
387316608	387316908	387317208	-	-	8	110.2 [4.34]	77.8 [3.06]	100.0 [3.94]	91.2 [3.59]
387316609	387316909	387317209	-	-	9	121.3 [4.78]	88.9 [3.50]	111.1 [4.38]	102.3 [4.03]
387316610	387316910	387317210	-	-	10	132.4 [5.21]	100.0 [3.94]	122.2 [4.81]	113.4 [4.47]
387316611	387316911	387317211	-	-	11	143.5 [5.65]	111.1 [4.38]	133.4 [5.25]	124.6 [4.90]
387316612	387316912	387317212	-	-	12	154.6 [6.09]	122.2 [4.81]	144.5 [5.69]	135.7 [5.34]
387316613	387316913	387317213	-	-	13	165.7 [6.53]	133.4 [5.25]	155.6 [6.13]	146.8 [5.78]
387316614	387316914	387317214	387390543	-	14	176.8 [6.96]	144.5 [5.69]	166.7 [6.56]	157.9 [6.22]
387316615	387316915	387317215	-	-	15	188.0 [7.40]	155.6 [6.13]	177.8 [7.00]	169.0 [6.65]
387316616	387316916	387317216	-	-	16	199.1 [7.84]	166.7 [6.56]	188.9 [7.44]	180.1 [7.09]
387316617	387316917	387317217	-	-	17	210.2 [8.28]	177.8 [7.00]	200.0 [7.88]	191.2 [7.53]
387316618	387316918	387317218	-	-	18	221.3 [8.71]	188.9 [7.44]	211.1 [8.31]	202.3 [7.97]
387316619	387316919	387317219	-	-	19	232.4 [9.15]	200.0 [7.88]	222.3 [8.75]	213.5 [8.40]
387316620	387316920	387317220	-	-	20	243.5 [9.59]	211.1 [8.31]	233.4 [9.19]	224.6 [8.84]
387316621	387316921	387317221	-	-	21	254.6 [10.03]	222.3 [8.75]	244.5 [9.63]	235.7 [9.28]
387316622	387316922	387317222	-	-	22	265.7 [10.46]	233.4 [9.19]	255.6 [10.06]	246.8 [9.72]
387316623	387316923	387317223	-	-	23	276.9 [10.90]	244.5 [9.63]	266.7 [10.50]	257.9 [10.15]
387316624	387316924	387317224	-	-	24	288.0 [11.34]	255.6 [10.06]	277.8 [10.94]	269.0 [10.59]
387316625	387316925	387317225	-	-	25	299.1 [11.78]	266.7 [10.50]	288.9 [11.38]	280.1 [11.03]
387316626	387316926	387317226	-	-	26	310.2 [12.21]	277.8 [10.94]	300.0 [11.81]	291.2 [11.47]
387316627	387316927	387317227	-	-	27	321.3 [12.65]	288.9 [11.38]	311.2 [12.25]	302.4 [11.90]
387316628	387316928	387317228	-	-	28	332.4 [13.09]	300.0 [11.81]	322.3 [12.69]	313.5 [12.34]
387316629	387316929	387317229	-	-	29	343.5 [13.53]	311.2 [12.25]	333.4 [13.13]	324.6 [12.78]
387316630	387316930	387317230	-	-	30	354.6 [13.96]	322.3 [12.69]	344.5 [13.56]	335.7 [13.22]

ADDED -59 OPTION
EC NO: ETC2006-0503
DRW:NEHLE 2006/07/17
CHKD: JMACNEIL 2006/07/19
APPR: RDOSS 2006/07/20

QUALITY SYMBOLS
▽=0
▽=0
DESCRIPTION
REV

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .005
2 PLACES	± 0.13	± .01
1 PLACE	± 0.3	± ---
ANGULAR ± 2 °		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY C. YORK	DATE 2003/12/29
CHECKED BY ---	DATE ---
APPROVED BY ---	DATE ---

MATERIAL NO.
SEE CHART

SIZE
B

SCALE
2:1

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

TITLE
11.11MM [.437] SR BTS
FT ASSY

MOLEX INCORPORATED

DOCUMENT NO.
SD-38731-001

SHEET NO.
2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

9

8

7

6

5

4

3

2

1