

## CMOS Presettable Up/Down Counter

Binary or BCD-Decade

High-Voltage Types (20-Volt Rating)

■ CD4029B consists of a four-stage binary or BCD-decade up/down counter with provisions for look-ahead carry in both counting modes. The inputs consist of a single **CLOCK**, **CARRY-IN (CLOCK ENABLE)**, **BINARY/DECADE**, **UP/DOWN**, **PRESET ENABLE**, and four individual **JAM** signals. **Q1**, **Q2**, **Q3**, **Q4** and a **CARRY OUT** signal are provided as outputs.


A high **PRESET ENABLE** signal allows information on the **JAM INPUTS** to preset the counter to any state asynchronously with the clock. A low on each **JAM** line, when the **PRESET-ENABLE** signal is high, resets the counter to its zero count. The counter is advanced one count at the positive transition of the clock when the **CARRY-IN** and **PRESET ENABLE** signals are low. Advancement is inhibited when the **CARRY-IN** or **PRESET ENABLE** signals are high. The **CARRY-OUT** signal is normally high and goes low when the counter reaches its maximum count in the **UP** mode or the minimum count in the **DOWN** mode provided the **CARRY-IN** signal is low. The **CARRY-IN** signal in the low state can thus be considered a **CLOCK ENABLE**. The **CARRY-IN** terminal must be connected to **V<sub>SS</sub>** when not in use.

Binary counting is accomplished when the **BINARY/DECADE** input is high; the counter counts in the decade mode when the **BINARY/DECADE** input is low. The counter counts up when the **UP/DOWN** input is high, and down when the **UP/DOWN** input is low. Multiple packages can be connected in either a parallel-clocking or a ripple-clocking arrangement as shown in Fig. 17.

Parallel clocking provides synchronous control and hence faster response from all counting outputs. Ripple-clocking allows for longer clock input rise and fall times.

The CD4029B-series types are supplied in 16-lead hermetic dual-in-line ceramic packages (F3A suffix), 16-lead dual-in-line plastic packages (E suffix), 16-lead small-outline packages (M, M96, MT, and NSR suffixes), and 16-lead thin shrink small-outline packages (PW and PWR suffixes).

CD4029B Terminal Diagram



92CS-24472R1


## CD4029B Types

### Features:

- Medium-speed operation . . . 8 MHz (typ.)  
@  $C_L = 50$  pF and  $V_{DD} - V_{SS} = 10$  V
- Multi-package parallel clocking for synchronous high speed output response or ripple clocking for slow clock input rise and fall times
- "Preset Enable" and individual "Jam" inputs provided
- Binary or decade up/down counting
- BCD outputs in decade mode
- 100% tested for quiescent current at 20 V
- 5-V, 10-V, and 15-V parametric ratings
- Standardized, symmetrical output characteristics
- Maximum input current of  $1 \mu A$  at 18 V over full package-temperature range; 100 nA at 18 V and 25°C
- Noise margin (over full package-temperature range)  
1 V at  $V_{DD} = 5$  V  
2 V at  $V_{DD} = 10$  V  
2.5 V at  $V_{DD} = 15$  V
- Meets all requirements of JEDEC Tentative Standard No. 13B, "Standard Specifications for Description of 'B' Series CMOS Devices"

### Applications:

- Programmable binary and decade counting/frequency synthesizers-BCD output
- Analog to digital and digital to analog conversion
- Up/Down binary counting
- Magnitude and sign generation
- Up/Down decade counting
- Difference counting



**RECOMMENDED OPERATING CONDITIONS** at  $T_A = 25^\circ C$ , Except as Noted. For maximum reliability, nominal operating conditions should be selected so that operation is always within the following ranges:

| CHARACTERISTIC                                                    | $V_{DD}$<br>(V) | LIMITS |      | UNITS   |
|-------------------------------------------------------------------|-----------------|--------|------|---------|
|                                                                   |                 | Min.   | Max. |         |
| Supply-Voltage Range (For $T_A =$ Full Package-Temperature Range) | —               | 3      | 18   | V       |
| Setup Time $t_{SU}$ :<br>Carry-In                                 | 5               | 200    | —    | ns      |
|                                                                   | 10              | 70     | —    |         |
|                                                                   | 15              | 60     | —    |         |
| U/D or B/D                                                        | 5               | 340    | —    |         |
|                                                                   | 10              | 140    | —    |         |
|                                                                   | 15              | 100    | —    |         |
| Clock Pulse Width, $t_W$                                          | 5               | 180    | —    | ns      |
|                                                                   | 10              | 90     | —    |         |
|                                                                   | 15              | 60     | —    |         |
| Preset Enable Pulse Width, $t_W$                                  | 5               | 130    | —    |         |
|                                                                   | 10              | 70     | —    |         |
|                                                                   | 15              | 50     | —    |         |
| Clock Input Frequency, $f_{CL}$                                   | 5               | —      | 2    | MHz     |
|                                                                   | 10              | —      | 4    |         |
|                                                                   | 15              | —      | 5.5  |         |
| Clock Rise and Fall Time, $t_{rCL}$ , $t_{fCL}$                   | 5               | —      | —    | $\mu s$ |
|                                                                   | 10              | —      | 15   |         |
|                                                                   | 15              | —      | —    |         |

# CD4029B Types

## MAXIMUM RATINGS, Absolute-Maximum Values:

|                                                                              |                                           |                                              |
|------------------------------------------------------------------------------|-------------------------------------------|----------------------------------------------|
| DC SUPPLY-VOLTAGE RANGE, ( $V_{DD}$ )                                        | Voltages referenced to $V_{SS}$ Terminal) | -0.5V to +20V                                |
| INPUT VOLTAGE RANGE, ALL INPUTS                                              |                                           | -0.5V to $V_{DD} + 0.5V$                     |
| DC INPUT CURRENT, ANY ONE INPUT                                              |                                           | $\pm 10mA$                                   |
| POWER DISSIPATION PER PACKAGE ( $P_D$ ):                                     |                                           |                                              |
| For $T_A = -55^\circ C$ to $+100^\circ C$                                    |                                           | 500mW                                        |
| For $T_A = +100^\circ C$ to $+125^\circ C$                                   |                                           | Derate Linearly at 12mW/ $^\circ C$ to 200mW |
| DEVICE DISSIPATION PER OUTPUT TRANSISTOR                                     |                                           |                                              |
| FOR $T_A =$ FULL PACKAGE-TEMPERATURE RANGE (All Package Types)               |                                           | 100mW                                        |
| OPERATING-TEMPERATURE RANGE ( $T_A$ )                                        |                                           | $-55^\circ C$ to $+125^\circ C$              |
| STORAGE TEMPERATURE RANGE ( $T_{stg}$ )                                      |                                           | $-65^\circ C$ to $+150^\circ C$              |
| LEAD TEMPERATURE (DURING SOLDERING):                                         |                                           |                                              |
| At distance $1/16 \pm 1/32$ inch ( $1.59 \pm 0.79mm$ ) from case for 10s max |                                           | $+265^\circ C$                               |

## STATIC ELECTRICAL CHARACTERISTICS

| CHARAC-<br>TERISTIC                                         | CONDITIONS            |                        |                        | LIMITS AT INDICATED TEMPERATURES (°C) |       |       |       |       |                   |      | UNITS |
|-------------------------------------------------------------|-----------------------|------------------------|------------------------|---------------------------------------|-------|-------|-------|-------|-------------------|------|-------|
|                                                             | V <sub>O</sub><br>(V) | V <sub>IN</sub><br>(V) | V <sub>DD</sub><br>(V) | -55                                   | -40   | +85   | +125  | +25   |                   |      |       |
|                                                             |                       |                        |                        |                                       |       |       |       | Min.  | Typ.              | Max. |       |
| Quiescent<br>Device<br>Current,<br>I <sub>DD</sub> Max.     | —                     | 0,5                    | 5                      | 5                                     | 5     | 150   | 150   | —     | 0.04              | 5    | μA    |
|                                                             | —                     | 0,10                   | 10                     | 10                                    | 10    | 300   | 300   | —     | 0.04              | 10   |       |
|                                                             | —                     | 0,15                   | 15                     | 20                                    | 20    | 600   | 600   | —     | 0.04              | 20   |       |
|                                                             | —                     | 0,20                   | 20                     | 100                                   | 100   | 3000  | 3000  | —     | 0.08              | 100  |       |
| Output Low<br>(Sink) Current<br>I <sub>OL</sub> Min.        | 0.4                   | 0,5                    | 5                      | 0.64                                  | 0.61  | 0.42  | 0.36  | 0.51  | 1                 | —    | mA    |
|                                                             | 0.5                   | 0,10                   | 10                     | 1.6                                   | 1.5   | 1.1   | 0.9   | 1.3   | 2.6               | —    |       |
|                                                             | 1.5                   | 0,15                   | 15                     | 4.2                                   | 4     | 2.8   | 2.4   | 3.4   | 6.8               | —    |       |
| Output High<br>(Source)<br>Current,<br>I <sub>OH</sub> Min. | 4.6                   | 0,5                    | 5                      | -0.64                                 | -0.61 | -0.42 | -0.36 | -0.51 | -1                | —    | mA    |
|                                                             | 2.5                   | 0,5                    | 5                      | -2                                    | -1.8  | -1.3  | -1.15 | -1.6  | -3.2              | —    |       |
|                                                             | 9.5                   | 0,10                   | 10                     | -1.6                                  | -1.5  | -1.1  | -0.9  | -1.3  | -2.6              | —    |       |
|                                                             | 13.5                  | 0,15                   | 15                     | -4.2                                  | -4    | -2.8  | -2.4  | -3.4  | -6.8              | —    |       |
| Output Voltage:<br>Low-Level,<br>V <sub>OL</sub> Max.       | —                     | 0,5                    | 5                      | 0.05                                  |       |       |       | —     | 0                 | 0.05 | V     |
|                                                             | —                     | 0,10                   | 10                     | 0.05                                  |       |       |       | —     | 0                 | 0.05 |       |
|                                                             | —                     | 0,15                   | 15                     | 0.05                                  |       |       |       | —     | 0                 | 0.05 |       |
| Output<br>Voltage:<br>High-Level,<br>V <sub>OH</sub> Min.   | —                     | 0,5                    | 5                      | 4.95                                  |       |       |       | 4.95  | 5                 | —    | V     |
|                                                             | —                     | 0,10                   | 10                     | 9.95                                  |       |       |       | 9.95  | 10                | —    |       |
|                                                             | —                     | 0,15                   | 15                     | 14.95                                 |       |       |       | 14.95 | 15                | —    |       |
| Input Low<br>Voltage<br>V <sub>IL</sub> Max.                | 0.5,4.5               | —                      | 5                      | 1.5                                   |       |       |       | —     | —                 | 1.5  | V     |
|                                                             | 1,9                   | —                      | 10                     | 3                                     |       |       |       | —     | —                 | 3    |       |
|                                                             | 1.5,13.5              | —                      | 15                     | 4                                     |       |       |       | —     | —                 | 4    |       |
| Input High<br>Voltage,<br>V <sub>IH</sub> Min.              | 0.5,4.5               | —                      | 5                      | 3.5                                   |       |       |       | 3.5   | —                 | —    | V     |
|                                                             | 1,9                   | —                      | 10                     | 7                                     |       |       |       | 7     | —                 | —    |       |
|                                                             | 1.5,13.5              | —                      | 15                     | 11                                    |       |       |       | 11    | —                 | —    |       |
| Input Current<br>I <sub>IN</sub> Max.                       | —                     | 0,18                   | 18                     | ±0.1                                  | ±0.1  | ±1    | ±1    | —     | ±10 <sup>-5</sup> | ±0.1 | μA    |




Fig. 1 - Typical output low (sink) current characteristics.




Fig. 2 - Minimum output low (sink) current characteristics.




Fig. 3 - Typical output high (source) current characteristics.




Fig. 4 - Minimum output high (source) current characteristics.

# CD4029B Types




Fig. 5 - Typical transition time as a function of load capacitance.




Fig. 6 - Typical propagation delay times as a function of load capacitance (Q output).




Fig. 7 - Typical propagation delay time as a function of load capacitance (carry output).




Fig. 8 - Typical power dissipation as a function of frequency.




Fig. 9 - Logic diagram.





Fig. 10 - Timing diagram-binary mode.


## CD4029B Types



| CONTROL INPUT                                | LOGIC LEVEL | ACTION                                                                                              |
|----------------------------------------------|-------------|-----------------------------------------------------------------------------------------------------|
| BIN/DEC (B/D)                                | 1<br>0      | BINARY COUNT<br>DECADE COUNT                                                                        |
| UP/DOWN (U/D)                                | 1<br>0      | UP COUNT<br>DOWN COUNT                                                                              |
| PRESET ENABLE (PE)                           | 1<br>0      | JAM IN<br>NO JAM                                                                                    |
| CARRY IN (C <sub>I</sub> )<br>(CLOCK ENABLE) | 1<br>0      | NO COUNTER<br>ADVANCE AT POS.<br>CLOCK TRANSITION<br>ADVANCE COUNTER<br>AT POS. CLOCK<br>TRANSITION |

92CL-28675 #1

Fig. 9 – Logic diagram (cont'd).




92CS-17193R2

Fig. 11 – Conversion of clock up, clock down input signals to clock and up/down input signals.

The CD4029B CLOCK and UP/DOWN inputs are used directly in most applications. In applications where CLOCK UP and CLOCK DOWN inputs are provided, conversion to the CD4029B CLOCK and UP/DOWN inputs can easily be realized by use of the circuit in Fig. 11.

CD4029B changes count on positive transitions of CLOCK UP or CLOCK DOWN inputs. For the gate configuration shown below, when counting up the CLOCK DOWN input must be maintained high and conversely when counting down the CLOCK UP input must be maintained high.



92CM-17193R3

Fig. 12 – Timing diagram-decade mode.

## CD4029B Types

**DYNAMIC ELECTRICAL CHARACTERISTICS** at  $T_A = 25^\circ\text{C}$ , Input  $t_r, t_f = 20\text{ ns}$ ,  
 $C_L = 50\text{ pF}$ ,  $R_L = 200\text{ k}\Omega$

| CHARACTERISTIC                                                | TEST CONDITIONS |      | LIMITS |      |     | UNITS   |
|---------------------------------------------------------------|-----------------|------|--------|------|-----|---------|
|                                                               | $V_{DD}$ (V)    | Min. | Typ.   | Max. |     |         |
| Clocked Operation                                             |                 |      |        |      |     |         |
| Propagation Delay Time: $t_{PHL}$ , $t_{PLH}$<br>Q Output     | Any Input       | 5    | —      | 250  | 500 | ns      |
|                                                               |                 | 10   | —      | 120  | 240 |         |
|                                                               |                 | 15   | —      | 90   | 180 |         |
| Carry Output                                                  |                 | 5    | —      | 280  | 560 |         |
|                                                               |                 | 10   | —      | 130  | 260 |         |
|                                                               |                 | 15   | —      | 95   | 190 |         |
| Transition Time:<br>Q Outputs, Carry Output                   |                 | 5    | —      | 100  | 200 |         |
|                                                               |                 | 10   | —      | 50   | 100 |         |
|                                                               |                 | 15   | —      | 40   | 80  |         |
| Minimum Clock Pulse Width, $t_W$                              |                 | 5    | —      | 90   | 180 | ns      |
|                                                               |                 | 10   | —      | 45   | 90  |         |
|                                                               |                 | 15   | —      | 30   | 60  |         |
| Clock Rise & Fall Time, $t_{rCL}$ , $t_{fCL}^{**}$            |                 | 5    | —      | —    | 15  | $\mu s$ |
|                                                               |                 | 10   | —      | —    | 15  |         |
|                                                               |                 | 15   | —      | —    | 15  |         |
| Minimum Setup Times, $t_S^*$<br>B/D or U/D                    |                 | 5    | —      | 170  | 340 | ns      |
|                                                               |                 | 10   | —      | 70   | 140 |         |
|                                                               |                 | 15   | —      | 50   | 100 |         |
| Maximum Clock Input Frequency, $f_{CL}$                       |                 | 5    | 2      | 4    | —   | MHz     |
|                                                               |                 | 10   | 4      | 8    | —   |         |
|                                                               |                 | 15   | 5.5    | 11   | —   |         |
| Input Capacitance, $C_{IN}$                                   |                 | —    | 5      | 7.5  | pF  |         |
| Preset Enable                                                 |                 |      |        |      |     |         |
| Propagation Delay Time: $t_{PHL}$ , $t_{PLH}$<br>Q Outputs    | Any Input       | 5    | —      | 235  | 470 | ns      |
|                                                               |                 | 10   | —      | 100  | 200 |         |
|                                                               |                 | 15   | —      | 80   | 160 |         |
| Carry Output                                                  |                 | 5    | —      | 320  | 640 |         |
|                                                               |                 | 10   | —      | 145  | 290 |         |
|                                                               |                 | 15   | —      | 105  | 210 |         |
| Minimum Preset Enable Pulse Width, $t_W$                      |                 | 5    | —      | 65   | 130 |         |
|                                                               |                 | 10   | —      | 35   | 70  |         |
|                                                               |                 | 15   | —      | 25   | 50  |         |
| Minimum Preset Enable Removal<br>Time, $t_{rem}^*$            |                 | 5    | —      | 100  | 200 | ns      |
|                                                               |                 | 10   | —      | 55   | 110 |         |
|                                                               |                 | 15   | —      | 40   | 80  |         |
| Carry Input                                                   |                 |      |        |      |     |         |
| Propagation Delay Time: $t_{PHL}$ , $t_{PLH}$<br>Carry Output | Any Input       | 5    | —      | 170  | 340 | ns      |
|                                                               |                 | 10   | —      | 70   | 140 |         |
|                                                               |                 | 15   | —      | 50   | 100 |         |
| Min. HOLD Time<br>$t_H^{***}$ Carry In                        |                 | 5    | —      | 25   | 50  | ns<br>↓ |
|                                                               |                 | 10   | —      | 15   | 30  |         |
|                                                               |                 | 15   | —      | 12   | 25  |         |
| Min Set-Up Time<br>$t_S^{***}$ Carry In                       |                 | 5    | —      | 100  | 200 | ns<br>↓ |
|                                                               |                 | 10   | —      | 35   | 70  |         |
|                                                               |                 | 15   | —      | 30   | 60  |         |

\* From Up/Down, Binary/Decode, Carry In, or Preset Enable Control Inputs to Clock Edge.

\*\* If more than one unit is cascaded in the parallel clocked application,  $t_{rCL}$  should be made less than or equal to the sum of the fixed propagation delay at 15 pF and the transition time of the carry output driving stage for the estimated capacitive load. This measurement was made with a decoupling capacitor ( $>1\text{ }\mu\text{F}$ ) between  $V_{DD}$  and  $V_{SS}$ .

\*\*\*From Carry In to Clock Edge




Fig. 13 — Power dissipation test circuit.




Fig. 14 — Quiescent device current test circuit.




Fig. 15 — Input voltage test circuit.






Fig. 16 — Input current test circuit.

### CD4029B Types




- \* CARRY OUT lines at the 2nd, 3rd, etc., stages may have a negative-going glitch pulse resulting from differential delays of different CD4029B IC's. These negative-going glitches do not affect proper CD4029B operation. However, if the CARRY OUT signals are used to trigger other edge-sensitive logic devices, such as FF's or counters, the CARRY OUT signals should be gated with the clock signal using a 2-input OR gate such as CD4071B.



**Ripple Clocking Mode:**

The Up/Down control can be changed at any count. The only restriction on changing the Up/Down control is that the clock input to the first counting stage must be high. For cascading counters operating in a fixed up-count or down-count mode, the OR gates are not required between stages, and  $\overline{CO}$  is connected directly to the CL input of the next stage with  $\overline{CI}$  grounded.

**Fig. 17 — Cascading counter packages.**



**Chip dimensions and pad layout for CD4029B**

*Dimensions in parentheses are in millimeters and are derived from the basic inch dimensions as indicated. Grid graduations are in mils ( $10^{-3}$  inch).*

**PACKAGING INFORMATION**

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup> |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| 8101602EA        | ACTIVE                | CDIP         | J               | 16   | 1           | TBD                     | A42              | N / A for Pkg Type           |
| CD4029BE         | ACTIVE                | PDIP         | N               | 16   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| CD4029BEE4       | ACTIVE                | PDIP         | N               | 16   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| CD4029BF         | ACTIVE                | CDIP         | J               | 16   | 1           | TBD                     | A42              | N / A for Pkg Type           |
| CD4029BF3A       | ACTIVE                | CDIP         | J               | 16   | 1           | TBD                     | A42              | N / A for Pkg Type           |
| CD4029BM         | ACTIVE                | SOIC         | D               | 16   | 40          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BM96       | ACTIVE                | SOIC         | D               | 16   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BM96E4     | ACTIVE                | SOIC         | D               | 16   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BM96G4     | ACTIVE                | SOIC         | D               | 16   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BME4       | ACTIVE                | SOIC         | D               | 16   | 40          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BMG4       | ACTIVE                | SOIC         | D               | 16   | 40          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BMT        | ACTIVE                | SOIC         | D               | 16   | 250         | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BMTE4      | ACTIVE                | SOIC         | D               | 16   | 250         | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BMTG4      | ACTIVE                | SOIC         | D               | 16   | 250         | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BNSR       | ACTIVE                | SO           | NS              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BNSRE4     | ACTIVE                | SO           | NS              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BNSRG4     | ACTIVE                | SO           | NS              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BPWR       | ACTIVE                | TSSOP        | PW              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BPWRE4     | ACTIVE                | TSSOP        | PW              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| CD4029BPWRG4     | ACTIVE                | TSSOP        | PW              | 16   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered

---

at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.


**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


**TAPE AND REEL INFORMATION**



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CD4029BM96 | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD4029BNSR | SO           | NS              | 16   | 2000 | 330.0              | 16.4               | 8.2     | 10.5    | 2.5     | 12.0    | 16.0   | Q1            |
| CD4029BPWR | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 7.0     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS




\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CD4029BM96 | SOIC         | D               | 16   | 2500 | 333.2       | 345.9      | 28.6        |
| CD4029BNSR | SO           | NS              | 16   | 2000 | 346.0       | 346.0      | 33.0        |
| CD4029BPWR | TSSOP        | PW              | 16   | 2000 | 346.0       | 346.0      | 29.0        |

## PW (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE PACKAGE

14 PINS SHOWN




- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.  
 D. Falls within JEDEC MO-153

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



| DIM \ PINS ** | 14    | 16    | 20    | 24    |
|---------------|-------|-------|-------|-------|
| A MAX         | 10,50 | 10,50 | 12,90 | 15,30 |
| A MIN         | 9,90  | 9,90  | 12,30 | 14,70 |


4040062/C 03/03

- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.


J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |




4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

D (R-PDSO-G16)

PLASTIC SMALL-OUTLINE PACKAGE




4040047-5/J 09/09

NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 (0,15) per end.
- D. Body width does not include interlead flash. Interlead flash shall not exceed .017 (0,43) per side.
- E. Reference JEDEC MS-012 variation AC.

## D(R-PDSO-G16)



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Refer to IPC7351 for alternate board design.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.


## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



14/18 Pin Only  
20 Pin vendor option

4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

|                             |                                                                    |
|-----------------------------|--------------------------------------------------------------------|
| Amplifiers                  | <a href="http://amplifier.ti.com">amplifier.ti.com</a>             |
| Data Converters             | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>     |
| DLP® Products               | <a href="http://www.dlp.com">www.dlp.com</a>                       |
| DSP                         | <a href="http://dsp.ti.com">dsp.ti.com</a>                         |
| Clocks and Timers           | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>           |
| Interface                   | <a href="http://interface.ti.com">interface.ti.com</a>             |
| Logic                       | <a href="http://logic.ti.com">logic.ti.com</a>                     |
| Power Mgmt                  | <a href="http://power.ti.com">power.ti.com</a>                     |
| Microcontrollers            | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a> |
| RFID                        | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>               |
| RF/IF and ZigBee® Solutions | <a href="http://www.ti.com/lprf">www.ti.com/lprf</a>               |

### Applications

|                    |                                                                          |
|--------------------|--------------------------------------------------------------------------|
| Audio              | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                   |
| Automotive         | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>         |
| Broadband          | <a href="http://www.ti.com/broadband">www.ti.com/broadband</a>           |
| Digital Control    | <a href="http://www.ti.com/digitalcontrol">www.ti.com/digitalcontrol</a> |
| Medical            | <a href="http://www.ti.com/medical">www.ti.com/medical</a>               |
| Military           | <a href="http://www.ti.com/military">www.ti.com/military</a>             |
| Optical Networking | <a href="http://www.ti.com/opticalnetwork">www.ti.com/opticalnetwork</a> |
| Security           | <a href="http://www.ti.com/security">www.ti.com/security</a>             |
| Telephony          | <a href="http://www.ti.com/telephony">www.ti.com/telephony</a>           |
| Video & Imaging    | <a href="http://www.ti.com/video">www.ti.com/video</a>                   |
| Wireless           | <a href="http://www.ti.com/wireless">www.ti.com/wireless</a>             |

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2009, Texas Instruments Incorporated