



Float Switch - Stainless Steel

Vertical



Float Switch - Stainless Steel

Vertical



Parameter @25°C	Symbol	Value			Unit
		Minimum	Type	Maximum	

Electrical Characteristics

Contact Form	-		A		
Contact Rating	P _S			10/10	W/VA
Switching Voltage	U _S			200/140	VDC/VAC
Breakdown Voltage	U _{bd}	250			VDC
Switching Current	I _S			500	mA
Carry Current	I _C			1000	mA
Resistance	R _{ges}			100	mΩ

Environmental Characteristics

Operating Temperature	T _{op}	-40		+125	°C
Storage Temperature	T _{stg}				

Mechanical Characteristics

Average Density	δ _m		0.67		g/cm ³
Housing Material	V2A 304				
Cable	AWG 24				

Part Number Table

Description	Part Number
Float Switch, NO, S/Steel	MCPLS-045A-3VAI

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2009.