


Conformity to RoHS Directive

SHAPES AND DIMENSIONS




Unbalanced impedance	50Ω	
Balanced impedance	50Ω	
Frequency range	2400 to 2500MHz	
Unbalanced port return loss	10dB min.	
Phase imbalance at balanced port	180±10deg.	
Amplitude imbalance at balanced port	0±2.0dB	
Insertion loss	1.0dB max.	
Temperature range	Operating	−40 to +85°C
	Storage	−40 to +85°C

- 001-01 / 20130901 / rf balun hhm1902a1 en.


FREQUENCY CHARACTERISTICS

Unbalance 50Ω/Balance 50Ω


RETURN LOSS



AMPLITUDE BALANCE



INSERTION LOSS



PHASE BALANCE

