

Customer Information Sheet

DRAWING No.: D6XXX-XX SHEET 2 OF 2 IF IN DOUBT - ASK (C) NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm

PART No.	No. OF CONTACTS	No. OF CENTRE BARS	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'
D6206-XX	6	0	7.62	5.08	10.16	7.62
D6208-XX	8	0	10.16	7.62	10.16	7.62
D6214-XX	14	0	17.78	15.24	10.16	7.62
D6216-XX	16	0	20.32	17.78	10.16	7.62
D6218-XX	18	0	22.86	20.32	10.16	7.62
D6220-XX	20	1	25.40	22.86	10.16	7.62
D6222-XX	22	1	27.94	25.40	12.70	10.16
D6224-XX	24	1	30.48	27.94	17.78	15.24
D6228-XX	28	1	35.62	33.02	17.78	15.24
D6232-XX	32	1	40.64	38.10	17.78	15.24
D6240-XX	40	2	50.80	48.26	17.78	15.24
D6248-XX	48	2	60.96	58.42	25.28	22.86
D6264-XX	64	2	81.28	78.74	25.28	22.86
D6724-XX	24	1	30.48	27.94	12.70	10.16
D6922-XX	22	1	27.94	25.40	10.16	7.62
D6924-XX	24	0	30.48	27.94	10.16	7.62
D6948-XX	48	2	60.96	58.42	17.78	15.24

SPECIFICATION:
MATERIAL:
MOULDING:
01 FINISH = GLASS-FILLED POLYESTER UL94V-0, BLACK
46 FINISH = HIGH TEMP. POLYAMIDE 46, UL94V-0, BLACK
CONTACTS = BRASS
FINISH:
CONTACTS = 3.5-5.0µ 100% TIN OVER 2µ NICKEL
ELECTRICAL:
CURRENT RATING AT 25°C = 1.5A
CURRENT RATING AT 85°C = 0.25A
CONTACT RESISTANCE (INITIAL) = 15 mΩ MAX
CONTACT RESISTANCE (AFTER CONDITIONING) = 23 mΩ MAX
INSULATION RESISTANCE (INITIAL) = 1,000 MΩ MIN
INSULATION RESISTANCE (AFTER CONDITIONING) = 100 MΩ MIN
ENVIRONMENTAL:
TEMPERATURE RANGE = -55°C TO +125°C
PACKING:
TUBE
FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C004XX (LATEST ISSUE)

NOTES:
1. RECOMMENDED PCB HOLE SIZE = Ø0.80mm MIN.

ORDER CODE:





D6XXX-XX

PITCH CODE
SEE TABLE

TOTAL No. OF CONTACTS

FINISH:
01 = 100% TIN
46 = 100% TIN (HIGH TEMP MOULD)

ILLUSTRATION OF NUMBER OF CENTRE BARS (SEE TABLE)



JMB	9	07.12.05	8905
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>[Signature]</i>			
CHECKED: <i>[Signature]</i>			
DRAWN: D. FAIRS			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN INC
U.S.A.
TEL: (812) 542 2540
FAX: (812) 542 2541

HARWIN PLC
U.K.
TEL: 023 9231 4545
FAX: 023 9231 4590

HARWIN PTE
SINGAPORE
TEL: 65 6779 4909
FAX: 65 6779 3868

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
DIL I.C. SLOTTED
HEADER ASSEMBLY
DRAWING NUMBER:
D6XXX-XX

SHT
2
OF
2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[D6206-46](#) [D6208-46](#) [D6214-46](#) [D6216-46](#) [D6218-46](#) [D6220-46](#) [D6222-46](#) [D6224-46](#) [D6228-46](#) [D6232-46](#)
[D6240-46](#) [D6248-46](#) [D6264-46](#) [D6724-46](#) [D6924-46](#) [D6218-01](#) [D6924-01](#) [D6228-01](#) [D6216-01](#) [D6208-01](#) [D6724-](#)
[01](#) [D6240-01](#) [D6264-01](#) [D6220-01](#) [D6248-01](#) [D6214-01](#) [D6224-01](#) [D6232-01](#) [D6206-01](#) [D6222-01](#)