


Fully Sealed Container 12 mm Square or Round Cermet Trimmer



The Vishay SFERNICE trimming potentiometers T12 and T13 fully meet the requirements of CECC 41 100.

The use of a cermet track combined with sealing of the case provides unique characteristics and performances.

T12 and T13 have been specially designed for mounting on printed circuit board.





FEATURES




- Military and professional grade
- High power rating (1 W at 70 °C)
- Tests according to CECC 41000 or IEC 60393-1
- High stability (1 % typical)
- Mechanical strength
- Hermetic sealing of the case
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

DIMENSIONS in millimeters (± 0.5 mm)

T12X - PM06X		T13Y							
									
		TERMINAL SPACING ON THE PCB Drilling Diameter: 1.2 mm <table border="1"> <tr> <td>T12X</td> <td>T12Y</td> </tr> <tr> <td>10.16</td> <td>10.16</td> </tr> <tr> <td>a 5.08 b 5.08</td> <td>c 5.08 b 5.08</td> </tr> </table>		T12X	T12Y	10.16	10.16	a 5.08 b 5.08	c 5.08 b 5.08
T12X	T12Y								
10.16	10.16								
a 5.08 b 5.08	c 5.08 b 5.08								
LOCKING DEVICE: T12XB-YB 									

ELECTRICAL SPECIFICATIONS					
Resistive element	Cermet				
Electrical travel	$270^\circ \pm 10^\circ$				
Resistance range	22Ω to $10 M\Omega$				
Standard series E3	1 - 2.2 - 4.7 and on request 1 - 2 - 5				
Tolerance	<table border="1"> <tr> <td>standard</td><td>$\pm 20\%$</td></tr> <tr> <td>on request</td><td>$\pm 10\%, \pm 5\%$</td></tr> </table>	standard	$\pm 20\%$	on request	$\pm 10\%, \pm 5\%$
standard	$\pm 20\%$				
on request	$\pm 10\%, \pm 5\%$				
Power rating	<table border="1"> <tr> <td>linear</td><td>1 W at 70°C</td></tr> <tr> <td>logarithmic</td><td>0.5 W at 70°C</td></tr> </table>	linear	1 W at 70°C	logarithmic	0.5 W at 70°C
linear	1 W at 70°C				
logarithmic	0.5 W at 70°C				
Power rating chart					
Circuit diagram					
Resistance laws					
Temperature coefficient	See Standard Resistance Element Table				
Limiting element voltage (linear law)	350 V				
Contact resistance variation	3 % R_n or 3Ω				
End resistance (typical)	1 Ω				
Dielectric strength (RMS)	1000 V				
Insulation resistance (500 V _{DC})	$10^6 M\Omega$				

MECHANICAL SPECIFICATIONS	
Mechanical travel	300° ± 5°
Operating torque (max. Ncm)	3
End stop torque (max. Ncm)	15
Unit weight (max. g)	4.7
Terminals	Pure Sn (code e3)

ENVIRONMENTAL SPECIFICATIONS	
Temperature range	-55 °C to +125 °C
Climatic category	55/100/56
Sealing	IP67 Fully sealed

PERFORMANCES		TYPICAL VALUES AND DRIFTS	
TESTS	CONDITIONS	$\Delta R_T/R_T$ (%)	$\Delta R_{1-2}/R_{1-2}$ (%)
Load life	1000 h at rated power 90'/30' - ambient temperature 70 °C	± 1 % Contact res. variation: < 2 % Rn	± 2 %
Climatic sequence	Phase A dry heat 100 °C Phase B damp heat Phase C cold -55 °C Phase D damp heat 5 cycles	± 0.5 %	± 1 %
Long term damp heat	56 days 40 °C, 93 % RH	± 0.5 % Dielectric strength: 1000 V _{RMS} Insulation resistance: > 10 ⁴ MΩ	± 1 %
Rapid temperature change	5 cycles -55 °C to +125 °C	± 0.5 %	$\Delta V_{1-2}/\Delta V_{1-3}$ ≤ ± 1 %
Shock	50 g at 11 ms 3 successive shocks in 3 directions	± 0.1 %	± 0.5 %
Vibration	10 Hz to 55 Hz 0.75 mm or 10 g during 6 h	± 0.1 %	$\Delta V_{1-2}/\Delta V_{1-3}$ ≤ ± 0.5 %
Rotational life	200 cycles	± 1 % Contact res. variation: < 2 % Rn	

Note

- Nothing stated herein shall be construed as a guarantee of quality or durability.

STANDARD RESISTANCE ELEMENT DATA							
STANDARD RESISTANCE VALUES	LINEAR LAW			LOG LAWS			TYPICAL TCR -55 °C to +125 °C
	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CURRENT THROUGH WIPER	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CURRENT THROUGH WIPER	
Ω	W	V	mA	W	V	mA	ppm/°C
22	1	4.69	213.2				± 100
47	1	6.85	145.8				
100	1	10	100				
220	1	14.8	67.4				
470	1	21.6	46.1				
1K	1	31.6	31.6	0.5	22.4	22.4	
2.2K	1	46.9	21.3	0.5	33.2	15.1	
4.7K	1	68.5	14.5	0.5	48.5	10.3	
10K	1	100	10	0.5	79.7	7.07	
22K	1	148.3	6.7	0.5	105	4.77	
47K	1	216.7	4.6	0.5	153	3.26	
100K	1	316.2	3.16	0.5	224	2.24	
220K	0.56	350	1.59	0.5	332	1.51	
470K	0.26	350	0.75	0.26	350	0.74	
1M	0.12	350	0.35	0.12	350	0.35	
2.2M	0.05	350	0.16				
4.7M	0.02	350	0.07				
10M	0.01	350	0.03				

MARKING
<ul style="list-style-type: none"> Vishay trademark Model Ohmic value (in Ω, $k\Omega$, $M\Omega$) Tolerance (in %) Manufacturing date Marking of terminal: 1, 2, 3

PACKAGING
<ul style="list-style-type: none"> For T13Y: In plastic box of 50 pieces, code B25 (BL50) For T12Y, T12X: In carton box of 50 pieces, code B25 (BO50)

ORDERING INFORMATION FOR T12 (part number)

T	1	2	X	B	2	2	3	M	A	B	2	5			
MODEL	STYLE		OPTION		OHMIC VALUE			TOLERANCE		TAPER		PACKAGING CODE		SPECIAL NUMBER	
T12	X Y		B = Locking shaft 0 = Without		From 22 Ω to 10 M Ω 103 = 10 k Ω			M = 20 % On request: K = 10 % J = 5 %		A L F		B25 = Box 50 pieces		(If applicable) Given by Vishay for custom design	

DESCRIPTION (for information only)

T12	X	B	22K	20 %	A		BO			e3
MODEL	STYLE	SPECIAL	VALUE	TOLERANCE	TAPER	SPECIAL	PACKAGING	SPECIAL	SHAFT	LEAD FINISH

ORDERING INFORMATION FOR T13 (part number)

T	1	3	Y	1	0	5	M	A	B	2	5			
MODEL	STYLE		OHMIC VALUE		TOLERANCE		TAPER		PACKAGING CODE		SPECIAL NUMBER			
T13	Y		From 22 Ω to 10 M Ω 103 = 10 k Ω		M = 20 % On request: K = 10 %		A L F		B25 = Box 50 pieces		(If applicable) Given by Vishay for custom design			

DESCRIPTION (for information only)

T13	Y	1M	20 %	A		BL50	e3
MODEL	STYLE	VALUE	TOLERANCE	TAPER	SPECIAL	PACKAGING	LEAD FINISH

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.