

samtec



(1,27 mm) .050"

TFSDT-05-30-G-05.00-D-NUS

TFSD-15-30-G-05.00-D-NUS

TFSS-07-30-G-05.00-D-NUS

TFSS, TFSST, TFSD, TFSDT SERIES

TIGER EYE™ DISCRETE CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications see www.samtec.com?TFSS, www.samtec.com?TFSD, www.samtec.com?TFSDT, or www.samtec.com?TFSST

Insulator Material:

Black LCP

Contact Material:

BeCu

Plating:

Au over 50µ" (1,27 µm) Ni

Operating Temp Range:

-10°C to +80°C (PVC)

-40°C to +125°C (*Teflon®)

Wire:

28 or 30 AWG

RoHS Compliant:

Yes

Mates with:

SFM, SFC (-TR requires

TFM-WT option),

SFML (-XL end option

required)

Single or
Double
Ended28 or 30
AWG(1,27 mm)
.050"
pitch

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

TYPE STRIP

TFSS

= Single Row PVC Cable

TFSST

= Single Row *Teflon® Cable

TFSD

= Double Row PVC Cable

TFSDT

= Double Row *Teflon® Cable

POSITIONS PER ROW

-03, -04,
-05, -07,
-10, -15,
-20, -25,
-40, -50
(Standard sizes)

WIRE GAUGE

-30
= 30 AWG
-28
= 28 AWG

PLATING OPTION

-G
= 10µ" (0,25 µm)
Gold on contact

ASSEMBLED LENGTH

"XX.XX"
= Assembled Length in Inches (76,20 mm)
03.00" min. for -S end option
(82,60 mm)
03.25" min. for -D end option

END OPTION

-S
= Single Ended
-D
= Double Ended
-T
= Transfer End Terminal on End 1 Socket on End 2 (See chart for End 2 option)

-TF*
= Transfer End with Friction Lock

-TR
= Transfer End with Retention Latch (TFM -WT option required for mating)

*-05 & -07 positions not available. TFSD, TFSDT only

END 2 OPTION

Requires -D, -TF or -TR (End 1 Notch Down).


-NUS
= Notch up, straight (Pin 1 to Pin 2)

-NDS
= Notch down, straight (Pin 1 to Pin N-1)

-NUS
= Notch up, crossed (Pin 1 to Pin 1) (TFSD/TFSDT only)

-NDX
= Notch down, crossed (Pin 1 to Pin N) (TFSD/TFSDT only)

END 2	END OPTION
T-NUS	Pin 1 to Pin N
T-NDS	Pin 1 to Pin 1
T-NUS	Pin 1 and Pin N-1
T-NDX	Pin 1 to Pin 2



ALSO AVAILABLE (MOQ Required)

- Color coded cable (*Teflon® N/A)
- Other plating options
- Contact Samtec.

*DuPont™ Teflon® is a registered trademark of the E.I. du Pont de Nemours and Company or its affiliates.

Note: For wiring option and pin position location information, refer to drawings on web.

Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685