




| LOC | DIST | REVISIONS |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
| H   | —    | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
|     |      |           | N   | REVISED PER ECO-11-008643 | 26MAR11 | RC  | CW   |
|     |      |           | P   | ECO-11-024491             | 13DEC11 | SY  | MQW  |



SECTION A-A


SECTION B-B



NOTES:

- ① MATERIAL CONTACT: PHOSPHORBRONZE  
MATERIAL HOUSING: GLASSFILLED POLYESTER  
UL-RATING 94V0(GRAY)
- ② GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27μm  
NICKEL MIN.AND ACTION PIN: 0,5μm TIN-LEAD MIN.  
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE  
FOR EACH DASH NUMBER.
- ③ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE  
LEVEL 2.
- ④ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE  
LEVEL 1.
- ⑤ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE  
QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- ⑥ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE  
QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.
- ⑦ CONNECTOR LUBRICATED WITH TELCORDIA APPROVED LUBRICANT.
- ⑧ CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE.
- ⑨ PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID (110 HOLES).
- ⑩ HOLES IN ROW f AND z FOR POSSIBLE FUTURE USE OF  
GROUND RETURN SHIELD. (SHIELDS NOT YET TOOLED)
- ⑪ AREA RESERVED FOR KEYING PART (BASIC P.N.:100526).

SCALE 2,5:1




COMPONENT SIDE AS SHOWN  
RECOMMENDED PCB-HOLE LAY-OUT

P.C.B. HOLE DIM. ACTION PIN  
FOR DETAILS SEE  
APPLICATION SPECIFICATION

- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 13 0.76µm MIN GOLG PLATING AT MATING SURFACES.

|                                                                                                                                                    |                                                                                                                                                                                                                                                                   |                                                                                       |                       |
|----------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-----------------------|
|  <div> <div>SUPERSEDED</div> <div>By 1-5106773-9</div> </div> |    |  | 3-106773-0            |
|                                                                                                                                                    |    |  | <del>1-106773-9</del> |
|                                                                                                                                                    |    |  | 106773-9              |
|                                                                                                                                                    |    |  | 106773-4              |
|                                                                                                                                                    |    |  | 106773-1              |
|                                                                                                                                                    | FINISH                                                                                                                                                                                                                                                            | MATERIAL                                                                              | PART NUMBER           |

|                                        |  |                                                                                                                                      |  |                                                                                                       |                    |
|----------------------------------------|--|--------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>L.V.D.HEIJDEN<br>CHK<br>D. TRUREN<br>14APR97<br>14APR97                                                                       |  |  TE Connectivity |                    |
| DIMENSIONS:<br>mm                      |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br> ±0.2 |  | NAME<br>F.V.KONINGSBRUGGE<br>PRODUCT SPEC<br>108-19082<br>APPLICATION SPEC<br>114-19029               |                    |
| MATERIAL<br>-                          |  | FINISH<br>-                                                                                                                          |  | SIZE<br>A2                                                                                            | CAGE CODE<br>00779 |
| CUSTOMER DRAWING                       |  |                                                                                                                                      |  | DRAWING NO<br>C-106773                                                                                | RESTRICTED TO<br>- |
|                                        |  |                                                                                                                                      |  | SCALE<br>NTS                                                                                          | SHEET<br>1 OF 1    |
|                                        |  |                                                                                                                                      |  | REV<br>P                                                                                              |                    |