


## High Current Low Profile Surface Mount Inductors



- Operating Temperature Range -40°C to +125°C
- Temperature Rise, Maximum 40°C
- Ambient Temperature, Maximum 80°C
- Insulation System Class F, 155°C

### Specifications

Part Number	Inductance 100kHz, 0.1 V			DCR <sup>(1)</sup>		I <sub>rated</sub> <sup>(2)</sup>	Heating Current <sup>(3)</sup>	Core Loss <sup>(4)</sup>	
	@ 0 Adc (nH±20%)	@ I <sub>rated</sub> (nH)		(mΩ)		@ 25 °C (Adc)		Factor	
	Typ.	Min.	Typ.	Typ.	Max.		(A)	K1	K2
HM69-10R025	25	18	25	0.27	0.33	42	22	3.847E-14	59.444
HM69-20R050	50	28	36	0.20	0.24	70	35	1.074E-13	50.117
HM69-30R070	70	50	67	0.40	0.48	46	25	1.074E-13	70.164
HM69-40R10	100	60	75	0.31	0.39	28	25	7.124E-14	156.891
HM69-50R10	100	72	95	0.40	0.48	29	24	8.733E-14	127.990
HM69-50R15	150	96	120	0.40	0.48	18	24	8.733E-14	191.986
HM69-55R10	100	64	80	0.45	0.56	45	25	1.337E-13	96.541
HM69-55R20	200	140	175	0.45	0.56	21	25	1.337E-13	160.902
HM69-60R10	100	69	87	0.42	0.50	68	31	2.311E-13	52.336
HM69-60R15	150	104	130	0.42	0.50	48	31	2.311E-13	78.503
HM69-60R20	200	144	180	0.42	0.50	31	31	2.311E-13	104.671
HM69-70R30	300	200	250	0.17	0.20	37	70	6.784E-13	98.921
HM69-75R20	200	150	175	0.40	0.50	20	40	3.559E-13	134.203
HM69-80R30	300	216	285	0.17	0.25	40	76	9.107E-13	72.674

- Notes:
- (1) DC resistance is measured at 25°C.
  - (2) The rated current (I<sub>rated</sub>) is the current at which the inductance will be decreased by 20% from its initial (zero DC) value.
  - (3) The heating current is the DC current, which causes the component temperature to increase by approximately 40°C. This current is determined by soldering the component on a typical application PCB, and then apply the device for 30 minutes.
  - (4) Core Loss approximation is based on published core data:  

$$\text{Core Loss} = K1 * (f)^{1.77} * (K2\Delta I)^{2.21}$$

Where: core loss in watt      f = switching frequency in kHz  
 K1 and K2 = core loss factor      ΔI = delta I across the component in Amp.  
 K2ΔI = one half of the peak to peak flux density across the component in Gauss

### Packaging

Standard: Embossed Tape & Reel

Reel:	Diameter:	=	13" (330.2mm)
	Capacity:	Case size 10,40	= 1000 Units
		Case size 20,30,60	= 800 Units
		Case size 50,55,75	= 500 Units
		Case size 70,80	= 350 Units

### Ordering Information


Model Series **HM69** **50** **R10** **LF** **TR** Tape & Reel Packing

Case Size

Inductance Code: First 2 digits are significant.  
Last digit denotes the number of trailing zeros.  
For values below 10μH, "R" denotes the decimal point.


Lead-Free Option  
LF = Lead-Free  
(No code used for non lead-free part)

## Outline Dimensions (mm)



Case size	A	B	C	D	E	F	G	H
10	6.00	5.00	3.00	1.50	1.50	1.60	2.50	7.20
20	7.50	6.50	5.00	1.50	2.95	3.00	2.40	8.00
30	7.00	7.00	5.00	2.50	2.30	2.50	1.00	7.00
40	7.01	6.35	3.30	1.50	2.85	3.20	2.50	7.50
50	8.60	6.30	3.30	1.50	2.85	3.20	2.50	9.00
55	8.60	6.30	4.80	1.50	2.85	3.20	2.50	9.00
60	10.2	7.00	5.10	1.00	2.50	2.80	5.50	10.5
70	13.5	13.0	6.80	1.00	5.00	5.30	5.50	13.5
75	13.5	13.0	3.50	2.00	2.50	3.20	7.00	13.5
80	13.8	13.0	8.20	2.00	5.00	5.30	5.50	13.8

## Electrical Characteristics @ 25 °C



**Electrical Characteristics @ 25 °C (Cont'd)**

