



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

NTE1600 Integrated Circuit VCR Direct Drive Motor Pre Driver

Features:

- Three Phase Control Signal Generation Circuit
- Phase, Speed Control
- Normal Rotation, Reverse Rotation Control

Absolute Maximum Ratings:

Supply Voltage, V_{CC} 14V
Power Dissipation ($T_A = +70^\circ\text{C}$), P_T 600mW
Operating Temperature Range, T_{opr} -20° to $+70^\circ\text{C}$
Storage Temperature Range, T_{stg} -55° to $+125^\circ\text{C}$

Electrical Characteristics: ($V_{CC} = 12\text{V}$, $T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Output Current						
U Phase	I_{U1}	Pin17	1.8	2.8	4.0	mA
V Phase	I_{V1}	Pin2	1.8	2.8	4.0	mA
W Phase	I_{W1}	Pin4	1.8	2.8	4.0	mA
Maximum Output Current						
U Phase	I_{U2}	Pin1	8.6	14.9	22.2	mA
V Phase	I_{V2}	Pin3	8.6	14.9	22.2	mA
W Phase	I_{W2}	Pin5	8.6	14.9	22.2	mA
Voltage Current Conversion Gain	g_2	–	40	80	160	mA/V
Interphase Current Dispersion	ΔI	I_{U1}/I_{V1} , I_{V1}/I_{W1} , I_{U1}/I_{W1}	–25	0	25	%
Closed Loop Gain	–	NTE1600 & NTE1554 Combination, $R_f = 1\Omega$	–	0.37	–	A/V
Three Phase Signal Input Level						
AC	$V_{H(AC)}$	U Phase: Pin16, Pin15	50	100	500	mV _{pp}
DC	$V_{H(DC)}$	V Phase: Pin14, Pin13	1.9	2.0	4.5	V
		W Phase: Pin12, Pin11				
Speed/Phase Control Input	V_{ID}	Pin8	0	4.5	9.0	V
Motor Normal Rotation	$V_{N/R-N}$	Pin6	1.5	3.0	9.0	V
Motor Reverse Rotation	$V_{N/R-R}$	Pin6	0	0	0.3	V

Pin Connection Diagram

