

	7	6	4	3	2	1																																																																																	
E							E																																																																																
D							D																																																																																
C	MATERIAL LIST: <table border="1"><thead><tr><th>NO.</th><th>PARTS NAME</th><th>SPECIFICATION DESCRIPTION</th></tr></thead><tbody><tr><td>①</td><td>CABLE</td><td>UL20276 4*(1P*28AWG+AL+D+T2D)+1P*28AWG+3C*28AWG +AL+D+B (60%) OD:7.3±0.2mm COLOR:BLACK</td></tr><tr><td>②</td><td>DVI CONNECTOR</td><td>DVI 18+1 MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL</td></tr><tr><td>③</td><td>HDMI CONNECTOR</td><td>HDMI 19P MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL</td></tr><tr><td>④</td><td>SCREW</td><td>Ø4*47mm NICKEL PLATED</td></tr><tr><td>⑤</td><td>MOLDING PVC</td><td>MOLDING PVC 063 45P COLOR:BLACK</td></tr><tr><td>⑥</td><td>MOLDING PVC</td><td>MOLDING PVC 063 30P COLOR:BLACK</td></tr></tbody></table>						NO.	PARTS NAME	SPECIFICATION DESCRIPTION	①	CABLE	UL20276 4*(1P*28AWG+AL+D+T2D)+1P*28AWG+3C*28AWG +AL+D+B (60%) OD:7.3±0.2mm COLOR:BLACK	②	DVI CONNECTOR	DVI 18+1 MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL	③	HDMI CONNECTOR	HDMI 19P MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL	④	SCREW	Ø4*47mm NICKEL PLATED	⑤	MOLDING PVC	MOLDING PVC 063 45P COLOR:BLACK	⑥	MOLDING PVC	MOLDING PVC 063 30P COLOR:BLACK	C																																																											
NO.	PARTS NAME	SPECIFICATION DESCRIPTION																																																																																					
①	CABLE	UL20276 4*(1P*28AWG+AL+D+T2D)+1P*28AWG+3C*28AWG +AL+D+B (60%) OD:7.3±0.2mm COLOR:BLACK																																																																																					
②	DVI CONNECTOR	DVI 18+1 MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL																																																																																					
③	HDMI CONNECTOR	HDMI 19P MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL																																																																																					
④	SCREW	Ø4*47mm NICKEL PLATED																																																																																					
⑤	MOLDING PVC	MOLDING PVC 063 45P COLOR:BLACK																																																																																					
⑥	MOLDING PVC	MOLDING PVC 063 30P COLOR:BLACK																																																																																					
B	Marking: Maxxtro STANDARD HDMI® CABLE AWM E200765 STYLE 20276 80°C 30V FT2 CONNECTION <table><thead><tr><th colspan="2">CN1</th><th colspan="2">CN2</th><th colspan="2">CN1</th><th colspan="2">CN2</th></tr></thead><tbody><tr><td>2</td><td>BROWN</td><td>1</td><td></td><td>23</td><td>RED</td><td>10</td><td></td></tr><tr><td>1</td><td>WHITE</td><td>3</td><td></td><td>24</td><td>WHITE</td><td>12</td><td></td></tr><tr><td>3</td><td>DRAIN</td><td>2</td><td></td><td>22</td><td>DRAIN</td><td>11</td><td></td></tr><tr><td>10</td><td>BLUE</td><td>4</td><td></td><td>6</td><td>WHITE</td><td>15</td><td></td></tr><tr><td>9</td><td>WHITE</td><td>6</td><td></td><td>7</td><td>VIOLET</td><td>16</td><td></td></tr><tr><td>11</td><td>DRAIN</td><td>5</td><td></td><td>15</td><td>YELLOW</td><td>17</td><td></td></tr><tr><td>18</td><td>GREEN</td><td>7</td><td></td><td>14</td><td>ORANGE</td><td>18</td><td></td></tr><tr><td>17</td><td>WHITE</td><td>9</td><td></td><td>16</td><td>RED</td><td>19</td><td></td></tr><tr><td>19</td><td>DRAIN</td><td>8</td><td></td><td>SHELL</td><td>BRAID</td><td>SHELL</td><td></td></tr></tbody></table>						CN1		CN2		CN1		CN2		2	BROWN	1		23	RED	10		1	WHITE	3		24	WHITE	12		3	DRAIN	2		22	DRAIN	11		10	BLUE	4		6	WHITE	15		9	WHITE	6		7	VIOLET	16		11	DRAIN	5		15	YELLOW	17		18	GREEN	7		14	ORANGE	18		17	WHITE	9		16	RED	19		19	DRAIN	8		SHELL	BRAID	SHELL		B
CN1		CN2		CN1		CN2																																																																																	
2	BROWN	1		23	RED	10																																																																																	
1	WHITE	3		24	WHITE	12																																																																																	
3	DRAIN	2		22	DRAIN	11																																																																																	
10	BLUE	4		6	WHITE	15																																																																																	
9	WHITE	6		7	VIOLET	16																																																																																	
11	DRAIN	5		15	YELLOW	17																																																																																	
18	GREEN	7		14	ORANGE	18																																																																																	
17	WHITE	9		16	RED	19																																																																																	
19	DRAIN	8		SHELL	BRAID	SHELL																																																																																	
A	<table border="1"><thead><tr><th>ITEM NO</th><th>LENGTH</th><th>PVC COLOR</th><th>PACKING</th></tr></thead><tbody><tr><td>101273</td><td>5000±75mm</td><td>BLACK 0020</td><td>BLISTER CARD</td></tr></tbody></table> ELECTRONIC TEST: A.OPEN/SHORT/INTERMITTENCE: 100%. B.HI-POT: 300V DC/sec C.INSULATION RESISTANCE: 10M ohm (MIN) D.CONDUCTIVE RESISTANCE: 5ohm (MAX)						ITEM NO	LENGTH	PVC COLOR	PACKING	101273	5000±75mm	BLACK 0020	BLISTER CARD	A																																																																								
ITEM NO	LENGTH	PVC COLOR	PACKING																																																																																				
101273	5000±75mm	BLACK 0020	BLISTER CARD																																																																																				
	7	6	5	4	3	2	1																																																																																