

HMM

TE Internal #: E94125-000

HMM, Standard Labels, Industrial Label, Die-Cut Label Style, High Tack Acrylic Adhesive, UL Listed Yes, Label Width 50.8 mm [2 in]

[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels > HMM HIGH TACK METALIZED POLYESTER LABELS



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **High Tack Acrylic Adhesive**

UL Listed: **Yes**

Label Width: **50.8 mm [2 in]**

All HMM HIGH TACK METALIZED POLYESTER LABELS (23)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Label Color	Matte Metalized Silver
-------------	------------------------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	1
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	50.8 mm[2 in]
Label Height	50.8 mm[2 in]
Label Material	Polyester
Label Thickness	107 Micron

Industry Standards

UL Listed	Yes
-----------	-----

Packaging Features



Packaging Quantity	3000
Packaging Method	Roll

Other

Label Adhesive Type	High Tack Acrylic Adhesive
---------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



Also in the Series | **HMM**

Standard Labels(23)

Customers Also Bought

TE Part #2040910-1
SEMI-HARD TRAY ASSY DDR 200P
VERTICAL

TE Part #1717478-1
REC. ASSEMBLY 8POS. 2.5MM PITCH
BATTERY

TE Part #1717478-2
REC. ASSEMBLY 8POS. 2.5MM PITCH
BATTERY

TE Part #1513472-1
UAM Assembly

TE Part #2176341-1
CRGCQ 0805 10R 1%

TE Part #2337230-3
TACT ULTRA TB 3.0X2.0X0.6 240GF

TE Part #C37234-000
HM-381191-5-8A

TE Part #1513472-5
UAM Assembly 360mm cable

PITCH BATTERY

Documents

Product Drawings

HMM-508508-3-8A

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

HMM-508508-3-8A

HMM, Standard Labels, Industrial Label, Die-Cut Label Style, High Tack Acrylic Adhesive, UL Listed Yes, Label Width 50.8 mm [2 in]



HMM High Tack Matte Metalized Polyester

English