

RF AMPLIFIER

MODEL TR9737

Available as: TR9737, 4 Pin TO-8 (T4)
 FP9737-4, 4 Pin Flatpack (FP4)
 BR9737, Connectrized Housing (H2)

Features

- GaAs FET Low Noise Figure: <4.5 dB Typical
- High Output Power: +24 dBm Typical
- Operating Temp. - 55 °C to +85 °C
- Environmental Screening Available

Specifications

CHARACTERISTIC	TYPICAL Ta= 25 °C	MIN/MAX Ta = -55 °C to +85 °C
Frequency	100 - 2000 MHz	200 - 2000 MHz
Gain (dB)	9.5	8.0 Min.
Power @ 1 dB Comp. (dBm)	+24	+22.0 Min.
Reverse Isolation (dB)	- 14	- 13 Max.
VSWR In	<1.75:1	2.0:1 Max.
VSWR Out	<1.75:1	2.0:1 Max.
Noise figure (dB)	<4.5	6.5 Max.
VSWR Vdc	+15	+15 Max.
mA	140	160 Max.

Note: Care should always be taken to effectively ground the case of each unit.


Typical Intermodulation Performance at 25 ° C

Second Order Harmonic Intercept Point +54(Typ.)
 Second Order Two Tone Intercept Point +49(Typ.)
 Third Order Two Tone Intercept Point +38(Typ.)

Maximum Ratings

Ambient Operating Temperature -55°C to + 100 °C
 Storage Temperature -62°C to + 125 °C
 Case Temperature + 125 °C
 DC Voltage + 18 Volts
 Continuous RF Input Power + 18 dBm
 Short Term RF Input Power 100 Milliwatts
 (1 Minute Max.)
 Maximum Peak Power.....0.5 Watt
 (3 µsec Max.)

Typical Performance Data



Legend ——— + 25 °C - - - + 85 °C -55 °C

Linear S-Parameters

FREQ. MHz	S11		S21		S12		S22	
	Mag	Deg	Mag	Deg	Mag	Deg	Mag	Deg
100	.24	179	2.97	171	.13	- 3	.26	163
200	.24	171	2.85	161	.13	- 7	.26	147
500	.20	154	2.83	132	.14	- 18	.24	101
1000	.08	133	3.01	84	.15	- 41	.24	24
1500	.09	-140	3.11	29	.16	- 69	.22	- 54
2000	.15	177	3.00	-34	.16	-106	.24	- 127

Amplifonix

2707 Black Lake Place, Philadelphia, PA 19154

TEL 215-464-4000 • • • • FAX 215-464-4001