



Search Results

- Evaluate
- FAQ's
- Design a Solution
- Part Drawings
 - PDFSimplex Fibe ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'F9F3-10M12Y'

Your search criteria matched only one product, shown below

F9F3-10M12Y



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR -326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Part Number	F9F3-10M12Y
RoHS Compliancy Status	Intended for use in fixed installations which are outside the scope of RoHS
Note	F9F3-10M12Y replaces F9F3-10M12
Part Description	SC to LC singlemode simplex patch cord, 1.6mm jacketed cable (one SC connector on one end and one LC connector on the other end)– 9/125 μ m.
Product Type	Hybrid Patch Cords
Length (m)	12
Fiber Compatibility	9/125 μ m
Fiber Cable Size	1.6mm
Fiber Cable Type	Jacketed
Fiber Type	Singlemode
Connector 1 Type	SC Connector
Connector 2 Type	LC Connector
End Configurations	SC to LC
Fiber Count	1
Flammability Rating	Riser (OFNR)
Pricing Description	9 μ m Simpl SGLC 1.6mm Patch Cord 12m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.