



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		H	REVISED PER E.O. P17744	11DEC2002	-	RDR
			J	REVISED PER E.O. P19419	11DEC2006	-	RDR
			K	REVISED PER E.O. P21366	4JUN2012	-	RDR
			K1	REVISED PER ECO-14-002953	29JAN2014	PV	DM



3-D VIEW




6. MATERIAL:
RECEPTACLE HOUSING AND WELD RING: PA 15%GF (GREY)
GROMMET: SILICONE (RED)
5. OVERALL DIMENSION DOES NOT INCLUDE RUBBER GROMMET.
4. THIS RECEPTACLE MATES WITH FOLLOWING PLUG (X= SEAL TYPE, XXXX= ALL MODIFICATIONS).
HD16-6-96SX-XXXX
3. SEE DRAWING 0425-015-0000 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS.
2. MAXIMUM PANEL THICKNESS IS .250 [6.35].

1. SEE TABLE FOR USABLE WIRE RANGE AND INSULATION RANGE.

CONTACT SIZE	MINIMUM O.D.	MAXIMUM O.D.	WIRE RANGE [mm ²]
16	.100 [2.54]	.150 [3.81]	14-20 AWG [2.0-.50]

NOTES:



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. OCHOA 18SEP1998		 TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK I. GRANTCHAROVA 16SEP2013			
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 4 PLC ± ANGLES ±0° 30'0		NAME RECEPTACLE CONNECTOR SQUARE FLANGE HD10 SERIES ARR. 6-96 COLOUR: GREY	
		APVD D. MEYER 18SEP2013			
MATERIAL 		PRODUCT SPEC -		SIZE	
		APPLICATION SPEC -		CAGE CODE	
		WEIGHT 34.55 (g)		DRAWING NO	
		Customer Drawing		RESTRICTED TO -	
				A200779 C=HD10-6-96P	
				SCALE 2:1	
				SHEET 1 OF 1	
				REV K1	