



Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

MC78L09BP

Features

- Internal Short Circuit Current Limiting
- Internal Thermal Overload Protection
- No External Components Required


Maximum Ratings

Parameter	Symbol	Value	Unit
Input Voltage	V_1	30	V
Operating Junction Temperature	T_{OPR}	-20---+120	°C
Storage Temperature Range	T_{STG}	-55---+150	°C

Electrical Characteristics($V_1=15V$, $I_o=40mA$, $0^\circ C < T_j < 125^\circ C$,
 $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified)


Parameter	Sym	Min	Typ	Max	Test conditions
Output Voltage	V_o	8.64V	9.0V	9.36V	$T_j=25^\circ C$
		8.55V		9.45V	$11.5V \leq V_1 \leq 24V$, $I_o=1mA-40mA$
		8.55V		9.45V	$11.5V \leq V_1 \leq V_{MAX}$, $I_o=1mA-70mA$ (Note)
Load Regulation	ΔV_o		20mV	90mV	$I_o=1mA-100mA$, $T_j=25^\circ C$,
			10mV	45mV	$I_o=1mA-40mA$, $T_j=25^\circ C$,
Line regulation	ΔV_o		90mV 100mV	200mV 150mV	$11.5V \leq V_1 \leq 24V$, $T_j=25^\circ C$ $13V \leq V_1 \leq 24V$, $T_j=25^\circ C$
Quiescent Current	I_q		2.0mA	6.0mA	$13V \leq V_1 \leq 24V$
	ΔI_q			1.5mA	
Quiescent Current Change	ΔI_q			0.1mA	$1mA \leq I_o \leq 40mA$
Output Noise Voltage	V_N		49uV		$10Hz \leq f \leq 100KHz$
Ripple Rejection	RR		38dB	44dB	$12V \leq V_1 \leq 23V$ $f=120Hz$, $T_j=25^\circ C$
Dropout Voltage	V_d		1.7V		$T_j=25^\circ C$

*Note: Bypass Capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators
Typical Application:



Three-Terminal Low Current Positive Voltage Regulator

TO-92



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
	A	.175	.185	4.45	
B	.175	.185	4.46	4.70	
C	.500	---	12.7	---	
D	.016	.020	0.41	0.63	
E	.135	.145	3.43	3.68	
G	.095	.105	2.42	2.67	