




LOC		DIST		REVISIONS			
AA		22		DESCRIPTION	DATE	DWN	APVD
		B2		REVISED PER ECO-11-005033	31MAR11	RK	HMR

- MATERIAL:
HOUSING — PCT POLYESTER, BLACK, UL94V-0.
OVERMOLDED TERMINAL ARRAY — PBT, BROWN.
TERMINALS — 0.33 [0.013] THICK PHOS BRONZE PLATED WITH 1.27um [0.00050] MIN THICK HARD GOLD IN LOCALIZED AREA AND 3.81um [0.00150] MIN THICK MATTE TIN IN SOLDER AREA OVER 1.27um [0.00050] MIN THICK NICKEL UNDERPLATE.
SHIELDS — 0.25 [0.010] THICK COPPER ALLOY PLATED WITH 1.27 um [0.00050] MINIMUM NICKEL AND 2.03 um [0.00080] MINIMUM HOT TIN DIP ON PCB GROUND TABS.
- JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
- DATE CODE LOCATED ON REAR OF PART APPROXIMATELY AS SHOWN:
FIRST 2 DIGITS ARE LAST 2 DIGITS OF YEAR,
SECOND 2 DIGITS ARE MANUFACTURING WORK WEEK,
LAST DIGIT IS DAY OF WEEK, WITH SUNDAY = 1.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SPRINKLE/L.A. MAYER 25MAY2005		5569264-1 PART NUMBER	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± 0.25[.05] 3. PLC ± 0.13[.005] 4. PLC ± - ANGLES ± -		TE Connectivity	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		CUSTOMER DRAWING	
SCALE 4:1		SHEET 1 of 1		REV B2	