






PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL


PC BOARD VERSIONS		
PRODUCT NR:	PCB THICKNESS	DIM A
85863-X02/X02LF	1.6	2.90
85863-X12/X12LF	2.4	3.53

LOADING CONFIGURATION
FULLY LOADED

* SPECIFY LOADING P/N SEE PAGE 2



- NOTES:
- BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - INDICATED HOLES ARE UNPLATED.
 - PLATING SOLDER TAILS 2-8 μ m SnPb 90-97 OR 2-8 μ m PURE Sn
 - PRODUCT MARKING: PART NUMBER & BATCH ID.
 - SET BACK FOR TAIL BLOCK
 - TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD.
 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS	
ltr	ecr no	dr	date	linear	projection	title	www.fciconnect.com
H	06-012848	06/09/06/12				5 ROW R.A. S.T.B. SIGNAL RECEPT. 12 mm MOD.PP	
D	0604-0104	Clu	041222	dr	R. VISSCHERS	941005	
E	0607-0169	Cent	05/15/07	engr	E. FEIJEN	941005	
F	0608-0171	TER	8/26/08	chr	E. FEIJEN	941005	
G	0609-0068	Cent	06/06/08	app	E. FEIJEN	941005	
sheet	revision	H	H		scale	5:1	
index	sheet	1	2		size	A2	
						85863	
						213	
						1 of 2	

This data is classified as "unclassified" information. Reproduction or dissemination of this data is prohibited without written authority from the originator. Property of FCI Inc.

All rights are reserved. Reproduction or use in any form is prohibited without written authority from the originator. Property of FCI Inc.

PRODUCT NO	PCB THICKNESS	DIM "A"	ROW	6	5	4	3	2	1
85863-X03 85863-X03LF	1.6	2.90	E	X	X	X	-	X	X
			D	X	X	X	-	X	X
			C	X	X	X	X	-	-
			B	X	X	X	-	X	X
			A	X	X	X	-	X	X

LOAD PATTERN	
X	LOADED
-	NOT LOADED

mat'l. code SEE NOTE				tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS www.fciconnect.com	
ltr	ecr	no	dr	date	linear	projection	title	5 ROW R.A. S.T.B. SIGNAL RECEPT. 12 mm MOD.PP	
H					angles	mm	product family		
					dr	R. VISSCHERS 941005	size	METRAL (tm)	code
					engr	E. FEIJEN 941005	dwg no	213	
					chr	E. FEIJEN 941005	scale	2 of 2	
					app	E. FEIJEN 941005	5:1	85863	
sheet	revision								
index	sheet								