

ULTRA FAST RECOVERY RECTIFIER DIODES



Glass-passivated, high-efficiency epitaxial rectifier diodes in DO-4 metal envelopes, featuring low forward voltage drop, ultra fast reverse recovery times, very low stored charge and soft recovery characteristic. They are intended for use in switched-mode power supplies and high-frequency circuits in general, where low conduction and switching losses are essential. The series consists of normal polarity (cathode to stud) types.


QUICK REFERENCE DATA

		BYW30-50					
			100	150	200		
Repetitive peak reverse voltage	V_{RRM}	max.	50	100	150	200	V
Average forward current	$I_{F(AV)}$	max.	14				A
Forward voltage	V_F	<	0.8				V
Reverse recovery time	t_{rr}	<	30				ns

MECHANICAL DATA

Dimensions in mm

Fig.1 DO-4: with metric M5 stud ($\phi 5$ mm); e.g. BYW30-50.
with 10-32 UNF stud ($\phi 4.83$ mm); e.g. BYW30-50U.



Net mass: 6 g

Diameter of clearance hole: max. 5.2 mm

Accessories supplied on request:
see ACCESSORIES section.

Supplied with device: 1 nut, 1 lock washer

Torque on nut: min. 0.9 Nm (9 kg cm)
max. 1.7 Nm (17 kg cm)

Nut dimensions across the flats:
M5: 8.0 mm; 10-32 UNF: 9.5 mm.



Products approved to CECC 50 009-001, available on request.

RATINGS

T-03-17

Limiting values in accordance with the Absolute Maximum System (IEC 134)

Voltages*

		BYW30-50	100	150	200	
Repetitive peak reverse voltage	V_{RRM}	max. 50	100	150	200	V
Crest working reverse voltage	V_{RWM}	max. 50	100	150	200	V
Continuous reverse voltage	V_R	max. 50	100	150	200	V

Currents

Average forward current; switching

losses negligible up to 500 kHz

square wave; $\delta = 0.5$; up to $T_{mb} = 120^\circ\text{C}$ up to $T_{mb} = 125^\circ\text{C}$ sinusoidal; up to $T_{mb} = 125^\circ\text{C}$

R.M.S. forward current

Repetitive peak forward current

 $t_p = 20 \mu\text{s}$; $\delta = 0.02$

Non-repetitive peak forward current

half sine-wave; $T_j = 150^\circ\text{C}$ prior to surge;with reapplied $V_{RWM\text{max}}$; $t = 10 \text{ ms}$ $t = 8.3 \text{ ms}$ $I^2 t$ for fusing ($t = 10 \text{ ms}$)

$I_F(\text{AV})$	max.	14	A
$I_F(\text{AV})$	max.	12	A
$I_F(\text{AV})$	max.	12.5	A
$I_F(\text{RMS})$	max.	20	A
I_{FRM}	max.	420	A
I_{FSM}	max.	200	A
I_{FSM}	max.	240	A
$I^2 t$	max.	200	A^2s

Temperatures

Storage temperature

Junction temperature

T_{stg}	-55 to +150	$^\circ\text{C}$
T_j	max. 150	$^\circ\text{C}$

THERMAL RESISTANCE

From junction to mounting base

From mounting base to heatsink

a. with heatsink compound

b. without heatsink compound

Transient thermal impedance; $t = 1 \text{ ms}$

$R_{th j-mb}$	=	2.2	K/W
$R_{th mb-h}$	=	0.5	K/W
$R_{th mb-h}$	=	0.6	K/W
$Z_{th j-mb}$	=	0.3	K/W

MOUNTING INSTRUCTIONS

The top connector should be neither bent nor twisted; it should be soldered into the circuit so that there is no strain on it.

During soldering the heat conduction to the junction should be kept to a minimum.

*To ensure thermal stability: $R_{th j-a} \leq 5.6 \text{ K/W}$ (continuous reverse voltage).

PHILIPS INTERNATIONAL

56E D ■ 7110826 0041566 807 ■ PHIN

CHARACTERISTICS

T-03-17

Forward voltage

$I_F = 15 \text{ A}; T_j = 150^\circ\text{C}$

$I_F = 50 \text{ A}; T_j = 25^\circ\text{C}$

V_F	<	0.8	V*
V_F	<	1.3	V*

Reverse current

$V_R = V_{RWM \text{ max}}; T_j = 100^\circ\text{C}$

$T_j = 25^\circ\text{C}$

I_R	<	1.3	mA
I_R	<	25	μA ←

Reverse recovery when switched from

$I_F = 1 \text{ A to } V_R \geq 30 \text{ V with } -dI_F/dt = 100 \text{ A}/\mu\text{s};$

$T_j = 25^\circ\text{C}; \text{ recovery time}$

t_{rr}	<	30	ns
----------	---	----	----

$I_F = 2 \text{ A to } V_R \geq 30 \text{ V with } -dI_F/dt = 20 \text{ A}/\mu\text{s};$

$T_j = 25^\circ\text{C}; \text{ recovered charge}$

Q_s	<	15	nC
-------	---	----	----

$I_F = 10 \text{ A to } V_R \geq 30 \text{ V with } -dI_F/dt = 50 \text{ A}/\mu\text{s};$

$T_j = 100^\circ\text{C}; \text{ peak recovery current}$



I_{RRM}	<	4	A
-----------	---	---	---

Forward recovery when switched to $I_F = 10 \text{ A}$

$\text{with } dI_F/dt = 10 \text{ A}/\mu\text{s}; T_j = 25^\circ\text{C}$

V_{fr}	typ.	1.0	V
----------	------	-----	---

M80 1519 3

Fig.2 Definition of t_{rr} , Q_s and I_{RRM} .Fig.3 Definition of V_{fr} .

*Measured under pulse conditions to avoid excessive dissipation.

SQUARE-WAVE OPERATION




Fig.4 The right-hand part shows the interrelationship between the power (derived from the left-hand part) and the maximum permissible temperatures. Power includes reverse current losses and switching losses up to $f = 500$ kHz.

$$\delta = \frac{t_p}{T}$$

$$I_{F(AV)} = I_{F(RMS)} \times \sqrt{\delta}$$

* T_{mb} scale is for comparison purposes and is correct only for $R_{th\ mb-a} < 3.1$ K/W.

SINUSOIDAL OPERATION

T-03-17




Fig.5 The right-hand part shows the interrelationship between the power (derived from the left-hand part) and the maximum permissible temperatures.

a = form factor = $I_F(RMS)/I_F(AV)$.

* T_{mb} scale is for comparison purposes and is correct only for $R_{th\ mb-a} < 17$ K/W.




Fig.6 Maximum permissible repetitive peak forward current for square or sinusoidal currents; $\mu s < t_p < 1$ ms.








Fig.7 — $T_j = 25^\circ C$; --- $T_j = 150^\circ C$.

PHILIPS INTERNATIONAL

56E D

7110826 0041570 238 PHIN

Fig.8 Maximum t_{rr} at $T_j = 25^\circ\text{C}$.Fig.9 Maximum t_{rr} at $T_j = 100^\circ\text{C}$.Fig.10 Maximum Q_s at $T_j = 25^\circ\text{C}$.

