

LOC	DIST	REVISIONS			
H	-	LTR	DESCRIPTION	DATE	APVD
		F1	REVISED PER ECO-11-005294	27APR11	HMR

1 CONSTRUCTION

1.1 Conductor:

- 1.1.1 Construction: Stranded 7x0.127 mm copper tin plated
- 1.1.2 Cross-section: 28AWG (0.089 mm²)
- 1.1.3 Diam.: 0.39 mm

1.2 Insulation:

- 1.2.1 Material: PVC 105°C
- 1.2.2 Insulation thickness: nom. 0.25 mm
- 1.2.3 Diam.: 0.93 mm
- 1.2.4 Pitch: 1.27 (see Table 1)
- 1.2.5 Colour: Gray RAL7032
- Conductor #1 Red
- 1.2.6 Shore hardness: 94

2. Electrical requirements:

- 2.1 DC Resistance: 216 Ohm/km at 20°C
- 2.2 Insulation Resistance: 100 MOhm x km at 20°C
- 2.3 Max Operating Voltage: 300V at 50Hz
- 2.4 Test voltage: min. 2000V 50Hz at 1Min
- 2.5 Capacitance: max. 60pF/m

3 Mechanical Requirements

3.1 Temperature Range


fixed	-30°C	+105°C	according DIN72551
fixed	-40°C	+105°C	
moving	-20°C	+105°C	

4 Certification: UL2651


CSA
VDE 0811

5 Dimensions (see Table 1)

6 Remarks: Length per Reel has to be splice free




DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	DWN	F.VRIELINK	MATERIAL	1 1	
	CHK	B.MAAS	TE Connectivity		
	APVD	J.V.GRUNSVEN			
	PRODUCT SPEC	-	NAME		
	APPLICATION SPEC	-	FLAT RIBBON CABLE 28AWG PITCH 1.27 mm		
	WEIGHT	-	SIZE	CAGE CODE	DRAWING NO
			A4	00779	C-167019
CUSTOMER DRAWING			SCALE	SHEET	1 OF 2 REV F1



LOC	DIST	REVISIONS			
H	-	LTR	DESCRIPTION	DATE	APVD
			SEE SHEET 1		

TABLE 1

100	80.94	80.01	64	6-167019-4
100	75.86	74.93	60	6-167019-0
100	63.16	62.23	50	5-167019-0
100	50.46	49.53	40	4-167019-0
100	46.65	45.72	37	3-167019-7
100	42.84	41.91	34	3-167019-4
100	32.68	31.75	26	2-167019-6
100	31.41	30.48	25	2-167019-5
100	30.14	29.21	24	2-167019-4
450	25.06	24.13	20	2-167019-0
500	22.52	21.59	18	1-167019-8
600	19.98	19.05	16	1-167019-6
625	18.71	17.78	15	1-167019-5
650	17.44	16.51	14	1-167019-4
700	14.90	13.97	12	1-167019-2
900	12.36	11.43	10	1-167019-0
950	11.09	10.16	9	0-167019-9
1000	9.82	8.89	8	0-167019-8
1300	7.28	6.35	6	0-167019-6
1800	4.74	3.81	4	0-167019-4
Length per Reel (m)	C (mm)	B (mm)	Number of Conductors	Partnumber

DIMENSIONS: mm		DWN F.VRIELINK		MATERIAL 		FINISH 	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -°'		CHK BMAAS 		 TE Connectivity			
		APVD J.V.GRUNSVEN					
		PRODUCT SPEC -		NAME FLAT RIBBON CABLE 28AWG PITCH 1.27 mm			
		APPLICATION SPEC -		SIZE A4		CAGE CODE 00779	
		WEIGHT -		CUSTOMER DRAWING			
				SCALE		SHEET 2 OF 2 REV F1	