

LOC	DIST	REVISIONS					
		#	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00	A1		REVISED PER ECO-09-024606	31OCT09	KK	AEG
		B		REVISED PER ECO-15-014641	22OCT15	DS	FY

- ⚠






HOUSING MATERIAL: LIQUID CRYSTAL POLYMER. COLOR: NATURAL
- ⚠

CONTACT MATERIAL: PHOSPHOR-BRONZE
- ⚠


CONTACT FINISH:(B)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.0006 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- ④

PART MARKING, LOCATED APPROXIMATELY AS SHOWN.
- ⑤

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED CIRCUIT PATTERN
(COMPONENT SIDE)



VIEW W-W
SCALE 20:1

⑤	OBSOLETE	94.00	47	95.88	240	-5223652-8
	OBSOLETE	82.00	41	83.88	210	-5223652-7
⑤	OBSOLETE	70.00	35	71.88	180	-5223652-6
	OBSOLETE	58.00	29	59.88	150	-5223652-5
⑤	OBSOLETE	46.00	23	47.88	120	5223652-4
	OBSOLETE	34.00	17	35.88	90	-5223652-3
⑤	OBSOLETE	22.00	11	23.88	60	5223652-2
	OBSOLETE	10.00	5	11.88	30	5223652-1
		DIM C	B	DIM A	NUMBER OF SIGNAL POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.MCMMASTER	15DEC04	TE Connectivity		
		CHK R.WERTZ	15DEC04			
		APVD R.WERTZ	15DEC04	NAME ASSEMBLY, RECEPTACLE, SIGNAL, VERTICAL, 5 ROW, Z-PACK 2mm FB, WITH PRESS-FIT LEADS		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A1		
		0 PLC ± -		CAGE CODE 00779		
		1 PLC ± -		DRAWING NO C=5223652		
		2 PLC ± 0.13		RESTRICTED TO		
		3 PLC ± -				
		4 PLC ± -				
		ANGLES ± -				
		FINISH				
MATERIAL		WEIGHT		SCALE 4:1		
				SHEET 1 OF 1		
				REV B		