

Adapter plate - VS-ADP24-VS25/RJ45 - 1652428


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Adapter plate, size B24, reinforced, including panel mounting frame with DSUB 25 protective cover and gender changer contact insert socket/socket, and RJ45/IP67 panel mounting frame for modular socket inserts with protective cover without contact insert

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 969790
GTIN	4017918969790
Weight per Piece (excluding packing)	73.000 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Mechanical characteristics

Degree of protection	IP54
Design	B24

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------

Material data

Flammability rating according to UL 94	HB
Material	PA
Sealing material	TPE
Seal material	TPE

Standards and Regulations

Adapter plate - VS-ADP24-VS25/RJ45 - 1652428

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Environmental Product Compliance

REACH SVHC	DEHP 117-81-7
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"