



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 50VDC, 50mA
- ▲5. OPERATING FORCE: 100 ± 50 gms
6. TRAVEL: 0.25mm +0.2/-0.1MM
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
- ▲9. CONTACTS: GOLD
10. PACKAGED TAPE AND REEL- 750 PIECES PER REEL. E
11. 2002/95/EC (ROHS) COMPLIANT
12. ▲DENOTES CRITICAL PARAMETER



E	21010	750 PER REEL WAS 1000 PER REEL	2/6/13	EBP
D	20921	P990006 WAS P990005	12/12/12	EBP
C	20800	Redrawn	10/01/12	RC
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE TL3301SPF100RG

SCALE 4:1

DATE 12/12/2012

DR rc

DWG P010803

REV E