






PART NUMBER		REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION
1852803-1		A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER
1852803-2		A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER
1852803-3		A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER
1852803-6		A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER
7-1852803-7		A	-	-	-	SPARE PARTS

- △ RECOMMENDED SPARE PARTS
△ GREASE LIGHTLY
△ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE



TE PN		DELPHI		DELPHI TERMINAL - DELPHI CRIMP SPECS	
1949860-1		12124519			
-		-		PAD LTR	
-		-		CRIMP HEIGHT	
-		-		WIRE SIZE	
-		-		A	
-		-		B	
-		-		C	
-		-		D	
-		-		CRIMP	
-		-		SIZE	
-		-		TYPE	
-		-		RANGE	
-		-		WIRE	
-		-		INSUL	
-		-		FEED	
WIRE STRIP LENGTH 5.23-5.59		TERM APPL SPEC -		APPLICATOR INSTRUCTIONS 408-8040	
				SET UP GAGE 458637-1	



	-	1	1	1	1	-	693855-1	FRONT STRIP GUIDE	127
	-	2	2	2	2	-	8-354778-1	PIN, WIRE DISC, .2900	126
3	-	-	-	REF	-	...	455749-1	GUARD WINDOW	116
3	-	-	REF	-	-	...	679532-1	INSERT, GUARD	115
	-	2	2	2	2	-	21024-2	WASHER, SPRG LOCK, REG NO 4	114
	-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
	-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
	-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
	-	2	2	2	2	-	1-21000-3	SCR, SKT HD CAP 4-40 X .250	85
	-	1	1	1	1	-	455888-1	SPACER, CRIMPER	82
	-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
	-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	7
	-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
	-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
	-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
	-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
	-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62
	-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
	-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
	-	1	1	1	1	-	458537-2	PAWL, FEED	56
	-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
	-	2	2	2	2	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	53
	-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
	-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
	-	1	1	1	1	-	690753-1	SPACER, TONKER	50
	-	-	1	-	-	...	690602-6	CAM, PRE FEED, 1 5/8	49
	-	-	-	1	-	...	690602-5	CAM, PRE FEED, 1 1/8	48
	-	1	-	-	1	-	690501-4	CAM, POST-FEED 1 5/8	47
	-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MQCA)	46
	-	1	1	1	1	-	690191-1	PLUG,NYLON	45
	-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
	-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
	-	1	1	1	1	-	690124-1	WASHER, RAM (.115)	42
	-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
	-	1	1	1	1	-	23241-6	BALL, STEEL	40
	-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
	-	1	1	1	1	-	690142-1	DISC, INSULATION	38
	-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
	-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
	-	1	1	1	1	-	690212-1	POST, RAM	35
	-	1	1	1	1	-	690786-5	TERMINAL SUPPORT	34
	-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
	-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
	-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
	-	1	1	1	1	-	1320908-3	SPACER, STRIP GUIDE	30
	-	1	1	1	1	-	1-1633091-7	ASSEMBLY, STRIP GUIDE	29
	-	1	1	1	1	-	1-455888-0	SPACER, CRIMPER	28
	-	1	1	1	1	-	1320928-2	PLATE, STRIP GUIDE	24
	-	1	-	-	1	-	690472-2	STRIPPER	22
	-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
	-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
	-	-	1	1	-	-	691353-1	STRIPPER	19
1	-	1	-	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	13
	-	1	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
	-	1	1	1	1	-	690461-1	STOP, SHEAR	11
	-	-	1	1	1	-	690459-1	SHEAR HOLDER, FRONT	10
	-	1	1	1	1	-	454276-1	FLOATING SHEAR, FRONT	9
1	1	1	1	1	1	-	2-1633544-5	ANVIL, COMBINATION	8
	-	-	-	-	-	...	-	-	7
	-	-	-	-	-	...	-	-	6
	-	1	1	1	1	-	1-455889-4	DEPRESSOR, SHEAR	5
	-	1	1	1	1	-	3-238011-1	BLOCK, CRIMPER SPACER	4
1	1	1	1	1	1	-	1633511-5	CRIMPER, INSULATION F	3
	-	1	1	1	1	-	455888-9	SPACER, CRIMPER	2
1	1	1	1	1	1	-	2-1633609-4	CRIMPER, WIRE	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852803-6](#)