



# Mining & Heavy Industry Tools

The Mumme Products' range of forged hand tools are produced to the highest possible standards for use in the mining and heavy construction industries. With top quality materials and safety as a priority, we design and manufacture superior products available worldwide.



For Professionals...  
Since 1857™




## Bars – Construction

### Crowbars - (St. Angelo Bars) Hexagon and Round




- Used for digging holes and breaking clay, rock and concrete
- Forged from tough high-tensile carbon manganese steel
- Ground and sharpened to a diamond point for easier digging and breaking concrete
- Long tapered blade also for easier digging
- Both ends heat treated for increased performance and strength
- Hexagon bar profile for greater control
- Round bar profile is easier on hands
- Anti-corrosive primer with enamel finish
- Precision heat treated to best suit product application

5CB180025



5CB180025



5CB180030

#### Hexagonal Bars

| Cat. No.  | Blade Width  | Diameter          | Length          | Weight               |
|-----------|--------------|-------------------|-----------------|----------------------|
| 5CB150025 | 2" (50.8 mm) | 1" (25.4 mm)      | 59" (1498.6 mm) | 13.5 lbs. (6.12 kg)  |
| 5CB150030 | 2" (50.8 mm) | 1-3/16" (30.2 mm) | 59" (1498.6 mm) | 19.0 lbs. (8.62 kg)  |
| 5CB165025 | 2" (50.8 mm) | 1" (25.4 mm)      | 65" (1651.0 mm) | 14.8 lbs. (6.71 kg)  |
| 5CB165030 | 2" (50.8 mm) | 1-3/16" (30.2 mm) | 65" (1651.0 mm) | 20.9 lbs. (9.48 kg)  |
| 5CB180025 | 2" (50.8 mm) | 1" (25.4 mm)      | 71" (1803.4 mm) | 16.2 lbs. (7.35 kg)  |
| 5CB180030 | 2" (50.8 mm) | 1-3/16" (30.2 mm) | 71" (1803.4 mm) | 23.0 lbs. (10.43 kg) |

#### Round Bars

| Cat. No.  | Blade Width      | Diameter          | Length          | Weight              |
|-----------|------------------|-------------------|-----------------|---------------------|
| 5CB180022 | 1-1/2" (38.1 mm) | 7/8" (22.2 mm)    | 71" (1803.4 mm) | 12.0 lbs. (5.44 kg) |
| 5CB180025 | 2" (50.8 mm)     | 1-1/16" (27.0 mm) | 71" (1803.4 mm) | 17.1 lbs. (7.76 kg) |
| 5CB180030 | 2" (50.8 mm)     | 1-3/16" (30.2 mm) | 71" (1803.4 mm) | 21.4 lbs. (9.71 kg) |

### Gooseneck Bar-Hexagon



- Used for levering and moving objects into place with a lift and swivel motion
- Forged from tough high-tensile carbon manganese steel
- Diamond point and gooseneck ends for flexibility of use
- Gooseneck set for improved leverage
- Hexagon bar profile for greater control
- Precision heat treated to best suit product application

5GNB180030



For more Gooseneck Bars see Steel Construction section.


| Cat. No.   | Hex Diameter      | Length          | Weight              |
|------------|-------------------|-----------------|---------------------|
| 5GNB180030 | 1-3/16" (30.2 mm) | 71" (1803.4 mm) | 24.7 lbs. (11.20kg) |

### Slate Bars-Hexagon (Pinch Bars)



- Used for levering and moving objects into place with a lift and swivel motion
- Forged from high-tensile carbon manganese steel for maximum strength
- Heel offset to 40° angle for optimum lifting
- Hexagon bar profile gives greater control and reduces bar roll
- Heat-treated blade ends for maximum toughness
- Precision heat treated to best suit product application

5PB180025



| Cat. No.  | Hex Diameter      | Length          | Weight               |
|-----------|-------------------|-----------------|----------------------|
| 5PB150025 | 1" (25.4 mm)      | 59" (1498.6 mm) | 13.6 lbs. (6.17 kg)  |
| 5PB150030 | 1-3/16" (30.2 mm) | 59" (1498.6 mm) | 19.6 lbs. (8.89 kg)  |
| 5PB165025 | 1" (25.4 mm)      | 65" (1651.0 mm) | 15.0 lbs. (6.80 kg)  |
| 5PB165030 | 1-3/16" (30.2 mm) | 65" (1651.0 mm) | 21.9 lbs. (9.983 kg) |
| 5PB180025 | 1" (25.4 mm)      | 71" (1803.4 mm) | 16.8 lbs. (7.62 kg)  |
| 5PB180030 | 1-3/16" (30.2 mm) | 71" (1803.4 mm) | 24.3 lbs. (11.0 2kg) |

| Cat. No. | Hex Diameter     | Length         | Weight             |
|----------|------------------|----------------|--------------------|
| 5PB45016 | 5/8" (15.9 mm)   | 18" (457.2 mm) | 1.6 lbs. (0.73 kg) |
| 5PB60020 | 25/32" (19.8 mm) | 24" (609.6 mm) | 3.4 lbs. (1.54 kg) |
| 5PB60025 | 1" (25.4 mm)     | 24" (609.6 mm) | 5.3 lbs. (2.40 kg) |
| 5PB75025 | 1" (25.4 mm)     | 30" (762.0 mm) | 6.7 lbs. (3.04 kg) |
| 5PB90025 | 1" (25.4 mm)     | 36" (914.4 mm) | 8.0 lbs. (3.63 kg) |

For more Connecting Bars Steel see Steel Construction section.

## Bars – Mining


### Scaling Bars - Tubular Aluminum (Aluminium) - Round and Hexagon




7SCTH1800

- Used in the mining industry for prying overhanging rock
- Aluminium tube body for light weight and less user fatigue
- Inserted steel ends forged from tough carbon manganese steel
- Heel offset to 40° angle for optimum levering
- Precision heat treated to best suit product application
- Round bar profile is easier on hands
- Hexagon bar profile for greater control

#### Round Bars



#### Hexagonal Bars



| Cat. No. | Diameter         | Length           | Weight              |
|----------|------------------|------------------|---------------------|
| 7SCT1800 | 1-1/4" (31.8 mm) | 71" (1803.4 mm)  | 6.4 lbs. (2.90 kg)  |
| 7SCT3660 | 1-1/4" (31.8 mm) | 144" (3657.6 mm) | 9.3 lbs. (4.22 kg)  |
| 7SCT4320 | 1-1/4" (31.8 mm) | 170" (4318.0 mm) | 10.2 lbs. (4.63 kg) |

| Cat. No.  | Diameter         | Length              | Weight             |
|-----------|------------------|---------------------|--------------------|
| 7SCTH1800 | 1-1/4" (31.8 mm) | 71" (1803.4 mm)     | 6.5 lbs. (2.95 kg) |
| 7SCTH2400 | 1-1/4" (31.8 mm) | 94-1/2" (2400.3 mm) | 7.5 lbs. (3.40 kg) |

### Scaling Bars-Chrome Alloy Steel-Hexagon



7SC150019

- Used in the mining industry for prying overhanging rock
- Forged from chrome alloy steel
- Heat-treated blades for maximum toughness
- Hex profile for good control
- Heel offset to 40° angle for optimum levering
- Precision heat treated to best suit product application



| Cat. No.  | Hex Diameter | Length              | Weight              |
|-----------|--------------|---------------------|---------------------|
| 7SC120019 | 25/32"       | 47" (1193.8 mm)     | 6.9 lbs. (3.13 kg)  |
| 7SC150019 | 25/32"       | 59" (1498.6 mm)     | 8.6 lbs. (3.90 kg)  |
| 7SC180019 | 25/32"       | 71" (1803.4 mm)     | 10.3 lbs. (4.67 kg) |
| 7SC210019 | 25/32"       | 83" (2108.2 mm)     | 12.0 lbs. (5.44 kg) |
| 7SC240019 | 25/32"       | 94-1/2" (2400.3 mm) | 13.8 lbs. (1.7 kg)  |

## Chisels & Punches


### Cold Chisels-Alloy Cross Cut

- Used for removing oil seals
- Also used for cutting in corners and difficult or confined areas
- Forged from chrome alloy steel to give a harder blade with great resilience
- Precision hardened and tempered so blade will not shatter when struck hard
- Accurately ground to the optimum angle for cutting



7CHC15013

| Cat. No.  | Blade Width    | Overall Length | Weight          |
|-----------|----------------|----------------|-----------------|
| 7CHC15013 | 1/4" (6.4 mm)  | 6" (152.4 mm)  | 4.2 oz. (119 g) |
| 7CHC17516 | 5/16" (7.9 mm) | 7" (177.8 mm)  | 8.0 oz. (227 g) |
| 7CHC20020 | 3/8" (9.5 mm)  | 8" (203.2 mm)  | 8.8 oz. (249 g) |



## Chisels & Punches

### Brass Punches

- Used where a softer punch is needed, e.g. where damage may occur from using a hardened punch
- Selected brass, correct composition for punch use
- Knurled handle for gripping easily
- Chamfered head for safety

| Cat. No. | Diameter         | Overall Length     | Weight             |
|----------|------------------|--------------------|--------------------|
| 4BP10    | 3/8" (9.5 mm)    | 6" (152.4 mm)      | 3.5 oz. (99 g)     |
| 4BP12    | 1/2" (12.7 mm)   | 7" (177.8 mm)      | 4.8 oz. (136 g)    |
| 4BP16    | 5/8" (15.9 mm)   | 7" (177.8 mm)      | 10.6 oz. (301 g)   |
| 4BP19    | 3/4" (19.1 mm)   | 8" (203.2 mm)      | 17.6 oz. (499 g)   |
| 7BP29219 | 3/4" (19.1 mm)   | 11-1/2" (292.1 mm) | 1.5 lbs. (0.68 kg) |
| 7BP29225 | 1" (25.4 mm)     | 11-1/2" (292.1 mm) | 2.8 lbs. (1.27 kg) |
| 7BP29232 | 1-1/4" (31.8 mm) | 11-1/2" (292.1 mm) | 4.3 lbs. (1.95 kg) |



4BP16

| Cat. No. | Set Contains   | Weight             |
|----------|----------------|--------------------|
| 4BPSET5  |                | 4.4 lbs. (2.00 kg) |
| Cat. No. | Diameter       | Overall Length     |
| 4BP10    | 3/8" (9.5 mm)  | 6" (152.4 mm)      |
| 4BP12    | 1/2" (12.7 mm) | 7" (177.8 mm)      |
| 4BP16    | 5/8" (15.9 mm) | 7" (177.8 mm)      |
| 4BP19    | 3/4" (19.1 mm) | 8" (203.2 mm)      |
| 4BP25    | 1" (25.4 mm)   | 8" (203.2 mm)      |

### Pin Punches

- Used for driving out and removing pins and keys
- Tough and resilient shaft made from quality tool steel
- Heat treated for durability and strength
- Soft head for safety; will mushroom, not chip
- Knurled handle for gripping easily



4PPL06.5

| Cat. No. | Diameter        | Overall Length     | Weight              |
|----------|-----------------|--------------------|---------------------|
| 4PPL02.5 | 3/32" (2.4 mm)  | 2-5/32" (54.8 mm)  | 0.13 lbs. (0.06 kg) |
| 4PPL03   | 7/64" (2.8 mm)  | 2-5/32" (54.8 mm)  | 0.13 lbs. (0.06 kg) |
| 4PPL04   | 5/32" (4.0 mm)  | 2-23/64" (59.9 mm) | 0.13 lbs. (0.06 kg) |
| 4PPL05   | 3/16" (4.8 mm)  | 2-35/64" (64.7 mm) | 0.15 lbs. (0.07 kg) |
| 4PPL06   | 15/64" (6.0 mm) | 2-35/64" (64.7 mm) | 0.15 lbs. (0.07 kg) |
| 4PPL06.5 | 1/4" (6.4 mm)   | 2-35/64" (64.7 mm) | 0.17 lbs. (0.08 kg) |
| 4PPL08   | 5/16" (7.9 mm)  | 2-3/4" (69.9 mm)   | 0.24 lbs. (0.11 kg) |
| 4PPL10   | 25/64" (9.9 mm) | 2-3/4" (69.9 mm)   | 0.35 lbs. (0.16 kg) |

| Cat. No. | Set Contains    | Weight             |
|----------|-----------------|--------------------|
| 4PPLSET8 |                 |                    |
| Cat. No. | Diameter        | Overall Length     |
| 4PPL02.5 | 3/32" (2.4 mm)  | 2-5/32" (54.8 mm)  |
| 4PPL03   | 7/64" (2.8 mm)  | 2-5/32" (54.8 mm)  |
| 4PPL04   | 5/32" (4.0 mm)  | 2-23/64" (59.9 mm) |
| 4PPL05   | 3/16" (4.8 mm)  | 2-35/64" (64.7 mm) |
| 4PPL06   | 15/64" (6.0 mm) | 2-35/64" (64.7 mm) |
| 4PPL06.5 | 1/4" (6.4 mm)   | 2-35/64" (64.7 mm) |
| 4PPL08   | 5/16" (7.9 mm)  | 2-3/4" (69.9 mm)   |
| 4PPL10   | 25/64" (9.9 mm) | 2-3/4" (69.9 mm)   |

## Construction Tools

### Starter Drift

- Used for aligning holes in heavy construction
- Forged from tough high-tensile carbon manganese steel
- Designed for driving with hammer
- Taper is forged, not turned, for finer grain, giving greater tensile strength
- Will not score edge when driven hard
- Hex profile for increased control
- Correctly heat treated to best suit product application



5SDL45025

| Cat. No.  | Point Diameter   | Diameter          | Overall Length | Weight              |
|-----------|------------------|-------------------|----------------|---------------------|
| 5SDL45025 | 0.500 (12.70 mm) | 1-3/32" (27.8 mm) | 18" (457.2 mm) | 3.48 lbs. (1.58 kg) |

## Construction Tools

### Barrel Drifts

- Used for aligning holes in construction
- Also used for expanding holes in mild steel
- Forged from tough high-tensile steel
- Taper is forged, not turned, for finer grain, giving greater tensile strength
- Will not score edge when driven hard
- Precision heat treated to best suit product application



5BD24

| Cat. No. | Point Diameter   | Diameter           | Overall Length     | Weight              |
|----------|------------------|--------------------|--------------------|---------------------|
| 5BD19    | 23/64" (9.1 mm)  | 3/4" (19.1 mm)     | 6-9/32" (159.5 mm) | 0.61 lbs. (0.28 kg) |
| 5BD20    | 3/8" (9.5 mm)    | 25/32" (19.8 mm)   | 7-5/64" (179.8 mm) | 0.77 lbs. (0.35 kg) |
| 5BD30    | 0.578" (14.7 mm) | 1-3/16" (30.2 mm)  | 7-7/8" (200.0 mm)  | 1.8 lbs. (0.82 kg)  |
| 5BD33    | 0.156" (3.97 mm) | 1-19/64" (32.9 mm) | 7-7/8" (200.0 mm)  | 2.3 lbs. (1.04 kg)  |

### Podger Pins (Broad Head Bull Pins)

- Used for aligning holes and expanding holes in mild steel
- Forged from tough high-tensile carbon manganese steel
- Forged, not turned, long tapered point for ease of aligning
- For added safety, forged head prevents pin being driven right through hole and falling
- Hex shaft allows spanner to be used to assist removal
- Can be carried on belt
- Precision heat treated to best suit product application



5POP25

| Cat. No. | Diameter Across Hexagon Points | Hexagon Shaft Diameter | Overall Length | Weight             |
|----------|--------------------------------|------------------------|----------------|--------------------|
| 5POP25   | 1-3/32" (27.8 mm)              | 1"                     | 16" (406.4 mm) | 3.3 lbs. (1.50 kg) |
| 5POP30   | 1-5/16"                        | 1-3/16"                | 16" (406.4 mm) | 4.5 lbs. (2.04 kg) |

For more Barrel and Bull Pins  
see Steel Construction section.

### Fox Wedge-Stainless Steel

- Used for splitting mating surfaces and for packing machinery and structures before fixing
- Also used in the marine environment because of its corrosion-resistant properties
- Forged from stainless steel for greater hardness and non-magnetic properties
- Ground blade with fine edge for easy entry
- Precision heat treated to best suit product application



7FWSS10025

| Cat. No.   | Width            | Thickness      | Material        | Overall Length | Weight              |
|------------|------------------|----------------|-----------------|----------------|---------------------|
| 5FW07538   | 1-1/2" (38.1 mm) | 1/2" (12.7 mm) | Steel           | 3" (76.2 mm)   | 0.35 lbs. (0.16 kg) |
| 5FW10025   | 1" (25.4 mm)     | 5/16" (7.9 mm) | Steel           | 4" (101.6 mm)  | 0.22 lbs. (0.10 kg) |
| 5FW17550   | 2" (50.8 mm)     | 1/2" (12.7 mm) | Steel           | 7" (177.8 mm)  | 1.01 lbs. (0.46 kg) |
| 7FW27050   | 2" (50.8 mm)     | 1" (25.4 mm)   | Steel           | 11" (279.4 mm) | 4.0 lbs. (1.81 kg)  |
| 7FWSS10025 | 1" (25.4 mm)     | 5/16" (7.9 mm) | Stainless Steel | 4" (101.6 mm)  | 3.5 oz. (99 g)      |


### Pry Bar



5PRBP45016

- Used for prying, separating flanges and aligning holes
- Forged from tough high-tensile carbon manganese steel
- Thin, finely ground curved chisel end for ease of entry between surfaces
- Forged, not turned, long tapered point for maximum strength
- Hexagon profile for greater control
- Precision heat treated to best suit product application

| Cat. No.   | Chisel Width     | Hex Diameter | Overall Length | Weight             |
|------------|------------------|--------------|----------------|--------------------|
| 5PRBP45016 | 25/32" (19.8 mm) | 5/8"         | 18" (457.2 mm) | 1.7 lbs. (0.77 kg) |



## Construction Tools

### Spoon Bar - Round



5SB75022

- Used for levering, prying between surfaces and aligning holes
- Forged from resilient 4140 steel
- Taper is forged, not turned, for finer grain, giving greater tensile strength
- Thin spoon blade ends provide easy access between surfaces and a gentle rolling lift
- Correctly heat treated to best suit product application
- Spoon end is at 40° angle

| Cat. No. | Point Diameter | Body Diameter  | Overall Length | Weight              |
|----------|----------------|----------------|----------------|---------------------|
| 5SB75022 | 1/4" (6.4 mm)  | 7/8" (22.2 mm) | 30" (762.0 mm) | 4.40 lbs. (2.00 kg) |

### Podger Bars - Hexagon



5POB37520

- Used for levering and aligning
- Forged from tough high-tensile carbon manganese steel
- Heel set to 40° angle for optimum levering; blade ground to 30° angle for easy entry between surfaces
- Taper is forged, not turned, for finer grain, giving greater tensile strength
- Hexagon profile for greater control and to minimize bar roll
- Precision heat treated to best suit product application

| Cat. No.  | Point Diameter  | Hex Diameter | Overall Length | Weight             |
|-----------|-----------------|--------------|----------------|--------------------|
| 5POB37516 | 0.313" (7.9 mm) | 5/8"         | 15" (381.0 mm) | 1.2 lbs. (0.54 kg) |
| 5POB37520 | 0.375" (9.5 mm) | 25/32"       | 15" (381.0 mm) | 1.8 lbs. (0.82 kg) |
| 5POB45016 | 0.313" (7.9 mm) | 5/8"         | 18" (457.2 mm) | 1.5 lbs. (0.68 kg) |
| 5POB45020 | 0.375" (9.5 mm) | 25/32"       | 18" (457.2 mm) | 2.3 lbs. (1.04 kg) |
| 5POB60020 | 0.375" (9.5 mm) | 25/32"       | 24" (609.6 mm) | 3.2 lbs. (1.45 kg) |
| 5POB90020 | 0.375" (9.5 mm) | 25/32"       | 36" (914.4 mm) | 4.9 lbs. (2.22 kg) |

### Star Dropper Hammer



5SDSH

- Used for driving in star (fencing) droppers
- Also used to drive in marker pegs, stakes and concreting stakes
- Heavy unit drives droppers very quickly and efficiently
- Solid steel handles and slug are welded together, which gives greater strength

| Cat. No. | Internal Diameter | Overall Length       | Weight              |
|----------|-------------------|----------------------|---------------------|
| 5SDSH    | 2-1/8" (54.0 mm)  | 33-55/64" (860.0 mm) | 19.1 lbs. (8.66 kg) |

## Construction Tools

### Star Dropper Remover

- Used for removing star droppers (also called star pickets or fencing droppers)
- Also used for removing selected pipes and steel pegs
- Gripper made from high-tensile steel for durability and long life
- Gripper bites efficiently into dropper for easy extraction
- Long handle for excellent leverage

| Cat. No. | Handle Length  | Slot Opening                   | Overall Height | Weight              |
|----------|----------------|--------------------------------|----------------|---------------------|
| 5SDR     | 36" (914.4 mm) | 1-21/64" x 2" (33.7 x 50.8 mm) | 32" (812.8 mm) | 17.8 lbs. (8.07 kg) |



5SDR

## Hammers

### Drill Hammer - Wooden Handle



5HDRH20

- Used for mining and confined environments
- Also ideal for close work with enough head weight for effective hammering
- Head forged from high-tensile carbon manganese steel, with hardened and tempered face and claw
- Fitted with tough Australian spotted gum hardwood handle, oiled for long life and user comfort
- Handle is fitted to head with a glued wooden and steel wedge assembly
- Precision heat treated to best suit product application
- This product must be maintained in accordance with Australian standard AS 3797:1991

| Cat. No. | Head Weight        | Overall Length | Weight             |
|----------|--------------------|----------------|--------------------|
| 5HDRH2.0 | 4.4 lbs. (2.00 kg) | 16" (406.4 mm) | 4.6 lbs. (2.09 kg) |


### Mason's Club Hammer-Wooden Handle



5HCMH135

- Great all-around club hammer for general striking applications
- Forged from tough high-tensile carbon manganese steel, with hardened and tempered face and claw
- Fitted with tough Australian spotted gum hardwood handle, oiled for long life and user comfort
- Ideal for work in confined spaces
- Handle is fitted to head with a glued wooden and steel wedge assembly
- Precision heat treated to best suit product application
- This product must be maintained in accordance with Australian standard AS 3797:1991

| Cat. No.  | Head Weight        | Overall Length | Weight             |
|-----------|--------------------|----------------|--------------------|
| 5HCMH1.35 | 3.0 lbs. (1.36 kg) | 10" (254.0 mm) | 3.5 lbs. (1.59 kg) |



## Hammers

### Brass Sledge Hammers-Fiberglass Rubber Grip Handle



- Used in non-sparking environments or to avoid damage to struck objects
- Head forged from brass for softer, non-damaging blow
- Head is pinned to handle as well as epoxied to prevent head coming off
- Comfortable, thick rubber grip handle for increased protection from shock and vibration
- Handle includes both overstrike protection and large sweep at base to prevent loss of grip
- This product must be maintained in accordance with Australian standard AS 3797:1991

7HBRFRH14

| Cat. No.  | Head Weight         | Overall Length | Weight              |
|-----------|---------------------|----------------|---------------------|
| 7HBRFRH04 | 4.0 lbs. (1.81 kg)  | 16" (406.4 mm) | 4.9 lbs. (2.22 kg)  |
| 7HBRFRH07 | 7.0 lbs. (3.18 kg)  | 32" (812.8 mm) | 9.9 lbs. (4.49 kg)  |
| 7HBRFRH10 | 10 lbs. (4.54 kg)   | 36" (914.4 mm) | 12.2 lbs. (5.53 kg) |
| 7HBRFRH14 | 14.0 lbs. (6.35 kg) | 36" (914.4 mm) | 16.8 lbs. (7.62 kg) |

### Chipping Hammer - Rubber Grip

- Used for chipping off slag and spatter around welds
- Also used as geologists' or miners' tool
- Head forged from chrome alloy steel and hardened and tempered for maximum toughness
- Ground and sharpened vertical chisel and diamond point
- Excellent balance with hardened ends that do not flatten when chipping
- Precision heat treated to best suit product application



5WHRG

| Cat. No. | Head Length         | Overall Length       | Weight             |
|----------|---------------------|----------------------|--------------------|
| 5WHRG    | 6-11/16" (169.9 mm) | 10-15/64" (260.0 mm) | 1.1 lbs. (0.50 kg) |

## Safety Punches & Tyre (Tire) Levers

### Wire Rope Punches

- Used to safely drive out pins and keys in machinery
- Long, two-handed rubber handle to lessen shocks from blows
- Head attached with wire rope to reduce shock
- Urethane ring around head to reduce likelihood of chipping
- Heat-treated punch, so it will not shatter



| Cat. No. | Diameter         | Shaft Length      | Weight             |
|----------|------------------|-------------------|--------------------|
| 7WRP13   | 1/2" (12.7 mm)   | 4-3/4" (120.7 mm) | 3.0 lbs. (1.36 kg) |
| 7WRP16   | 5/8" (15.9 mm)   | 4-3/4" (120.7 mm) | 3.2 lbs. (1.45 kg) |
| 7WRP19   | 3/4" (19.1 mm)   | 4-3/4" (120.7 mm) | 3.6 lbs. (1.63 kg) |
| 7WRP22   | 7/8" (22.2 mm)   | 4-3/4" (120.7 mm) | 4.4 lbs. (2.00 kg) |
| 7WRP25   | 1" (25.4 mm)     | 4-3/4" (120.7 mm) | 4.6 lbs. (2.09 kg) |
| 7WRP32   | 1-1/4" (31.8 mm) | 4-3/4" (120.7 mm) | 5.3 lbs. (2.40 kg) |

7WRP22