




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C1	REVISED PER ECO-11-005030	22MAR11	RK	HMR






SECT B-B



-1:AS SHOWN





SECT A-A



AMP MARK

NOTES

1. FINISH(CONTACT AREA):0.38 μ mMIN GOLD PLATING
OVER Ni PLATING

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED : ± 0.3 >10 : ± 0.35 >30 : ± 0.4 ANGLE : $\pm 3'$	DWN K.IKEDA 7/DEC/'98	TE Connectivity					
			CHK N.MATSUBARA 7/DEC/'98						
APVD I.HASEGAWA 7/DEC/'98	NAME								
PRODUCT SPEC									
108-5619									
		APPLICATION SPEC	REC CONNTACT "S" SIZE, L/P <DYNAMIC D-2 SERIES>						
		114-5258							
MATERIAL		FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
(COPPER ALLOY)		SEE NOTE		A3	00779	C-1318108	-		
CUSTOMER DRAWING						SCALE	SHEET	OF	REV
						8-1	1	1	C1