


Eveready 1215

AA

SUPER HEAVY DUTY



Industry Standard Dimensions



Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)
(No Added Mercury or Cadmium)



Designation: ANSI-15D, IEC-R6
Battery Voltage: 1.5 Volts
Operating Temp: -18°C to 55°C (0°F to 130°F)
Average Weight: 15.0 grams (0.5 oz.)
Volume: 8.0 cubic centimeters (0.5 cubic inch)
Average Capacity: 1,100 mAh to 0.8 volts
(Rated capacity at 25 mA continuous at 21°C)
Cell: One No. 15 (size "AA")
Jacket: Metal

INTERNAL RESISTANCE VS. TEMPERATURE

The measurement is an approximation of the battery's actual internal resistance. It is sensitive to the loads and operator technique.

Schedule: Background Load 750 ohms
Pulse Load 4.0 ohms
Pulse Duration 1 second

Temperature	Typical Ri (ohms)
45°C (113°F)	0.4
21°C (70°F)	0.5
0°C (32°F)	0.8
-21°C (-4°F)	5.0

Important Notice





This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved

Eveready 1215

Industry Standard Tests (21° C)

**Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Energizer:

1215BP4 1215SW-4