



Taptite 2000® 02EQ



English	Français	Deutsch	Italiano	Español
Oval countersunk Torx Plus®	Tête fraisée bombée Torx Plus®	Linsen-Senkkopf Torx Plus®	Testa Svasata con calotta Torx Plus®	Avellanada gota de sebo Torx Plus®
Steel case hardened* Hardness: Surface: > 450 HV0,3 Core: 290 to 370 HV10	Acier cémenté* Dureté: Superficielle: > 450 HV0,3 À coeur: 290 à 370 HV10	Stahl einsatzgehärtet* Härte: Oberfläche: > 450 HV0,3 Kern: 290 bis 370 HV10	Acciaio cementato* Durezza: Superficiale: > 450 HV0,3 A cuore: 290 a 370 HV10	Acero cementado* Dureza: Superficial: > 450 HV0,3 Núcleo: 290 a 370 HV10
Zinc alkaline clear ¹⁾ or Zinc -nickel alkaline clear ²⁾	Zinc alcalin claire ¹⁾ ou Zinc-nickel alcalin claire ²⁾	Zink alkalisch transparent ¹⁾ oder Zink-Nickel alkalisch transparent ²⁾	Zinco alcalino chiaro ¹⁾ o Zinco-Nichel alcalino chiaro ²⁾	Zincado y pasivado claro ¹⁾ o Niquelado ²⁾





¹⁾ 96 h / ²⁾ 720 h **

≡ EN ISO 14584 (except/hors de/außer/eccetto/excepto Torx Plus®)

* : EN ISO 7085

** : to red rust / à la rouille rouge / bis Rotrost / alla ruggine rossa / al óxido rojo (ASTM B117)



Ø	Ø C	Ø D	Pitch / Pas / Steigung/ Paso / Paso	Cp max.	Ø Dk	K max.	f	Torx Plus®	t	L	Part No/ref
M2.0	1.93 - 2.01	1.88 - 1.97	0.40	1.77	3.50 - 3.80	1.20	0.50	6IP	0.63 - 0.77	4 ±0.24	02EQ2000401
										6 ±0.24	02EQ2000601
										8 ±0.29	02EQ2000801
										10 ±0.29	02EQ2001001
										12 ±0.35	02EQ2001201
										16 ±0.35	02EQ2001601
M2.5	2.43 - 2.52	2.37 - 2.48	0.45	2.25	4.40 - 4.70	1.50	0.60	8IP	0.91 - 1.04	20 ±0.42	02EQ2002001
										6 ±0.24	02EQ2500601
										8 ±0.29	02EQ2500801
										10 ±0.29	02EQ2501001
										12 ±0.35	02EQ2501201
M3.0	2.93 - 3.02	2.87 - 2.97	0.50	2.72	5.20 - 5.50	1.65	0.70	10IP	0.88 - 1.15	16 ±0.35	02EQ2501601
										20 ±0.42	02EQ2502001
										6 ±0.24	02EQ3000601
										8 ±0.29	02EQ3000801
										10 ±0.29	02EQ3001001
										12 ±0.35	02EQ3001201
										16 ±0.35	02EQ3001601
										25 ±0.42	02EQ3002501
										30 ±0.42	02EQ3003001

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros



www.acument.com

© 2008 Acument Intellectual Properties, LLC

Torx Plus® is a trademark of Acument Intellectual Properties, LLC. Taptite 2000® is Licensed by Research Engineering & Manufacturing, Inc.

page 1/3

Data shown is subject to change without prior notice as a result of continuous product development and improvement policy.
Your local Acument Global Technologies representative is at your disposal should you need to confirm latest information.

Taptite 2000® 02EQ

Ø	Ø C	Ø D	Pitch / Pas/ Steigung/ Passo / Paso	Cp max.	Ø Dk	K max.	f	Torx Plus®	t	L	Part No/ref
M4.0	3.92 - 4.02	3.83 - 3.95	0.70	3.61	8.04 - 8.40	2.70	1.00	20IP	1.42 - 1.80	8 ±0.29	02EQ4000801
										10 ±0.29	02EQ4001001
										12 ±0.35	02EQ4001201
										16 ±0.35	02EQ4001601
										20 ±0.42	02EQ4002001
										25 ±0.42	02EQ4002501
										30 ±0.42	02EQ4003001
										35 ±0.50	02EQ4003501
										8 ±0.29	02EQ5000801
										10 ±0.29	02EQ5001001
										12 ±0.35	02EQ5001201
										16 ±0.35	02EQ5001601
										20 ±0.42	02EQ5002001
										25 ±0.42	02EQ5002501
M5.0	4.91 - 5.02	4.81 - 4.94	0.80	4.55	8.94 - 9.30	2.70	1.20	25IP	1.65 - 2.03	30 ±0.42	02EQ5003001
										35 ±0.50	02EQ5003501
										40 ±0.50	02EQ5004001
										10 ±0.29	02EQ6001001
										12 ±0.35	02EQ6001201
										16 ±0.35	02EQ6001601
										20 ±0.42	02EQ6002001
										25 ±0.42	02EQ6002501
										30 ±0.42	02EQ6003001
										35 ±0.50	02EQ6003501
										40 ±0.50	02EQ6004001
										45 ±0.50	02EQ6004501
										50 ±0.50	02EQ6005001
										16 ±0.35	02EQ8001601
M6.0	5.90 - 6.03	5.78 - 5.93	1.00	5.38	10.87 - 11.30	3.30	1.40	30IP	2.02 - 2.42	20 ±0.42	02EQ8002001
										25 ±0.42	02EQ8002501
										30 ±0.42	02EQ8003001
										35 ±0.50	02EQ8003501
										40 ±0.50	02EQ8004001
										45 ±0.50	02EQ8004501
										50 ±0.50	02EQ8005001
										16 ±0.35	02EQ8001601
										20 ±0.42	02EQ8002001
										25 ±0.42	02EQ8002501
										30 ±0.42	02EQ8003001
										35 ±0.50	02EQ8003501
										40 ±0.50	02EQ8004001
										45 ±0.50	02EQ8004501
										50 ±0.50	02EQ8005001
										60 ±0.60	02EQ8006001
										70 ±0.60	02EQ8007001
										80 ±0.60	02EQ8008001
										16 ±0.35	02EQ8001601
										20 ±0.42	02EQ8002001
M8.0	7.87 - 8.03	7.71 - 7.91	1.25	7.23	15.37 - 15.80	4.65	2.00	45IP opt. 40IP	2.92 - 3.31	25 ±0.42	02EQ8002501
										30 ±0.42	02EQ8003001
										35 ±0.50	02EQ8003501
										40 ±0.50	02EQ8004001
										45 ±0.50	02EQ8004501
										50 ±0.50	02EQ8005001
										60 ±0.60	02EQ8006001
										70 ±0.60	02EQ8007001
										80 ±0.60	02EQ8008001
										16 ±0.35	02EQ8001601

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

Quality level / Niveau qualité / Qualitätsniveau / Livello qualità / Nivel de calidad: 150 ppm

Optional heat treatment : Class 10-9

Traitement thermique optionnel: Classe 10-9

Optionale Wärmebehandlung: Klasse 10-9

Trattamento termico opzionale: Classe 10-9

Tratamiento térmico opcional: Clase 10-9



Taptite 2000® 02EQ

Highlighted part numbers are non standard, non in stock - Références surlignées non standard et non tenues en stock - Markierte Artikel-Nummern sind kein Standard, keine Lagerware - I codici evidenziati non sono standard, non sono a stock - Referencias no estándar, generalmente no en stock

Finishes / finition / Oberflächen / superficie / superficie

Type	Description / description / Beschreibung / descrizione / descripción	~~Cr6~~	 3)	Code ⁴⁾
Standard	Zinc alkaline 8 µm mini clear, friction 0.08 - 0.14 / Zinc alcalin 8µm mini passivation claire, coefficient de frottement 0.08 - 0.14 / Zink alkalisch 8µm min. transparent, Reibkoeffizient 0.08 - 0.14 / Zinco alcalino 8µm min. passivazione chiara, coefficiente d'attrito 0.08 - 0.14 / Zincado y pasivado claro min. 8 µm coeficiente de fricción 0.08 - 0.14	✓	96 h	AG
Optional	Zinc alkaline 8 µm mini clear, friction 0.08 - 0.14 / Zinc alcalin 8µm mini passivation claire, coefficient de frottement 0.08 - 0.14 / Zink alkalisch 8µm min. transparent, Reibkoeffizient 0.08 - 0.14 / Zinco alcalino 8µm min. passivazione chiara, coefficiente d'attrito 0.08 - 0.14 / Zincado y pasivado claro min. 8 µm coeficiente de fricción 0.08 - 0.14	✓	400 h	AJ
Optional	Zinc-nickel alkaline clear, friction 0.08 - 0.14 / Zinc-nickel alcalin 8µm mini passivation claire, coefficient de frottement 0.08 - 0.14 / Zink-Nickel alkalisch transparent, Reibkoeffizient 0.08 - 0.14 / Zinco Nickel alcalino 8µm min. passivazione chiara, coefficiente d'attrito 0.08 - 0.14 / Niquelado claro min. 8 µm coeficiente de fricción 0.08 - 0.14	✓	720 h	BE
Optional	Zinc-nickel alkaline black, friction 0.08 - 0.14 / Zinc-nickel alcalin 8µm mini passivation noir, coefficient de frottement 0.08 - 0.14 / Zink-Nickel alkalisch schwarz, Reibkoeffizient 0.08 - 0.14 / Zinco Nickel alcalino 8µm min. passivazione nera, coefficiente d'attrito 0.08 - 0.14 / Niquelado negro min. 8 µm coeficiente de fricción 0.08 - 0.14	✓	720 h	BF

3) to red rust / à la rouille rouge / bis Rotrost / alla ruggine rossa / al óxido rojo

4) add code to the part number / ajoutez le code à la référence / fügen Sie den Code zur Artikel-Nummer hinzu / aggiungere il codice alla referenza / añadir numeración a la referencia