



PROD 3321 CODE	LOC DF	DIST X0	P	F	REVISIONS						
					ZONE	LTR	DESCRIPTION			DATE	APPD
				✓		E	REV & REDRAWN; 0600-1969-94 CT			2-95	JD




ASSEMBLED VIEW



CABLE (CUSTOMER SUPPLIED)



RECOMMENDED STRIP LENGTH
SCALE: N.T.S.



- FOR USE WITH RG-180/U, 180A/U, 180B/U, 195/U & 195A/U COAX CABLE.
- FERRULE CRIMPING TOOL: AMP TOOL #220066-1 CRIMP B OR #220066-2 CRIMP B.
- CONTACT CRIMPING TOOL: M22520/2-01 OR AMP TOOL NUMBER 1-601966-6, SETTING NUMBER 5. DANIELS POSITIONER PART NO. K345 OR AMP TOOL NO. 1-601966-6.
- SEE I.S.2348.
- DANIELS MANUFACTURING CORP
2266 FRANKLIN ROAD
BLOOMFIELD HILLS, MI 48013
- OUTER JACKET OF CABLE MUST BE TRIMMED TO ALLOW PROPER INTER-PIN CONTACT LOCATION AFTER FERRULE CRIMP OPERATION.
- PARTS SHIPPED UNASSEMBLED AND CABLE IS SUPPLIED BY CUSTOMER.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL SEE CALLOUTS FINISH SEE CALLOUTS	DR 2-1-95 C.C.THOMAS	AMP AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 2-2-95 J.DUNBAR			
	APPD 2-2-95 J.DUNBAR	NAME CONNECTOR, COAXIAL, RF SOCKET SIZE 5, ARINC (HEX CRIMP)		
	APPD 2-2-95 C.C.THOMAS	SIZE CAGE CODE DRAWING NO		
	PRODUCT SPEC 108-12045	C	00779	G=225791-8
	APPLICATION SPEC -	SCALE	5:1	SHEET 1 OF 1
	WEIGHT -			