



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		K3	REVISED PER ECR-11-006644	05APR11	HMR	GJ

D



- 1
- CONTINUOUS STRIP ON REELS.
- 2
- TIN PLATE OVER COPPER UNDERPLATE.
- 3
- WIRE RANGE FOR NEW APPLICATIONS: 1.27–2.38mm²[2500–4700 CMA]
(WIRE RANGE APPROVED FOR APPLICATIONS IMPLEMENTED PRIOR TO 2005: 2000–5300 CMA).
- 4
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 5
- CRIMP WIDTH:3.05[.120] F TYPE. CRIMP HEIGHT IN INCHES (+/–.002)=(TOTAL CMA OF WIRES + 12240)/220000.

C



B

4	OBSOLETE	—	H02 COPPER NICKEL	3	61492—3	
		2	082 BRASS	3	61492—2	
		—	082 BRASS	3	61492—1	
		FINISH	MATERIAL	WIRE RANGE	PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN MICHAEL S. FEHER 06MAR2000	TE TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK STEVE HEADER 06MAR2000				
		APVD STEVE HEADER 06MAR2000	NAME SPLICE			
		PRODUCT SPEC —				
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114—2088	SIZE A2	CAGE CODE 00779
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —	CUSTOMER DRAWING			
			SCALE 10:1	SHEET 1 OF 1	REV K3	

D

C

61492

B

A