







INSULATION CRIMP

BARREL CRIMP

"G" DIM. WITH PIN AT	
N / GO	N / NO GO
.052	.072

"W" DIM.	
GO	NO GO
.091	.097

DOUBLE END HANDLE
A.G.D. STANDARD



NOTE: PLUG GAGE TOOL FROM SIDE OPPOSITE INSULATION INSERTS

NOTE: "G" DIM. APPLIES AT CENTER OF "V" NOTCH AS INDICATED ON DRAWING.

NOTE: TOOL SHOULD BE BOT TOMED, OR CLOSED, BEFORE PLUG GAGING.

NOTE: FOR REPLACEMENT OF PARTS OTHER THAN SNAP RINGS & PINS, TOOL SHOULD BE RETURNED TO OUR FACTORY TO INSURE PROPER CERTI-CRIMP ADJUSTMENT.

PLUG GAGE DIMENSIONS APPL. WHEN TOOL IS DEFORMED BUT NOT UNDER PRESSURE.

AMP 550

FINISH: ✓ EXCEPT AS NOTED:
MATERIAL:
HEAT TREAT:

LOC. 5124	DR. R. VOLANSKI	DATE 5/18/59	SCALE 1:1	REV J-2
M C	ORD. 18-10-10	APPROV. 5/18/59	DATE 5/18/59	REV J-2
CUSTOMER COPY ONLY		AMP INCORPORATED HARRISBURG, PENNA.		
HEAVY HEAD HAND TOOL ASSEMBLY		CLASS. 44017-10-10 TYPE W-DIAMOND GRIP STEATH THERM		
ALL RIGHTS RESERVED AND PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.		59461		