


CEFC301-G Thru. CEFC305-G

Reverse Voltage: 50 to 600 Volts

Forward Current: 3.0 Amp

RoHS Device




Features

- Ideal for surface mount applications.
- Easy pick and place.
- Plastic package has Underwriters Lab. flammability classification 94V-0.
- Super fast recovery time for high efficient.
- Built-in strain relief.
- Low forward voltage drop.

Mechanical data

- Case: JEDEC DO-214AB, molded plastic.
- Terminals: solderable per MIL-STD-750, method 2026.
- Polarity: Color band denotes cathode end.
- Approx. weight: 0.21 grams



Maximum Ratings and Electrical Characteristics

Parameter	Symbol	CEFC301-G	CEFC302-G	CEFC303-G	CEFC304-G	CEFC305-G	Units
Max. repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	V
Max. DC blocking voltage	V_{DC}	50	100	200	400	600	V
Max. RMS voltage	V_{RMS}	35	70	140	280	420	V
Peak surge forward current, 8.3ms single half sine-wave superimposed on rate load (JEDEC method)	I_{FSM}	150					A
Max. average forward current	I_o	3.0					A
Max. instantaneous forward voltage at 3.0A	V_F	0.9			1.3	1.7	V
Reverse recovery time	T_{rr}	50				75	nS
Max. DC reverse current at $T_A=25^{\circ}\text{C}$ rated DC blocking voltage $T_A=100^{\circ}\text{C}$	I_R	10 200					μA
Max. thermal resistance (Note 1)	$R_{\theta JL}$	55					$^{\circ}\text{C/W}$
Max. operating junction temperature	T_J	150					$^{\circ}\text{C}$
Storage temperature	T_{STG}	-55 to +150					$^{\circ}\text{C}$

Notes: 1. Thermal resistance from junction to lead mounted on P.C.B. with 8.0×8.0 mm copper pad area.

RATING AND CHARACTERISTIC CURVES (CEFC301-G thru CEFC305-G)

Fig.1 Reverse Characteristics




Fig.2 Forward Characteristics




Fig.3 Junction Capacitance




Fig.4 Non-repetitive Forward Surge Current




Fig.5 Test Circuit Diagram and Reverse Recovery Time Characteristics




Fig.6 Current Derating Curve

