



PRODUCT NUMBER

20020034-XXXXXXLF

20020034-□ □ □ □ B 0 □ L F

PITCH

G: 5.00 mm
H: 5.08 mm

POLES

02: 2 POLES
03: 3 POLES
.....
24: 24 POLES

LF : DENOTED RoHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

PROPERTY TABLE				
FCI SERIES NAME		35-500	35-508	
PITCH (mm)		5.00	5.08	
VOLTAGE RATING (VAC)		300	300	
CURRENT RATING (A)		10	10	
APPLICABLE WIRE RANGE (AWG)		1-WIRE	12~26	12~26
		2-WIRE	NA	NA
WIRE CROSS SECTION (mm ²)	SOLID	1-WIRE	2.5	2.5
		2-WIRE	NA	NA
	STRANDED	1-WIRE	2.5	2.5
		2-WIRE	NA	NA
OPENING CONTACT HOUSING(mm ²)		2.4x3.0	2.2x2.7	
WIRE STRIP LENGTH(mm)		9~10	9~10	
WITHSTANDING VOLTAGE (kV)		1.6	1.6	
OPERATING TEMP. (°C)		-40~+115	-40~+115	
POLES AVAILABLE		02~24	02~24	
SAFETY CERTIFICATE				



NOTES:

1. MATERIALS

- 1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-2 INSULATING LEVER: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-3 WIRE GUARD : STAINLESS STEEL.
- 1-4 TERMINAL: COPPER ALLOY, TIN PLATED.
- 1-5 SCREW: STEEL, ZINC PLATED.
2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.
3. PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.
4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.
5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.


mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
A	T11-0004	WL	011811	angles	about	X.±0.5		MM  [INCH]	TERMINAL BLOCK				
B	T-005306	WL	082311			X.X±0.3			PLUGGABLE SIGNAL PLUG, UPSIDE CONTACT				
						X.XX±0.1			W/FLANGE				
								scale	dwg no				
				dr	WENDY CHEN	113010			sheet 1 of 3		size		
				enr	JASON HSU	113010			20020034		A4		
				chr	JASON HSU	113010							
				appd	JASON HSU	113010							
sheet index	revision sheet	B	B	B						type	CUSTOMER Drawing		
		1	2	3									

PRODUCT NUMBER	SERIES NAME	PITCH
20020034-GXXXXXXLF	35-500	5.00 mm




N = Number of poles
 Dim. L=(N $\times$ 5.0[.197])+0.6[.111]
 Dim. P=(N-1) $\times$ 5.0[.197]
 Dim. T=(N $\times$ 5.0[.197])+10.62[.418]
 Dim. K=(N+1) $\times$ 5.0[.197]




POLES	Dim. L & P	Dim.T & K
2-6p	$\pm 0.15[.006]$	$\pm 0.15[.006]$
7-12p	$\pm 0.20[.008]$	$\pm 0.25[.010]$
13-18p	$\pm 0.25[.010]$	$\pm 0.30[.012]$
19-24p	$\pm 0.30[.012]$	$\pm 0.40[.016]$



SECTION A-A


[illegible]

PRODUCT NUMBER	SERIES NAME	PITCH
20020034-HXXXXXXLF	35-508	5.08 mm




N = Number of poles
 Dim. L = $(N \times 5.08 [.200]) + 0.5 [.020]$
 Dim. P = $(N - 1) \times 5.08 [.200]$
 Dim. T = $(N \times 5.08 [.200]) + 10.16 [.400]$
 Dim. K = $(N + 1) \times 5.08 [.200]$

Poles	Dim.L & P & T & K
2-6p	$\pm 0.20 [.008]$
7-12p	$\pm 0.30 [.012]$
13-16p	$\pm 0.40 [.016]$
17-24p	$\pm 0.50 [.020]$



SECTION A-A



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title TERMINAL BLOCK PLUGGABLE SIGNAL PLUG, UPSIDE CONTACT W/FLANGE
B				angles X°±1°	X.±0.5 X.X±0.3 X.XX±0.1	scale	sheet 3 of 3 size A4
		dr	WENDY CHEN	113010			dwg no 20020034
		enr	JASON HSU	113010			
		chr	JASON HSU	113010			
		appd	JASON HSU	113010			
sheet index	revision sheet						type CUSTOMER Drawing