


SERIES 39

SPST, 150 mA to 1/2 Amp

FEATURES


- Requires an Absolute Minimum of Space
- Molded-In Terminals in SPST-N.O.
- Solder Lug Terminals



DIMENSIONS in inches (and millimeters)

Normally Open-SPST Economy and Standard Version

39-1
39-3
39-601*



Economy Version

Electrical Ratings	Operations at Rated Load	*Complete Part Number	Button Color
At 5 Vdc 150 mA	At 20 Vdc 20 mA	1,000,000	39-601 RED 39-601 BLK

Action	Total Travel	Actuating Force (oz.)	Mtg. Hole
Momentary	.035 ± .015 (0.89 ± 0.38)	4 + 4 - 2	11/64" (4.37) DIA.


Standard

Electrical Ratings	Operations at Rated Load	Complete Part Number	Button Color
At 115 Vac 1/2 Amp Res.	At 220 Vac 1/4 Amp Res.	1,000,000	39-1 39-3

Action	Total Travel	Actuating Force (oz.)	Mtg. Hole
Momentary	.035 ± .015 (0.89 ± 0.38)	4 + 4 - 2	11/64" (4.37) DIA.

Normally Open-SPST with Sealed Bushing and Button

39-351*




Rating at 115 Vac Resistive	Rating at 220 Vac Resistive	Operations at Rated Load	*Complete Part Number	Button Color
1/2 Amp	1/4 Amp	250,000	39-351 RED 39-351 BLK	Red Black

Action	Total Travel	Actuating Force (oz.)
Momentary	.035 ± .015 (0.89 ± 0.38)	16 ± 8

Normally Open-SPST with Overtravel

39-12
39-24




Rating at 115 Vac Resistive	Rating at 220 Vac Resistive	Operations at Rated Load	Complete Part Number	Button Color
1/2 Amp	1/4 Amp	100,000	39-12 39-24	Red Black

Action	Total Travel	Over Travel	Actuating Force (oz.)	Mtg. Hole
Momentary	.130 ± .025 (3.30 ± 0.64)	.015 (0.38) Min.	5 ± 3	11/64" (4.37) DIA.


Normally Closed–SPST

39-2



Action	Total Travel	Actuating Force (oz.)	Mtg. Hole
Momentary	.042 ± .010 (.07 ± .025)	+ 4 - 2	.172 (.4,37) DIA.

39-352*



Action	Total Travel	Actuating Force (oz.)
Momentary	.042 ± .010 (0.17 ± 0.25)	8 ± 4

SPST N.O.

SPST N.O. WITH OVERTRAVEL


SPST N.C.

Mounting Nut: Brass, tin zinc
Housing: Aluminum, clear anodized for 39-351 and 39-352; Brass, zinc trivalent chromate-plated for others
Button: Thermoset plastic
Base: Thermoset plastic
Shorting Bar: Fine silver for 39-2 and 39-352; brass, gold-plated over nickel plate for 39-601; fine silver, gold-plated for others
Terminals: Fine silver for 39-2 and 39-352; commercial bronze with gold-plated fine silver contact surface for others
Spring: Tinned music wire
O-Rings: (39-351 and 39-352) Internal ring is silicone; external ring is buna 'N'

Rating Criteria

Contact Resistance: 25 milliohms maximum
on a new switch
Voltage Breakdown: 1,000 Vac between
mutually insulated parts
Insulation Resistance: 1,000 megohms
minimum
Operating Temperature: -40°C to +85°C
Mounting Torque: 2 inch-pounds

ACCESSORY



Part Number	Description
39-1	N.O., Red Button
39-2	N.C., Black Button
39-3	N.O., Black Button
39-12	N.O., Overtravel Red Button
39-24	N.O., Overtravel Black Button
39-351 RED	N.O., Sealed, Red Button
39-351 BLK	N.O., Sealed, Black Button
39-352 RED	N.C., Sealed, Red Button
39-352 BLK	N.C., Sealed, Black Button
39-601 RED	N.O., Economy, Red Button
39-601 BLK	N.O., Economy, Black Button

Accessory cap may be used with all switches shown except 39-2.

Accessory Part Number	Description
30B1012-5	Red Button Cap
30B1012-9	Black Button Cap
30B1012-8	White Button Cap