


# Low Signal Relay

## G6S

### Surface Mount DPDT Relay

- High dielectric withstand voltage of 2,000 VAC between coil and contacts (standard type); 1,500 VAC between contacts of different polarity.
- Meets FCC Part 68 and Telcordia 2.5 kV surge withstand.
- European version certified for EN60950/EN41003 Supplementary Insulation at 250 V at Pollution Degree 2.
- Low power consumption of 140 mW (Non-latching)
- Available in through-hole and SMT terminals.
- Tape and reel or tube packaging.
- RoHS Compliant.



## Ordering Information

### ■ Standard Version

| Terminal         | Model<br>Contact form | Non-latching |                   | Single coil latching | Dual coil latching |
|------------------|-----------------------|--------------|-------------------|----------------------|--------------------|
|                  |                       | Standard     | European Version* |                      |                    |
| Gull-wing        | DPDT                  | G6S-2F       | G6S-2F-Y          | G6SU-2F              | G6SK-2F            |
| Inside "L"       |                       | G6S-2G       | G6S-2G-Y          | G6SU-2G              | G6SK-2G            |
| PCB through-hole |                       | G6S-2        | G6S-2-Y           | G6SU-2               | G6SK-2             |

\* Certified for EN60950/EN41003 Supplementary Insulation at 250 V (pollution degree 2)

**Notes:** 1. When ordering, add the rated coil voltage to the model number.

Example: G6S-2F DC12  
Rated coil voltage

2. When ordering tape packing (surface mount models), add "-TR" to the model number.

Example: G6S-2F-TR DC12  
Tape packing

"-TR" is not part of the relay model number. Therefore, it is not marked on the relay case.

3. Dual coil latching models are available with a High-sensitivity coil. (140 mW; 200 mW for DC24)  
When ordering High-sensitivity dual coil latching models, add "-H" to the model number.

Example: G6SK-2G-H-TR DC5  
High-sensitivity coil

### Model Number Legend

G6S    -       -    -    DC     
1    2   3   4   5   6

#### 1. Relay Function

None: Non-latching  
U: Single coil latching  
K: Dual coil latching

#### 3. Terminal Shape

None: Through-hole  
F: Gull-wing surface mount  
G: Inside "L" surface mount

#### 5. Packaging

None: Tube packaging  
TR: Tape and reel packaging  
(Surface mount models)

#### 2. Contact Form

2: DPDT

#### 4. Approved Standards

None: UL/CSA  
Y: EN60950/EN41003  
(Standard coil models - 5, 12, 24 VDC)

#### 6. Rated Coil Voltage

3, 4.5, 5, 12, 24 VDC

# Specification

## ■ Contact Data

| Load                    | Resistive load (cos $\phi$ = 1)   |
|-------------------------|-----------------------------------|
| Rated load              | 0.5 A at 125 VAC<br>2 A at 30 VDC |
| Contact material        | Ag (Au clad)                      |
| Max. carry current      | 2 A                               |
| Max. operating voltage  | 250 VAC, 220 VDC                  |
| Max. operating current  | 2 A                               |
| Max. switching capacity | 62.5 VA, 60 W                     |
| Min. permissible load   | 10 $\mu$ A, 10 mVDC               |

Note: P level:  $\lambda_{60} = 0.1 \times 10^{-6}$ /operation

This value was measured at a switching frequency of 120 operations/min and the criterion of contact resistance is 50  $\Omega$ . This value may vary depending on the operating environment. Always double-check relay suitability under actual operating conditions.

## ■ Coil Data

### G6S - Standard Non-latching (G6S-2F, G6S-2G, G6S-2)

| Rated voltage (VDC) | Rated current (mA) | Coil resistance ( $\Omega$ ) | Pick-up voltage    | Dropout voltage | Maximum voltage  | Power consumption (mW) |
|---------------------|--------------------|------------------------------|--------------------|-----------------|------------------|------------------------|
|                     |                    |                              | % of rated voltage |                 |                  |                        |
| 3                   | 46.7               | 64.3                         | 75% max.           | 10% min.        | 200% max. @ 23°C | Approx. 140            |
| 4.5                 | 31.0               | 145                          |                    |                 |                  |                        |
| 5                   | 28.1               | 178                          |                    |                 |                  |                        |
| 12                  | 11.7               | 1,028                        |                    |                 |                  |                        |
| 24                  | 8.3                | 2,880                        |                    |                 | 170% max. @ 23°C | Approx. 200            |

### G6SU - Standard Single Coil Latching (G6SU-2F, G6SU-2G, G6SU-2)

| Rated voltage (VDC) | Rated current (mA) | Coil resistance ( $\Omega$ ) | Coil Inductance (H) (ref. value) |             | Set pick-up voltage | Reset pick-up voltage | Maximum voltage  | Power consumption (mW) |
|---------------------|--------------------|------------------------------|----------------------------------|-------------|---------------------|-----------------------|------------------|------------------------|
|                     |                    |                              | Armature OFF                     | Armature ON | % of rated voltage  |                       |                  |                        |
| 3                   | 33.3               | 90                           | 0.108                            | 0.069       | 75% max.            | 75% max.              | 180% max. @ 23°C | Approx. 100            |
| 4.5                 | 22.2               | 203                          | 0.27                             | 0.14        |                     |                       |                  |                        |
| 5                   | 20.0               | 250                          | 0.36                             | 0.18        |                     |                       |                  |                        |
| 12                  | 8.3                | 1,440                        | 2.12                             | 1.14        |                     |                       |                  |                        |
| 24                  | 6.3                | 3,840                        | 5.80                             | 3.79        |                     |                       |                  | Approx. 150            |

### G6SK - Standard Dual Coil Latching (G6SK-2F, G6SK-2G, G6SK-2)

| Rated voltage (VDC) | Rated current (mA) | Coil resistance ( $\Omega$ ) | Coil Inductance (H) (ref. value) |             |              |             | Set pick-up voltage | Reset pick-up voltage | Maximum voltage  | Power consumption (mW) |
|---------------------|--------------------|------------------------------|----------------------------------|-------------|--------------|-------------|---------------------|-----------------------|------------------|------------------------|
|                     |                    |                              | Set                              |             | Reset        |             | % of rated voltage  |                       |                  |                        |
|                     |                    |                              | Armature OFF                     | Armature ON | Armature OFF | Armature ON |                     |                       |                  |                        |
| 3                   | 66.6               | 45                           | 0.045                            | 0.035       | 0.032        | 0.045       | 75% max.            | 75% max.              | 170% max. @ 23°C | Approx. 200            |
| 4.5                 | 44.4               | 101                          | 0.12                             | 0.074       | 0.082        | 0.14        |                     |                       |                  |                        |
| 5                   | 40                 | 125                          | 0.14                             | 0.088       | 0.098        | 0.16        |                     |                       |                  |                        |
| 12                  | 16.7               | 720                          | 0.60                             | 0.41        | 0.46         | 0.54        |                     |                       |                  |                        |
| 24                  | 12.5               | 1,920                        | 1.98                             | 1.23        | 1.34         | 2.23        |                     |                       | 140% max. @ 23°C | Approx. 300            |

### G6S - European Version, Non-latching (G6S-2F-Y, G6S-2G-Y, G6S-2-Y)

| Rated voltage (VDC) | Rated current (mA) | Coil resistance ( $\Omega$ ) | Pick-up voltage    | Dropout voltage | Maximum voltage  | Power consumption (mW) |
|---------------------|--------------------|------------------------------|--------------------|-----------------|------------------|------------------------|
|                     |                    |                              | % of rated voltage |                 |                  |                        |
| 5                   | 40.0               | 125                          | 75% max.           | 10% min.        | 170% max. @ 23°C | Approx. 200            |
| 12                  | 16.7               | 720                          |                    |                 |                  |                        |
| 24                  | 9.6                | 2,504                        |                    |                 |                  | Approx. 230            |

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of  $\pm 10\%$ .

2. The operating characteristics are measured at a coil temperature of 23°C.

3. Pick-up voltage will vary with temperature.

4. The maximum voltage is the highest voltage that can be imposed on the relay coil.




## ■ Characteristics

|                                           |                                       |                                                                                                                                                                                                                                                                                                                                                            |
|-------------------------------------------|---------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Contact resistance (See note 1)</b>    |                                       | 75 mΩ max.                                                                                                                                                                                                                                                                                                                                                 |
| <b>Operate (set) time (See note 2)</b>    |                                       | 4 ms max. (mean value approx. 2.5 ms G6S; 2.0 ms G6SU, G6SK)                                                                                                                                                                                                                                                                                               |
| <b>Release (reset) time (See note 2)</b>  |                                       | 4 ms max. (mean value approx. 1.5 ms G6S; 2.0 ms G6SU, G6SK)                                                                                                                                                                                                                                                                                               |
| <b>Bounce time</b>                        |                                       | Approx. 0.5 ms                                                                                                                                                                                                                                                                                                                                             |
| <b>Max. operating frequency</b>           |                                       | Mechanical: 36,000 operations/hr<br>Electrical: 1,800 operations/hr (under rated load)                                                                                                                                                                                                                                                                     |
| <b>Insulation resistance (See note 3)</b> |                                       | 1,000 MΩ min. (at 500 VDC)                                                                                                                                                                                                                                                                                                                                 |
| <b>Dielectric strength</b>                |                                       | 2,000 VAC, 50/60 Hz for 1 minute (G6S, G6SU) between coil and contacts<br>1,000 VAC, 50/60 Hz for 1 minute (G6SK) between coil and contacts<br>1,500 VAC, 50/60 Hz for 1 minute between contacts of different poles<br>1,000 VAC, 50/60 Hz for 1 minute between contacts of same pole<br>500 VAC, 50/60 Hz for 1 minute between set and reset coils (G6SK) |
| <b>Surge withstand voltage</b>            | <b>Conforming to Telcordia specs.</b> | 2,500 V (2 x 10 μS) between coil and contacts for G6S and G6SU<br>2,500 V (2 x 10 μS) between contacts of different poles                                                                                                                                                                                                                                  |
|                                           | <b>Conforming to FCC Part 68</b>      | 1,500 V (10 x 160 μS) between coil and contacts for G6SK<br>1,500 V (10 x 160 μS) between contacts of same pole                                                                                                                                                                                                                                            |
| <b>Vibration</b>                          | <b>Mechanical durability</b>          | 10 to 55 Hz; 5 mm double amplitude                                                                                                                                                                                                                                                                                                                         |
|                                           | <b>Malfunction durability</b>         | 10 to 55 Hz; 3.3 mm double amplitude                                                                                                                                                                                                                                                                                                                       |
| <b>Shock</b>                              | <b>Mechanical durability</b>          | 1,000 m/s <sup>2</sup> ; approx. 100 G                                                                                                                                                                                                                                                                                                                     |
|                                           | <b>Malfunction durability</b>         | 750 m/s <sup>2</sup> ; approx. 75 G                                                                                                                                                                                                                                                                                                                        |
| <b>Ambient temperature</b>                |                                       | -40 to +85°C with no icing; -40 to +70°C with no icing (G6SK, DC24 coil)                                                                                                                                                                                                                                                                                   |
| <b>Ambient Humidity</b>                   |                                       | 5% to 85% RH                                                                                                                                                                                                                                                                                                                                               |
| <b>Service life</b>                       | <b>Mechanical</b>                     | 100,000,000 operations min. (at 36,000 operations/hour)                                                                                                                                                                                                                                                                                                    |
|                                           | <b>Electrical</b>                     | 100,000 operations min. (2A@30VDC, resistive; 1,200 ops/hr.)<br>100,000 operations min. (0.5A@125VAC, resistive)<br>See "Characteristic Data"                                                                                                                                                                                                              |
| <b>Weight</b>                             |                                       | Approx. 2g                                                                                                                                                                                                                                                                                                                                                 |


- Note:** 1. The contact resistance was measured with 10 mA at 1 VDC with a voltage drop method.  
 2. Values in parentheses are typical values unless otherwise stated.  
 3. The insulation resistance was measured with a 500-VDC megohmmeter applied to the same parts as those used for checking the dielectric strength (except between the set and reset coil).  
 4. Data shown are of initial value.

## ■ Characteristic Data


### Service Life




## Maximum Switching Capacity



## Ambient Temperature vs. Maximum Coil Voltage Non-latching




## Single Coil Latching Dual Coil Latching




**Note:** The maximum coil voltage refers to the maximum value in a varying range of operating power voltage, not a continuous voltage.

## Reference Data


### Ambient Temperature vs. Switching Current Non-latching



### Single Coil Latching Dual Coil Latching





## Electrical Service Life




## Dielectric Strength (Standard Version, Non-latching)

Detecting current: 1mA




# Impulse Withstand Voltage (Standard Version, Non-latching)


(2 x 10  $\mu$ s)



(10 x 160  $\mu$ s)




(10 x 160  $\mu$ s)




# Impulse Withstand Voltage (European version)


(2 x 10  $\mu$ s)



(10 x 160  $\mu$ s)





(10 x 160  $\mu$ s)



# Dielectric Strength (European Version, Non-latching)

Detecting current: 1mA





# Dimensions

**Note:** 1. All units are in millimeters unless otherwise indicated.  
2. Coplanarity is 0.1 mm max.


## ■ Standard

### G6S-2F, G6S-2F-Y

Tolerance:  $\pm 0.3$




### Terminal Arrangement/ Internal Connections (Top View)





### Footprint (Top View)

Tolerance:  $\pm 0.1$




### G6S-2G, G6S-2G-Y

Tolerance:  $\pm 0.3$




### Terminal Arrangement/ Internal Connections (Top View)





### Footprint (Top View)

Tolerance:  $\pm 0.1$




### G6S-2, G6S-2-Y

Tolerance:  $\pm 0.3$




### Terminal Arrangement/ Internal Connections (Bottom View)



### Footprint (Bottom View)



Tolerance:  $\pm 0.1$




# ■ Single Coil Latching

## G6SU-2F

Tolerance:  $\pm 0.3$




## Terminal Arrangement/ Internal Connections (Top View)





## Footprint (Top View)

Tolerance:  $\pm 0.1$




## G6SU-2G

Tolerance:  $\pm 0.3$




## Terminal Arrangement/ Internal Connections (Top View)





## Footprint (Top View)

Tolerance:  $\pm 0.1$




## G6SU-2

Tolerance:  $\pm 0.3$




## Terminal Arrangement/ Internal Connections (Bottom View)



## Footprint (Bottom View)



Tolerance:  $\pm 0.1$




# Dual Coil Latching

## G6SK-2F

Tolerance:  $\pm 0.3$




### Terminal Arrangement/ Internal Connections (Top View)





### Footprint (Top View)

Tolerance:  $\pm 0.1$




## G6SK-2G

Tolerance:  $\pm 0.3$




### Terminal Arrangement/ Internal Connections (Top View)





### Footprint (Top View)

Tolerance:  $\pm 0.1$




## G6SK-2

Tolerance:  $\pm 0.3$




### Terminal Arrangement/ Internal Connections (Bottom View)




### Footprint (Bottom View)

Tolerance:  $\pm 0.1$




# Recommended Soldering Method

## (1) IRS Method (Mounting Solder: Lead)



## (2) IRS Method (Mounting Solder: Lead-free)



**Note:** The temperature profile indicates the temperature of the relay terminal section.






# Packaging


|                                       |                                                                                                                                                                     |                             |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| Tube packing                          | Standard nomenclature                                                                                                                                               | 50 pcs per anti-static tube |
| Tape packing (Surface mount versions) | When ordering, add "TR" before the rated coil voltage (e.g., G6S-2F-TR-DC12)<br>Note: TR is not part of the relay model number and will not be marked on the relay. |                             |

## Tape and Reel Dimensions (Surface Mount Models)


- Tape type: TE2416R (Refer to EIAJ - Electronic Industrial Association of Japan)
- Reel type: R24E (Refer to EIAJ - Electronic Industrial Association of Japan)
- Relays per reel: 400
- Reels per packing carton: 2 (800 relays)



G6S-2F, G6SU-2F, G6SK-2F, G6S-2F-Y



G6S-2G, G6SU-2G, G6SK-2G, G6S-2G-Y



## Approvals

UL Recognized (File No. E41515) / CSA Certified (File No. LR31928) - - Ambient Temp. = 40°C

| Type                           | Contact form | Coil rating | Contact ratings                | Number of test operations |
|--------------------------------|--------------|-------------|--------------------------------|---------------------------|
| G6S-2, G6S-2F, G6S-2G          | DPDT         | 2 to 48 VDC | 3 A at 30 VDC (Resistive)      | 6,000                     |
| G6SU-2, G6SU-2F, G6SU-2G       |              | 2 to 24 VDC | 0.3 A at 110 VDC (Resistive)   |                           |
| G6SK-2, G6SK-2F, G6SK-2G       |              |             | 0.5 A at 125 VAC (General Use) |                           |
| G6SK-2-Y, G6SK-2F-Y, G6SK-2G-Y |              |             |                                |                           |

EN60950 / EN41003

| Type                        | Contact form | Isolation Category      | Voltage |
|-----------------------------|--------------|-------------------------|---------|
| G6S-2-Y, G6S-2F-Y, G6S-2G-Y | DPDT         | Supplementary Isolation | 250 VAC |

- Note:** 1. The rated values approved by each of the safety standards (e.g., UL and CSA) may be different from the performance characteristics individually defined in this catalog.  
2. In the interest of product improvement, specifications are subject to change.

# Precautions

- Use a DC power supply with 5% or less ripple factor to operate the coil.
- Do not use the G6S where subject to strong external magnetic fields.
- Do not use the G6S where subject to magnetic particles or excessive amounts of dust.
- Do not reverse the polarity of the coil (+, -).

- Latching types are delivered in the reset position. We recommend that a reset voltage be applied in advance to start operation.
- Do not drop the G6S or otherwise subject it to excessive shock.
- Remove the relay from the packing immediately prior to usage.

## ■ Correct use

### Long-term Continuously ON Contacts

Using the Relay in a circuit where the Relay will be ON continuously for long periods (without switching) can lead to unstable contacts because the heat generated by the coil itself will affect the insulation, causing a film to develop on the contact surfaces. We recommend using a latching relay (magnetic-holding relay) in this kind of circuit. If a single-side stable model must be used in this kind of circuit, we recommend using a fail-safe circuit design that provides protection against contact failure or coil burnout.

### Relay Handling

Use the Relay as soon as possible after opening the moisture-proof package. If the Relay is left for a long time after opening the moisture-proof package, the appearance may suffer and seal failure may occur after the solder mounting process. To store the Relay after opening the moisture-proof package, place it into the original package and sealed the package with adhesive tape.


When washing the product after soldering the Relay to a PCB, use a water-based solvent or alcohol-based solvent, and keep the solvent temperature to less than 40°C. Do not put the Relay in a cold cleaning bath immediately after soldering.

### G6S (K) (-U) -2 Soldering


- Soldering temperature: Approx. 250°C (At 260°C if the DWS method is used.)
- Soldering time: Approx. 5 s max. (Approx. 2 s for the first time and approx. 3 s for the second time if the DWS method is used.)
- Be sure to adjust the level of the molten solder so that the solder will not overflow onto the PCB.

### Claw Securing Force During Automatic Mounting

During automatic insertion of Relays, be sure to set the securing force of each claw to the following so that the Relay's characteristics will be maintained.



Dimension A: 1.96 N max.  
Dimension B: 4.90 N max.  
Dimension C: 1.96 N max.



All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at [http://www.components.omron.com/components/web/webfiles.nsf/sales\\_terms.html](http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html)

**ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.**

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

---

**OMRON**<sup>®</sup>

**OMRON ELECTRONIC  
COMPONENTS LLC**

55 E. Commerce Drive, Suite B  
Schaumburg, IL 60173

**847-882-2288**

**OMRON ON-LINE**

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. X301-E-1b

09/11

Specifications subject to change without notice

Printed in USA