


Visit Hammond's Website at [www.hammondmtg.com](http://www.hammondmtg.com)

Line “Auto” Transformers

- Hard Wired Version
- Single Winding (Does Not Provide Isolation) for Use Where Equipment Is already Isolated and Only Voltage Change Is Required
- Flexible World Wide Applications, 50 or 60 Hz Operation, Step Down (230 VAC to 115 VAC) or Step Up (115 VAC to 230 VAC)
- Flexible Leads, 8" Minimum Length


| Stock No. | Mfr.'s Type | VA (Max.) | Dimensions (Inches) |      |      |      |      | Weight (Lbs.) | EACH  |       |
|-----------|-------------|-----------|---------------------|------|------|------|------|---------------|-------|-------|
|           |             |           | A                   | B    | C    | D    | E    |               | 1-5   | 6-49  |
| 836-6300  | 170A        | 100       | 2.50                | 3.00 | 3.06 | 2.00 | 1.94 | 3.0           | 24.22 | 22.36 |
| 836-6305  | 170B        | 200       | 3.13                | 3.50 | 3.81 | 2.50 | 2.19 | 4.5           | 31.88 | 29.42 |
| 836-6310  | 170C        | 300       | 3.13                | 4.00 | 3.81 | 2.50 | 2.69 | 6.0           | 35.70 | 32.95 |
| 836-6315  | 170D        | 500       | 3.75                | 4.50 | 4.56 | 3.00 | 3.31 | 10.0          | 51.00 | 47.08 |




Line Isolation Transformers

- Included Plug and Receptacle
- Dual Winding (Provides Isolation)
- Electrostatic Shield Between Primary and Secondary
- Primary — 115 VAC 50/60Hz, Secondary — 115 VAC
- Standard 3-Wire, Grounded Plug and Receptacle
- 5 Foot “U-Ground” Cord and Plug


| Stock No. | Mfr.'s Type | VA (Max.) | Dimensions (Inches) |      |      |      |      | Weight (Lbs.) | EACH   |        |
|-----------|-------------|-----------|---------------------|------|------|------|------|---------------|--------|--------|
|           |             |           | A                   | B    | C    | D    | E    |               | 1-5    | 6-49   |
| 836-6320  | 171A        | 100       | 3.75                | 4.00 | 5.00 | 3.00 | 1.88 | 6.5           | 63.84  | 58.92  |
| 836-6325  | 171B        | 200       | 3.75                | 4.50 | 5.00 | 3.00 | 2.38 | 8.0           | 77.20  | 71.26  |
| 836-6330  | 171C        | 300       | 3.75                | 5.00 | 5.00 | 3.00 | 2.88 | 11.0          | 80.87  | 74.65  |
| 836-6335  | 171E        | 500       | 3.75                | 6.00 | 5.00 | 3.00 | 3.88 | 14.0          | 114.17 | 105.39 |



Low Voltage Rectifier Transformers



C Style



H Style

- All Primaries 115 Volts, 60 Hz
- Primary and Secondary Leads 6" Long

| Stock No. | Mfr.'s Type | Style | Secondary |       | Dimensions |      |      |      |           | EACH  |       |
|-----------|-------------|-------|-----------|-------|------------|------|------|------|-----------|-------|-------|
|           |             |       | Volts     | Amps  | A          | B    | C    | D    | G         | 1-4   | 5-9   |
| 836-6005  | 166L2       | C     | 2.5 ct    | 2.50  | 2.81       | 1.50 | 1.69 | 2.38 | .187      | 14.08 | 13.09 |
| 836-6010  | 166Q2       | C     | 2.5 ct    | 6.00  | 3.25       | 1.63 | 2.00 | 2.81 | .187      | 14.59 | 14.00 |
| 836-6015  | 166G6       | C     | 6.3 ct    | 0.60  | 2.38       | 1.38 | 1.38 | 2.00 | .187      | 12.13 | 11.64 |
| 836-6020  | 166J6       | C     | 6.3 ct    | 1.00  | 2.81       | 1.50 | 1.69 | 2.38 | .187      | 13.08 | 12.55 |
| 836-6025  | 166L6       | C     | 6.3 ct    | 2.00  | 2.81       | 1.63 | 1.69 | 2.38 | .187      | 13.15 | 12.61 |
| 836-6030  | 166N6       | C     | 6.3 ct    | 4.00  | 3.25       | 1.75 | 2.00 | 2.81 | .187      | 13.94 | 13.37 |
| 836-6035  | 166J8       | C     | 8.5 ct    | 1.00  | 2.81       | 1.50 | 1.69 | 2.38 | .187      | 15.42 | 14.23 |
| 836-6040  | 166L8       | C     | 8.5 ct    | 2.00  | 3.25       | 1.63 | 2.00 | 2.81 | .187      | 13.53 | 12.98 |
| 836-6045  | 166G10      | C     | 10.0 ct   | 0.50  | 2.38       | 1.50 | 1.38 | 2.00 | .187      | 12.69 | 12.17 |
| 836-6055  | 166M10      | C     | 10.0 ct   | 3.00  | 3.25       | 2.00 | 2.00 | 2.81 | .187      | 15.20 | 14.12 |
| 836-6060  | 166F12      | C     | 12.6 ct   | 0.30  | 2.38       | 1.38 | 1.38 | 2.00 | .187      | 12.17 | 11.68 |
| 836-6065  | 166G12      | C     | 12.6 ct   | 0.50  | 2.81       | 1.50 | 1.69 | 2.38 | .187      | 12.91 | 12.37 |
| 836-6070  | 166J12      | C     | 12.6 ct   | 1.00  | 2.81       | 1.63 | 1.69 | 2.38 | .187      | 13.36 | 12.81 |
| 836-6075  | 166L12      | C     | 12.6 ct   | 2.50  | 3.25       | 2.00 | 2.00 | 2.81 | .187      | 14.67 | 14.07 |
| 836-6080  | 166N12      | C     | 12.6 ct   | 4.00  | 3.69       | 2.13 | 2.31 | 3.13 | .187      | 19.82 | 18.30 |
| 836-6085  | 166Q12      | C     | 12.6 ct   | 6.00  | 4.03       | 2.25 | 2.63 | 3.56 | .187      | 22.86 | 21.24 |
| 836-6090  | 165S12      | H     | 12.6 ct   | 10.00 | 3.00       | 3.25 | 2.56 | 2.50 | .22 x .56 | 38.94 | 36.17 |
| 836-6095  | 165V12      | H     | 12.6 ct   | 20.00 | 3.75       | 3.63 | 3.13 | 3.13 | .22 x .56 | 53.43 | 49.33 |
| 836-6100  | 166E14      | C     | 14.0 ct   | 0.15  | 2.06       | 1.38 | 1.19 | 1.75 | .187      | 15.11 | 14.05 |
| 836-6105  | 166G14      | C     | 14.0 ct   | 0.50  | 2.81       | 1.50 | 1.69 | 2.38 | .187      | 12.94 | 12.40 |
| 836-6110  | 166J14      | C     | 14.0 ct   | 1.00  | 2.81       | 1.63 | 1.69 | 2.38 | .187      | 12.02 | 11.53 |
| 836-6115  | 166F16      | C     | 16.0 ct   | 0.25  | 2.38       | 1.38 | 1.38 | 2.00 | .187      | 12.45 | 11.94 |
| 836-6120  | 166G16      | C     | 16.0 ct   | 0.50  | 2.81       | 1.50 | 1.69 | 2.38 | .187      | 12.96 | 12.42 |
| 836-6125  | 166J16      | C     | 16.0 ct   | 1.00  | 3.25       | 1.63 | 2.00 | 2.81 | .187      | 13.49 | 12.94 |
| 836-6130  | 166L16      | C     | 16.0 ct   | 2.20  | 3.25       | 2.00 | 2.00 | 2.81 | .187      | 14.38 | 13.78 |

- Horizontal Channel Bracket Two Hole Mount (C Style) or Open Horizontal Four Hole Mount (H Style)

| Stock No. | Mfr.'s Type | Style | Secondary |       | Dimensions |      |      |      |           | EACH  |       |
|-----------|-------------|-------|-----------|-------|------------|------|------|------|-----------|-------|-------|
|           |             |       | Volts     | Amps  | A          | B    | C    | D    | G         | 1-4   | 5-9   |
| 836-6135  | 166M16      | C     | 16.0 ct   | 3.00  | 3.69       | 2.13 | 2.31 | 3.13 | .187      | 18.27 | 16.96 |
| 836-6140  | 166K18      | C     | 18.0 ct   | 1.50  | 3.25       | 1.75 | 2.00 | 2.81 | .187      | 15.11 | 14.04 |
| 836-6145  | 166M18      | C     | 18.0 ct   | 3.00  | 3.69       | 2.13 | 2.31 | 3.13 | .187      | 21.01 | 19.51 |
| 836-6150  | 166P18      | C     | 18.0 ct   | 5.00  | 4.03       | 2.50 | 2.63 | 3.56 | .187      | 24.42 | 22.67 |
| 836-6155  | 165S18      | H     | 18.0 ct   | 10.00 | 3.75       | 3.13 | 3.13 | 3.13 | .22 x .56 | 45.99 | 42.43 |
| 836-6165  | 166E20      | C     | 20.0 ct   | 0.15  | 2.06       | 1.38 | 1.19 | 1.75 | .187      | 14.17 | 13.57 |
| 836-6170  | 166G20      | C     | 20.0 ct   | 0.50  | 2.81       | 1.63 | 1.69 | 2.38 | .187      | 12.94 | 12.40 |
| 836-6175  | 166J20      | C     | 20.0 ct   | 1.00  | 3.25       | 1.75 | 2.00 | 2.81 | .187      | 13.50 | 12.94 |
| 836-6180  | 166L20      | C     | 20.0 ct   | 2.00  | 3.69       | 1.88 | 2.31 | 3.13 | .187      | 18.47 | 17.70 |
| 836-6185  | 165T22      | H     | 22.0 ct   | 12.00 | 4.50       | 3.88 | 3.75 | 3.75 | .28 x .56 | 54.35 | 50.16 |
| 836-6190  | 166L24      | C     | 24.0 ct   | 2.00  | 3.69       | 2.13 | 2.31 | 3.13 | .187      | 19.25 | 17.76 |
| 836-6195  | 166N24      | C     | 24.0 ct   | 4.00  | 4.50       | 2.50 | 2.88 | 4.00 | .203      | 26.80 | 24.74 |
| 836-6200  | 166E25      | C     | 25.0 ct   | 0.15  | 2.38       | 1.38 | 1.38 | 2.00 | .187      | 12.20 | 11.70 |
| 836-6205  | 166F25      | C     | 25.0 ct   | 0.30  | 2.81       | 1.50 | 1.69 | 2.38 | .187      | 12.93 | 12.39 |
| 836-6210  | 166G25      | C     | 25.0 ct   | 0.50  | 2.81       | 1.63 | 1.69 | 2.38 | .187      | 13.15 | 12.62 |
| 836-6215  | 166J25      | C     | 25.0 ct   | 1.00  | 3.25       | 1.75 | 2.00 | 2.81 | .187      | 13.97 | 13.39 |
| 836-6220  | 166K25      | C     | 25.0 ct   | 1.50  | 3.69       | 1.88 | 2.31 | 3.13 | .187      | 16.16 | 15.49 |
| 836-6225  | 166L25      | C     | 25.0 ct   | 2.00  | 3.69       | 2.13 | 2.31 | 3.13 | .187      | 16.64 | 15.95 |
| 836-6235  | 165S25      | H     | 25.0 ct   | 10.00 | 3.75       | 3.63 | 3.13 | 3.13 | .22 x .56 | 47.31 | 43.93 |
| 836-6240  | 166G28      | C     | 28.0 ct   | 0.50  | 2.81       | 1.63 | 1.69 | 2.38 | .187      | 14.36 | 13.33 |
| 836-6245  | 166J28      | C     | 28.0 ct   | 1.00  | 3.25       | 2.00 | 2.00 | 2.81 | .187      | 15.06 | 13.98 |
| 836-6250  | 165S30      | H     | 30.0 ct   | 10.00 | 4.50       | 3.88 | 3.75 | 3.75 | .28 x .56 | 47.98 | 46.01 |
| 836-6255  | 166J33      | C     | 33.0 ct   | 1.00  | 3.25       | 2.00 | 2.00 | 2.81 | .187      | 14.37 | 13.79 |
| 836-6265  | 166G36      | C     | 36.0 ct   | 0.50  | 2.81       | 1.63 | 1.69 | 2.38 | .187      | 14.44 | 13.40 |
| 836-6270  | 166J36      | C     | 36.0 ct   | 1.00  | 3.69       | 1.88 | 2.31 | 3.13 | .187      | 16.17 | 15.51 |