



Products > Audio > XLR > XLR Chassis Connectors > B Series > NC3MBHL-B

print

NC3MBHL-B

3 pole male XLR receptacle, grounding: separate ground contact to mating connector shell and front panel, steel retention lug, lateral left PCB mount, black chrome shell

Same as A series with exception of a metal mounting flange featuring continuous circumferential ground contact to chassis for best EMC practice. UL recognized component.



Features & Benefits

- Smallest XLR receptacles, highest packing density
- Metal mounting flange featuring continuous circumferential ground contact to chassis for best EMC and RF protection
- Housing flammability UL94V-0

Technical Information hide

Product	
Title	NC3MBHL-B
Connection Type	XLR
Gender	male
Electrical	
Capacitance between contacts	≤ 4 pF
Contact resistance	≤ 5 mΩ (inner)
Dielectric strength	1,5 kVdc
Insulation resistance	> 2 GΩ (initial)
Rated current per contact	6 A
Rated voltage	50 V
Grounding Options	Separate ground contact connected to mating connector shell and front panel, no connection to Pin 1
Mechanical	

Downloads

-  [Product Guide 2012, 02 XLR](#)
-  [Drawing NC3MBHL](#)
-  [Drawing NC3MBHL](#)

Links

-  [UL Certificate \(ECBT2.E135070\)](#)

Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Locking device	Latch lock
Mounting direction	rear
Chassis shape	B
Mounting	B-Screw

Material

Contacts	Brass (CuZn35Pb2)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Stahl Ck67
Ring	Zinc diecast (ZnAl4Cu1)
Flange	Black Metal

Environmental

Approvals	UL
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

Accessories



B-SCREW-1-8



CAS-DUMMY



NDM



SCM

