





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER E.O.P20196	07MAY2009	-	RDR
	B	REVISED PER E.O.P20274	09SEPT2009	-	RDR
	C	REVISER PER PCN-24-226269	06JAN2025	AJT	MB
	D	REVISED PER PCN-25-253066	27JUN2025	UBF	CB

3D VIEW



4 MATERIAL: RECEPTACLE: PA66 GF15, GRAY
CAP: PA66 GF15, BLACK
WEDGELOCK (INCLUDED): PBT GF30 (GREEN)
BUSBAR: COPPER ALLOY, NICKEL PLATED.

3. THE 8 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 52 AMPS.

2 ORIENTATION OF "DEUTSCH" AND "-P021" TO BE OPTIONAL.

1. MATES WITH DT06-08SA-XXXX (XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR MODIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. MCCORD	23APR2009	 TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK -	-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	-	NAME DT 8 WAY RECEPTACLE KEY ARRANGEMENT A 8 PIN BUSBAR-NICKEL PLATED COLOR; GREY		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±025[0,63] 4 PLC ± ANGLES ±		PRODUCT SPEC 108-151009	-			
MATERIAL 4		APPLICATION SPEC 114-151009	-	SIZE A3	CAGE CODE 00779	DRAWING NO C-DT04-08PA-P021
		WEIGHT -	-	RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE 2:1	SHEET 1	OF 1	REV D