

D2SBA60

600V 1.5A


FEATURES

- Thin Single In-Line Package
- High IFSM
- Applicable to Automatic Insertion

APPLICATION

- Switching power supply
- Home Appliances, Office Equipment
- Telecommunication, Factory Automation

OUTLINE DIMENSIONS



RATINGS

●Absolute Maximum Ratings (If not specified TI=25°C)


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-40~150	°C
Operating Junction Temperature	T _j		150	°C
Maximum Reverse Voltage	V _{RM}		600	V
Average Rectified Forward Current	I _{FO}	50Hz sine wave, R-load, On glass-epoxy substrate, T _a =25°C	1.5	A
Peak Surge Forward Current	I _{FSM}	50Hz sine wave, Non-repetitive 1cycle peak value, T _j =25°C	60	A
Current Squared Time	I ² t	1ms≤t<10ms T _j =25°C	16	A ² s

●Electrical Characteristics (If not specified Tl=25°C)

Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	V_F	$I_F=0.75A$, Pulse measurement, Rating of per diode	Max.1.05	V
Reverse Current	I_R	$V_R=V_{RM}$, Pulse measurement, Rating of per diode	Max.10	μA
Thermal Resistance	θ_{jl}	junction to lead	Max.10	$^{\circ}C/W$
	θ_{ja}	junction to ambient	Max.47	


D2SBAX

Forward Voltage



D2SBAx

Forward Power Dissipation




$T_j = 150^\circ\text{C}$

Sine wave

D2SBAx

Derating Curve



Sine wave
R-load
Free in air

D2SBAx

Peak Surge Forward Capability

