






PART NUMBER	# OF COLUMNS	DIM "A" MAX	DIM "B"
76011 - *6**	6	22.20	18.50
76011 - *1**	10	37.00	33.30



76011-***0*
UNGUIDED,
OPEN ENDED



- NOTES:
1. MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP), BLACK, UL 94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
 2. FINISH: SELECTIVE 30μ * GOLD IN CONTACT AREA WITH LUBE.
SELECTIVE TIN/LEAD (-0***) OR SELECTIVE TIN (-1***)
ON PCB TAILS. NICKEL UNDERPLATE OVERALL.
 3. MOLEX PRODUCT SPECIFICATION: PS-75710-999.
 4. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPEC PS-45499-002.
 5. PACKAGED PER PK-70873-588.

CLARIFY ST GRD EC NO: UCP2008-2982 DRWN: C STEWART 2008/06/11 CHKD: TELO 2008/06/11 APPR: J BINGHAM 2008/06/11	DESCRIPTION REVISION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY ELO	DATE 2006/11/13	TITLE I-TRAC 7-ROW RIGHT ANGLE MALE OPEN ASSEMBLY					
			4 PLACES ± ---	± ---	CHECKED BY	DATE						
			3 PLACES ± ---	± ---	ELO	2007/02/02						
			2 PLACES ± 0.25	± ---	APPROVED BY	DATE	MOLEX MOLEX INCORPORATED					
			1 PLACE ± 0.13	± ---	CBIXLER	2007/02/02						
			ANGULAR ± ---°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-76011-001		1 OF 3			
			SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

13 12 11 10 9 8 7 6 5 4 3 2 1


7 6 0 1 1 - * * * *

MODULE TYPE -- TAIL PLATING TYPE
0 = UNGUIDED - TIN/LEAD
1 = UNGUIDED - TIN ONLY


OF COLUMNS
6 = 6 COL
1 = 10 COL

ORIENTATION
GUIDE POST
0 = OPEN ENDED
1 = LEFT-END WALL
2 = RIGHT-END WALL
3 = DUAL-END WALL


PIN LENGTH (P)
3 = 4.70
5 = 3.80, 4.70 STAGGERED




STAGGERED PIN OPTION
(76011-***5)



76011-**1*
LEFT-END WALL



76011-**2*
RIGHT-END WALL





76011-**3*
DUAL-END WALL

REM OPT 76011-***6				DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
EC NO: UCP2008-2982						▽=0 ▽=0	mm INCH		DRAWN BY DATE		TITLE I-TRAC 7-ROW RIGHT ANGLE MALE OPEN ASSEMBLY			
DRWN: STEWART 2008/06/11							4 PLACES ± --- ± ---	ELO 2006/11/13						
CHKD: TELO 2008/06/11							3 PLACES ± --- ± ---	CHECKED BY DATE						
APPR: BINGHAM 2008/06/11					2 PLACES ± 0.25 ± ---	ELO 2007/02/02	APPROVED BY DATE		MOLEX MOLEX INCORPORATED					
					1 PLACE ± 0.13 ± ---	CBIXLER 2007/02/02	MATERIAL NO.						DOCUMENT NO.	
						ANGULAR ± ---°		SEE CHART		SD-76011-001			2 OF 3	
				REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

12 11 10 9 8 7 6 5 4 3 2 1



COPLANAR APPLICATION



**COPLANAR
MATED SIGNAL PATHS**

RAM PIN A4b.....	DC PIN A1a
RAM PIN A4a.....	DC PIN A1b
RAM PIN A1b.....	DC PIN A4a
RAM PIN A1a.....	DC PIN A4b

INVERTED APPLICATION



**INVERTED
MATED SIGNAL PATHS**

RAM PIN G1a.....	DC PIN A1a
RAM PIN G1b.....	DC PIN A1b
RAM PIN G4a.....	DC PIN A4a
RAM PIN G4b.....	DC PIN A4b

SEE SHEET 1
EC NO: UCP2008-2982
DRAWN: STEWART
CHKD: TELO
APPR: J. BINGHAM

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0004
3 PLACES	± .005	± .0004
2 PLACES	± .025	± .0010
1 PLACE	± 0.13	± .0050

ANGULAR ± .005°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY	DATE
ELO	2006/11/13
CHECKED BY	DATE
ELO	2007/02/02
APPROVED BY	DATE
CBIXLER	2007/02/02

MATERIAL NO.

SEE SHEET 2

SCALE
4:1

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

**I-TRAC 7-ROW
RIGHT ANGLE MALE
OPEN ASSEMBLY**

MOLEX INCORPORATED

DOCUMENT NO.
SD-76011-001

SHEET NO.
3 OF 3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION