




COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THE DRAWING. WITHOUT OUR PRIOR CONSENT,
THIS DOCUMENT CANNOT BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS,
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



Fy^{*1)} xx^{*2)} P7-K120

e.g. FL25P7-K120

*1) y for series FL or FU

*2) xx No. of contacts 09, 15, 25 or 37

xx	A [mm]	B [mm]	C [mm]	D [mm]
09	30,8	16,9	25	19,3
15	39,1	25,2	33,3	27,5
25	53	38,9	47,04	41,3
37	69,3	55,3	63,5	57,7

Technical data for modification -K120 (FU)

Crimp contacts FK20S (AWG 20-24/1,3µm Au) included in delivery

3	1	Shell	Steel	tin plated
2	1	Insulator rear part	PI (-55°C - +130°C)	green
1	1	Insulator front part	PBTP	green
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

Technical data for modification -K120 (FL)

3	1	Shell	Steel	tin plated
2	1	Insulator rear part	PA66 (-55°C - +115°C)	black
1	1	Insulator front part	PBTP	black
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

				Measurement without tolerance occ. to ISO 2768-m	SCALE 2:1	TITLE
				DATE	NAME	
			DRAWN	21-11-2003	Denzinger	
			CHECKED	21-11-2003	ffloßmann	
1						
REV.	DATE	CH.-NO.	ORIGINAL: DIN A3-DRAWING AS A FILE	REPLACEMENT FOR:	FyxxP7-K120 a	PAGES 1

D-Sub Crimp Connector

DWG.NO. FyxxP7-K120 REV. 1