

SUBJECT: Metallized Polypropylene Film Capacitor, ECW-H(L) series

BULLETIN #: DCN.PG42.01.31.05-1

Date: Jan. 31, 2005 Page 1 of 1

LAST ORDER DATE: December 30, 2004

LAST SHIPMENT DATE: February 1, 2005

DISCONTINUATION DETAILS: The ECW-H(L) series will be discontinued due to a change in our merchandise plan. No replacement parts will be offered. Instead we will continue to support our ECW-H(V) series

	ECW H (L) series		ECW H (V) series	
Operating Temperature	-40 to 110 C		-25 to 85 C	
Voltage	Voltage	Cap Range	Voltage	Cap Range
	800VDC	0.001 to 0.056 uF	800VDC	0.001 to 0.091
	1250VDC (1000Vp-p)	0.001 to 0.022uF	1250VDC (1000Vp-p)	0.001 to 0.091
	1600VDC (1250Vp-p)	0.001 to 0.022uF	1600VDC (1200Vp-p)	0.001 to 0.056
Tolerance	+3% (I), +5% (J)		+3% (I), +5% (J)	
Withstand Voltage (Between terminals)	Rated Voltage (VDC) times 140% 60 Sec		Rated Voltage (VDC) times 150% 60 Sec	
Dissipation Factor	0.1% Max at 20C, 1kHz		0.1% Max at 20C, 1kHz	
	0.2% Max at 20C, 10kHz		0.2% Max at 20C, 10kHz	
Insulation Resistance	30000M Ohm (at 20C, 500VDC, 60Sec)		30000M Ohm min (at 20C, 500VDC, 60Sec)	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panasonic:](#)

[ECW-H8122HL](#)